

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 216152

Battery Holder

BH Series




For Six "AA" Cells

BH-363A
 Lead wire (150mm)
 Strip & Tin: 5mm+/-1mm
 UL1007, AWG#26

BH-363B
 Four-prong or six-prong snap terminal

BH-363D
 With TAG (Solder, LUG) Terminal




For one "AA" Cell

BH-311-2A
 Lead wire (150mm)
 Strip & Tin: 5mm+/-1mm
 UL1007, AWG#26

BH-311-2D
 With TAG (Solder, LUG) Terminal

BH-311-2P
 With Pin (PC Mounted)




For two "AA" Cells

BH-321-2A
 Lead wire (150mm)
 Strip & Tin: 5mm+/-1mm
 UL1007, AWG#26

BH-321-2AS
 Lead wire (150mm)
 Strip & Tin: 5mm+/-1mm
 UL1007, AWG#26
 With Switch

BH-321-2D
 With TAG (Solder, LUG) Terminal

BH-321-2P
 With Pin (PC Mounted)




For two "AA" Cells

BH-321-4A
 Lead wire (150mm)
 Strip & Tin: 5mm+/-1mm
 UL1007, AWG#26

BH-321-4B
 Four-prong or six-prong snap terminal

BH-321-4D
 With TAG (Solder, LUG) Terminal

BH-321-4P
 With Pin (PC Mounted)






For four "AA" Cells

BH-341-2A
 Lead wire (150mm)
 Strip & Tin: 5mm+/-1mm
 UL1007, AWG#26

BH-341-2B
 Four-prong or six-prong snap terminal

BH-341-2D
 With TAG (Solder, LUG) Terminal

BH-341-2P
 With Pin (PC Mounted)




For three "AA" Cells

BH-331-A
 Lead wire (150mm)
 Strip & Tin: 5mm+/-1mm
 UL1007, AWG#26

BH-331-B
 Four-prong or six-prong snap terminal

BH-331-D
 With TAG (Solder, LUG) Terminal

BH-331-P
 With Pin (PC Mounted)




For four "AA" Cells

BH-343-1A
 Lead wire (150mm)
 Strip & Tin: 5mm+/-1mm
 UL1007, AWG#26

BH-343-1B
 Four-prong or six-prong snap terminal


BH-343-1D
 With TAG (Solder, LUG) Terminal



For six "AA" Cells

BH-364-A
 Lead wire (150mm)
 Strip & Tin: 5mm+/-1mm
 UL1007, AWG#26

BH-364-D
 With TAG (Solder, LUG) Terminal




Battery Holder

BH Series



BH-382-A
Lead wire (150mm)
Strip & Tin: 5mm+/-1mm
UL1007, AWG#26




BH-382-B
Four-prong or six-prong snap terminal

BH-382-D
With TAG (Solder, LUG) Terminal

For eight "AA" Cells



BH-383-A
Lead wire (150mm)
Strip & Tin: 5mm+/-1mm
UL1007, AWG#26




BH-383-B
Four-prong or six-prong snap terminal

BH-383-D
With TAG (Solder, LUG) Terminal

For eight "AA" Cells



BH-421-1A
Lead wire (150mm)
Strip & Tin: 5mm+/-1mm
UL1007, AWG#26



BH-421-1B
Four-prong or six-prong snap terminal


BH-421-1D
With TAG (Solder, LUG) Terminal

For two "AA" Cells

BH-421-1P
With Pin (PC Mounted)



BH431-1A
With lead wires 150mm
Strip & Tin: 5mm+/-1mm
UL1007, AWG#26



BH431-1B
With 4prong or 6prongsnap terminal

BH431-1D
With TAG(Solder,LUG)Terminal

For Three "AAA" Cells

BH431-1P
With Pin(PC Mounted)

Battery Holder


BH Series



BH9VA
With lead wires 150mm
Strip & Tin: 5mm +/- 1mm
UL1007, AWG#26

BH9VD
With TAG (Solder, LUG) Terminal

BH9VP
With Pin (PC Mounted)



FOR 9V CELL