


**Audio-Video Adapters**

Black Molded Plastic Construction  
Nickel- or Gold-Plated Contacts



- 251-110** Nickel
- 251-111** Gold
- 251-113** Gold
- 251-115** Nickel
- 251-116** Gold
- 251-117** Gold
- 251-118** Nickel
- 251-120** Nickel
- 251-122** Nickel
- 251-200** Gold
- 251-125** Nickel
- 251-130** Nickel
- 251-140** Nickel
- 251-142** Nickel
- 251-149** Nickel
- 251-150** Nickel
- 251-151** Gold
- 251-152** Gold
- 251-153** Gold
- 251-154** Gold
- 251-155** Nickel
- 251-156** Nickel
- 251-160** Nickel
- 251-165** Nickel
- 251-175** Nickel
- 251-310** Nickel
- 251-320** Nickel
- 251-330** Nickel
- 251-340** Nickel
- 251-410** Gold
- 260-700** Gold
- 260-710** Gold

- 251-110** RCA Coupler Plug-Plug
- 251-111** RCA Jack – RCA Plug 90° Connector
- 251-113** 2 x RCA Jack – RCA Plug
- 251-115** RCA Coupler Jack-Jack
- 251-116** RCA Coupler Jack-Jack
- 251-117** RGB RCA Coupler 3 x Jack – 3 x Jack
- 251-118** 3.5mm St-Jack – 3.5mm St Jack
- 251-120** RCA Jack to 1/4" Mono Plug
- 251-122** RCA Jack to 3.5mm Mono Plug
- 251-125** 3.5mm Mn-Jack – 2.5mm Mn-Plug
- 251-130** 2x3.5mm St-Jack – 3.5mm St-Plug
- 251-140** 2x1/4" St-Jack to 3.5mm St-Plug
- 251-142** 2x3.5mm St-Jacks to 1/4" St-Plug
- 251-149** 1/4" Mono Jack to RCA Plug
- 251-150** 3.5mm Mono Jack to RCA Plug
- 251-151** S-Video Jack – RCA Jack
- 251-152** S-Video Plug – RCA Jack
- 251-153** S-Video Jack – RCA Plug
- 251-154** S-Video Plug – RCA Plug
- 251-155** 1/4" St-Jack to 3.5mm St-Plug
- 251-156** 3.5mm Mn-Jack to 1/4" Mn-Plug
- 251-160** 3.5mm St-Jack to 1/4" St-Plug
- 251-165** 3.5mm St-Jack to 3.5mm Mn-Plug
- 251-175** 1/4" Mn-Jack to 3.5mm Mn-Plug
- 251-200** RCA Jack to 3.5mm Mn-Plug
- 251-310** 3C XLR Jack to XLR Jack
- 251-320** 3C XLR Plug to XLR Plug
- 251-330** 3C XLR Jack to 1/4" Mono Plug
- 251-340** 3C XLR Plug to 1/4" Mono Plug
- 251-410** 4-Pin Mini Din Jack to Jack
- 260-700** Toslink-Toslink Extension Adapter
- 260-710** Toslink to Mini-Plug Adapter