

Distributed by:

JAMECO[®]
ELECTRONICS


www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.


Jameco Part Number 855471

LOC	DIST	P	F	ZONE	LTR	REV AND REDWN PER ECN CM-11	DESCRIPTION	DATE	APPD
CM	54				L			3-27-91	TS RS

1. DIMENSIONS IN BRACKETS ARE IN INCHES.




SECTION A-A



3-DIMENSIONAL MODEL
NTS

QTY	DESCRIPTION	UNIT	WEIGHT	DR	DATE	NAME	PART NO
24	CIRCUIT ASSY		95.10		4-2-91	AMPA	640551-4
23	CIRCUIT ASSY		91.14		4-5-91	AMPA	2-640551-3
22	CIRCUIT ASSY		87.17		4-10-91	AMPA	2-640551-2
21	CIRCUIT ASSY		83.21			AMPA	2-640551-1
20	CIRCUIT ASSY		79.25			AMPA	2-640551-0
19	CIRCUIT ASSY		75.29			AMPA	1-640551-9
18	CIRCUIT ASSY		71.32			AMPA	1-640551-8
17	CIRCUIT ASSY		67.36			AMPA	1-640551-7
16	CIRCUIT ASSY		63.40			AMPA	1-640551-6
15	CIRCUIT ASSY		59.44			AMPA	1-640551-5
14	CIRCUIT ASSY		55.47			AMPA	1-640551-4
13	CIRCUIT ASSY		51.51			AMPA	1-640551-3
12	CIRCUIT ASSY		47.55			AMPA	1-640551-2
11	CIRCUIT ASSY		43.59			AMPA	1-640551-1
10	CIRCUIT ASSY		39.62			AMPA	1-640551-0
9	CIRCUIT ASSY		35.66			AMPA	640551-9
8	CIRCUIT ASSY		31.70			AMPA	640551-8
7	CIRCUIT ASSY		27.74			AMPA	640551-7
6	CIRCUIT ASSY		23.77			AMPA	640551-6
5	CIRCUIT ASSY		19.81			AMPA	640551-5
4	CIRCUIT ASSY		15.85			AMPA	640551-4
3	CIRCUIT ASSY		11.89			AMPA	640551-3
2	CIRCUIT ASSY		7.92			AMPA	640551-2

DO NOT SCALE PRINT.
 UNLESS SPECIFIED
 DIMENSIONS IN mm (INCHES)
 TOLERANCES ON:
 2 PLC DEC ±
 3 PLC DEC ±
 ANGLES ±
 MATERIAL
 POLYESTER, UL 94V-0
 NATURAL



FINISH	SCALE	SIZE	CAGE CODE	DRAWING NO
NATURAL	5:1	00779	640551	640551

COVER, MTA 156

AMPA
AMP Incorporated
Harrisburg, PA 17105-3608

640551