

7, 14 & 16-Segment LED Displays (Continued)

★ Web Code: PBW

Single Digit 14 & 16-Segment Alphanumeric LED Displays

Figure images on previous page

Part No.	Manufacturer	Product No.	Character Height	Illuminated Color	Bus Polarity*	Pins/Leads	Typical Vf @ If (mA)	Typical mcd @ mA	Wavelength nm	Decimal Point #	Pricing		
											1	10	100
2076703	Ligitek	LSD3E62-20/A	0.39"	Green	CA	16	2.1 @ 20	3.05 @ 10	565	RHDP	\$1.39	\$1.25	\$.95
2076691	Ligitek	LSD3E6SBKS-20/A	0.39"	Blue	CA	16	3.5 @ 20	7.2 @ 10	475	RHDP	2.95	2.49	1.95
308152	ValuePro	LA5041R-11BRRRN	0.50"	Orange	Alphanumeric	18	2.1 @ 20	7.4 @ 10	635	RHDP	.99	.89	.79
2125253	Kingbright	PSC05-11HWA	0.50"	Bright Red Gap	CC	18	2.0 @ 20	1.9 @ 10	700	RHDP	1.49	1.35	1.19

2-Digit 7-Segment Numeric LED Displays

Part No.	Manufacturer	Product No.	Character Height	Illuminated Color	Bus Polarity*	Pins/Leads	Typical Vf @ If (mA)	Typical mcd @ mA	Wavelength nm	Decimal Point #	Pricing		
											1	10	100
1955781	Lite-On	LTD-2701WC	0.28"	Red	CC	10	1.8 @ 20	3.1 @ 5	660	RHDP	\$.99	\$.89	\$.79
1955845	Lite-On	LTD-383E-R2	0.30"	Red Orange	CA	16	2.0 @ 20	1.6 @ 10	630	RHDP	.89	.75	.59
2075786	Ligitek	LDD4062-20/A	0.40"	Green	CA	16	2.1 @ 20	3.05 @ 10	565	RHDP	1.09	.89	.75
1955861	Lite-On	LTD-432GC	0.40"	Green	CC	16	2.1 @ 20	1.1 @ 10	565	No DP	.89	.75	.59
2005340	Lite-On	LTD-4608B	0.40"	Blue	CA	10	3.8 @ 20	3.6 @ 10	428	RHDP	1.95	1.59	1.25
24715	Ligitek	LDD5121-20/A	0.56"	Red	CA	18	2.1 @ 20	0.8 @ 20	697	RHDP	1.59	1.39	1.19
24723	Ligitek	LDD5111-11/A	0.56"	Red	CC	18	2.1 @ 20	0.8 @ 20	697	RHDP	1.59	1.39	1.19
24707	Ligitek	LDD5114-20/A	0.56"	Orange Red	CC	18	2.0 @ 20	2.4 @ 20	635	RHDP	1.59	1.39	1.19
200539	Arctic	ELD556YWA	0.56"	Yellow	CA	18	2.0 @ 20	1.9 @ 10	590	RHDP	.79	.69	.55
790022	Lite-On	LTD-6410AG	0.56"	Green	CA	18	2.1 @ 20	2.4 @ 10	565	RHDP	1.59	1.39	1.19
2005358	Lite-On	LTD-5623BG	0.56"	Green	CC	18	2.1 @ 20	2.4 @ 10	565	RHDP	1.95	1.75	1.49
2005366	Lite-On	LTD-6440G	0.56"	Green	CC	18	2.1 @ 20	2.4 @ 10	570	RHDP	.99	.89	.79
2075794	Ligitek	LDD512SBKS-20/A	0.56"	Blue	CA	18	3.5 @ 20	58 @ 10	475	RHDP	3.95	3.75	3.49

3-Digit 7-Segment Numeric LED Displays

Part No.	Manufacturer	Product No.	Character Height	Illuminated Color	Bus Polarity*	Pins/Leads	Typical Vf @ If (mA)	Typical mcd @ mA	Wavelength nm	Decimal Point #	Pricing		
											1	10	100
335055	ValuePro	UN4043-13 EWRS	0.40"	Orange	CA	12	2.1 @ 20	3.3 @ 10	635	RHDP	\$1.59	\$1.25	\$1.09
1956493	Lite-On	LTC561R	0.56"	Red	CA	12	1.7 @ 20	0.6 @ 10	665	RHDP	2.25	1.95	1.59
2125229	ValuePro	LN5643R-11	0.56"	Orange	CA	12	2.1 @ 20	4.5 @ 10	630	RHDP	.69	.59	.49
308224	ValuePro	LM5643R-11RRRN	0.56"	Orange	CC	12	2.1 @ 20	7.4 @ 20	630	RHDP	1.95	1.75	1.59
225963	ValuePro	KW3-562A2B	0.56"	Green	CA	28	2.2 @ 20	15 @ 20	568	RHDP	2.49	2.25	1.95

2-Digit 14 & 16-Segment Alphanumeric LED Displays

Part No.	Manufacturer	Product No.	Character Height	Illuminated Color	Bus Polarity*	Pins/Leads	Typical Vf @ If (mA)	Typical mcd @ mA	Wavelength nm	Decimal Point #	Pricing		
											1	10	100
2005382	Lite-On	LTP-4323P	0.40"	Bright Red	CC	20	2.1 @ 20	0.75 @ 10	697	RHDP	\$.89	\$.79	\$.69
2005391	Lite-On	LTP-4323JD	0.40"	AllnGap Hyper Red	CC	20	2.1 @ 20	0.65 @ 10	650	RHDP	.79	.69	.59
1955870	Lite-On	LTP-4323G	0.40"	Green	CC	20	2.1 @ 20	2.0 @ 10	569	RHDP	.79	.69	.59
1955896	Lite-On	LTP-3786S-03	0.54"	AlGaAs Red	CA	18	1.8 @ 20	4.0 @ 10	660	RHDP	.79	.69	.59
1955909	Lite-On	LTP-3785E-01	0.54"	Red Orange	CA	18	2.0 @ 20	2.0 @ 10	630	RHDP	.79	.69	.59
1955917	Lite-On	LTP-3785G-01	0.54"	Green	CA	18	2.1 @ 20	2.0 @ 10	565	RHDP	.79	.69	.59
335222	ValuePro	UA5422-11 EWRS	0.54"	Green	CA	18	2.1 @ 20	2.9 @ 10	567	RHDP	.89	.79	.69
2075807	Ligitek	LDD525SBKS-20/A	0.56"	Blue	CC	18	3.5 @ 20	10.5 @ 10	460	RHDP	3.95	3.75	3.49

4-Digit 7-Segment Numeric LED Displays

Part No.	Manufacturer	Product No.	Character Height	Illuminated Color	Bus Polarity*	Pins/Leads	Typical Vf @ If (mA)	Typical mcd @ mA	Wavelength nm	Decimal Point #	Pricing		
											1	10	100
2006810	Ligitek	LFD2121-20/A-PF	0.28"	Red	CA	12	2.1 @ 20	0.8 @ 10	697	RHDP	\$2.25	\$1.95	\$1.75
2006828	Ligitek	LFD4161-20/A-PF	0.40"	Red	CA	16	2.1 @ 20	0.8 @ 10	697	RHDP	1.95	1.75	1.49
2006836	Ligitek	LFD5221-20/A-PF	0.56"	Red	CA	12	2.1 @ 20	1.0 @ 10	697	RHDP	2.49	2.25	1.95
2005711	Lite-On	LTC-5653G-01	0.56"	Green	CA	12	2.1 @ 20	2.4 @ 10	565	RHDP	1.75	1.59	1.39
1956573	Lite-On	LTC-5848G	0.56"	Green	CA	36	2.1 @ 20	2.4 @ 10	565	RHDP##	1.59	1.35	1.19
335194	ValuePro	UM5624-11-EWRS	0.56"	Green	CC	12	2.1 @ 20	2.9 @ 10	567	RHDP	2.95	2.49	2.19
11360	Lite-On	LTC-5851Y	0.56"	Yellow	CA	36	2.1 @ 20	2.1 @ 10	585	RHDP##	1.29	.95	.79

* CA-Common Anode/CC-Common Cathode # LHDP-Left Hand Decimal Point / RHDP-Right Hand Decimal Point ## 1st & 2nd digits only † 16 segment \$ 14 segment

BEST SELLING HIGH OUTPUT LEDs

Part No.	Description	1	10
183222	Blue, water clear, 5mm	\$1.39	\$1.25
320531	White, water clear, 5mm	.99	.89

See pages 20-24 for complete selection of LEDs

RGB HIGH OUTPUT LEDs

Part No.	Description	1	10
2128500	Water clear, 5mm	\$1.95	\$1.75
2152163	Diffused (auto-blink) 10mm	1.79	1.59

* For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above

4 LEVELS OF SAVINGS

NAME BRANDS	HOUSE BRANDS	FACTORY OVERRUN	DOLLAR SALE
-------------	--------------	-----------------	-------------

Order by Phone at 1-800-831-4242 or Online at www.Jameco.com