

# Heat Guns & Soldering Equipment

3 LEVELS OF SAVINGS  
 NAME BRANDS HOUSE BRANDS SPECIAL BUY



## Glue Gun and Glue Sticks

- Adheres to PCBs, cardboard, wires, metal and cloth
- Silicon nozzle
- Electronic heating
- Trigger action
- Utilizes 100mm long gluesticks (2 sticks included) • Size: 7.3"L x 6.3"W



Part No.	Description	1	5	25
72696	Glue gun .....	\$7.49	\$6.95	\$6.49
78633	Glue sticks (6/pk) .....	2.75	2.25	1.95



## 16 to 30-Watt Variable Soldering Iron & Stand

- 116572: Length: 7.5"
- 36329: • Black anodized steelbase – 5.3"L x 3.3"W
- See below for replacement sponge (P/N 134631)
- Fits most soldering irons .85" dia.



**Includes:** Sponge

Part No.	Description	1	5	25
116572	258VL soldering iron ...	\$19.95	\$17.95	\$15.95
36329	Soldering stand .....	5.95	5.39	4.79
134631	Sponge (for P/N 36329) .....	2.95	2.59	2.29

## Weller® 18-Watt Pro Series Soldering Iron

- Heats up to working temperature in just 35 seconds
- Up to 900°F temperature
- Co-molded grip for a comfortable feel
- Performance equivalent to a 60 watt iron
- Designed be self-standing, no stand is needed
- Tips use a phono jack and plug for easy tip exchange • UL and CUL listed
- Ideal for hobbies, kits, radios and electronics



**Includes:** Charger and WPS10 soldering tip

Part No.	Mfr. Part No.	Description	1	5
2153810	WPS18MP	18-watt iron .....	\$31.95	\$29.95
2158637	WPS11	0.03125" chisel tip ...	9.95	8.95
2158629	WPS10	0.03125" conical tip ...	9.95	8.95

## Weller® 20-Watt Soldering Iron

A high-quality, mains-powered soldering iron for general purposes.

- Power supply: 20W/110VAC
- UL approved
- Cord length: 5 feet



**Includes:** Iron stand

Part No.	Mfr. Part No.	1	5
2131151	VTS20U	\$7.95	\$7.49



## 25-Watt Thermally Balanced Soldering Iron

The XY200GX is a thermally balanced soldering iron for the professional or hobbyist.

- 120VAC; 6' cord • UL listed
- 25-watt power consumption
- Interchangeable tips (pg 127)
- Length: 8.0"
- One-year warranty



**Includes:** 1.6mm conical tip

Part No.	Mfr. Part No.	1	5	25
129040	200GX-25W	\$13.95	\$12.49	\$11.49



## Heat Guns and Strippers

All Master® products are made in the US from superior quality materials and the finest craftsmanship. Heat guns are ideally suited for drying, heating, welding, shrinking, soldering, desoldering and many other applications where heat is required.

191943: • 3-pos. switch (hot/off/cool)



\* Web Code: QAJ



Part No.	Mfr.	Product No.	Description	Watts	Heat Setting (°F)	Temp. (°F max.)	1	5
2117413	NTE	HG300-D	Mini heat gun	350	482-662	662	\$24.95	\$22.49
254925	BenchPro	1001A	Economical heat gun	1200	600 & 1000	1000	42.95	39.95
76865	BenchPro	G1HG1	Heat gun/stripper	1500	600 & 1100	1100	46.95	44.95
191943	Weller	6996C	Industrial heat gun	250	750-800	800	139.95	134.95
2007062	BenchPro	1004	Accessory kit for P/N 254925	—	—	—	9.95	8.95

## Weller® 25 & 35-Watt High-Quality Soldering Irons

- 120VAC @ 60Hz
  - Interchangeable heater elements
  - Lightweight handle with cushioned grip
  - Quick change knurled collar • Length: 9"
- Includes:** Power cord & ST3 tip (pg 125)



Part No.	Mfr. Part No.	Description	1	5
170587	WP25	25W solder iron ..	\$44.95	\$41.95
192102	WP35	35W solder iron ....	54.95	52.49
146608	ST1	Screwdriver tip 1/16"	4.95	4.49
146616	ST3	Screwdriver tip 1/8"	5.95	5.49
192145	ST6	Screwdriver tip .031"	5.95	5.39
146624	ST7	Conical tip 1/32"	5.95	5.39

## 35-Watt Soldering Iron

A high quality, mains powered soldering iron for general purposes.

- 110-120VAC
- 35-watt
- Long life tip
- Cord length: 5'
- 5' solder tube
- UL/CUL approved



Part No.	Mfr. Part No.	1	5	25
2228367	CL-1	\$9.95	\$8.95	\$7.95

\* Soldering Stands — Enter Web Code YAU

## Weller® LED Soldering Irons

- 3 high-temperature LEDs with 25 lumen light intensity
- Each iron includes soldering aid tool, tip and user's manual
- 2174901/2174928 includes soldering aid tool, lead-free solder and 2 spare soldering tips

Part No.	Mfr. Part No.	Description	1	5
2174901	SP25NKUS	25W soldering iron kit .....	\$20.95	\$18.95
2174936	SP40NUS	40W soldering iron .....	19.95	18.95
2174928	SP40NKUS	40W soldering iron kit .....	23.95	21.95
2174944	SP80NUS	80W soldering iron .....	26.95	24.95

## LEARN TO SOLDER KITS

Learning to solder might seem like a daunting process, but with the detailed manual you'll get a background on the tools and suggested best practices for setting up soldering equipment as well as some "do's and don'ts" while soldering. You'll be surprised how easy it can be.

Part No.	Mfr. Part No.	Description	Price
2161617	SP-1A	Make a siren kit, age 12+ (kit only) .....	\$10.95
2124218	AK-100	Make a siren, age 12+, (kit with 25W iron and cutter) .....	18.95
2175541	EDU03U	2 mini LED kits with iron, solder and cutter .....	39.95



## 40 & 60W High-Performance, Economical Soldering Irons

- Iron length: 9"
- 120VAC; 6' cord with 3-prong plug
- High-performance double-wound nichrome heating element
- Flexible, burn-resistant silicon cable



Part No.	Description	1	5	25
224602	40W soldering iron .....	\$11.95	\$10.95	\$9.95
195223	60W soldering iron .....	12.95	11.49	10.49
226018	Conical tip for P/N 224602 ...	2.95	2.75	2.49

## 60-Watt Replacement Soldering Iron

- Compatible with the following XYtronic soldering stations: 168-3C, 168-3CD, 9-60A and 9-60D.



Part No.	Mfr. Part No.	1	5
2144649	XY-207ESD	\$39.95	\$35.95

## Stand for Solder Irons

Safely rest hot irons on the stand to prevent burning your work surface.



- Perfect for pencil irons
- 1.93" diameter x 1.2" tall (max.)

Part No.	Mfr. Part No.	1	10	100
2237992	27A1040406	\$ .99	\$ .89	\$ .79

\* Soldering Irons — Enter Web Code QAS

Test/Tools