

# Rocker Switches

3 LEVELS OF SAVINGS  
 NAME BRANDS HOUSE BRANDS SPECIAL BUY



JAMECO ValuePro

## Standard Appliance Panel Mount Rocker Switches (Cont.)

See page 65 for figures

Web Code: VBU

| Part No. | Mfr. | Product No.             | Fig. | Pins | Contact Form<br>( ) Momentary | Contact Rating<br>(A @ VAC) | Dimensions<br>(L" x W" x D") | Lead Space |     | Rocker Color   | Terminal Type       | Pricing |        |        |
|----------|------|-------------------------|------|------|-------------------------------|-----------------------------|------------------------------|------------|-----|----------------|---------------------|---------|--------|--------|
|          |      |                         |      |      |                               |                             |                              | A"         | B"  |                |                     | 1       | 10     | 100    |
| 2267239  | MSW  | 103-7048-EV             | 12   | 3    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.0 x .43 x 1.0              | .43        | —   | Green illum.   | .250" quick connect | \$ 2.95 | \$2.59 | \$2.29 |
| 2267247  | MSW  | 103-7049-EV             | 12   | 3    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.0 x .43 x 1.0              | .43        | —   | Orange illum.  | .250" quick connect | 1.95    | 1.75   | 1.49   |
| 2267255  | MSW  | 103-7050-EV             | 12   | 3    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.0 x .43 x 1.0              | .43        | —   | Red illum.     | .250" quick connect | 1.95    | 1.75   | 1.49   |
| 2267263  | MSW  | 103-7051-EV             | 11   | 2    | SPST on-off                   | 16 @ 125 & 10 @ 250         | .84 Dia. x .80               | .28        | —   | Black          | .187" quick connect | .79     | .69    | .59    |
| 2267271  | MSW  | 103-7052-EV             | 11   | 3    | SPST on-off                   | 16 @ 125 & 10 @ 250         | .84 Dia. x .80               | .28        | —   | Orange illum.  | .187" quick connect | 1.09    | .99    | .85    |
| 2267279  | MSW  | 103-7053-EV             | 11   | 3    | SPST on-off                   | 16 @ 125 & 10 @ 250         | .84 Dia. x .80               | .28        | —   | Red illum.     | .187" quick connect | 1.09    | .99    | .85    |
| 2267287  | MSW  | 103-7055-EV             | 11   | 3    | SPST on-off                   | 16 @ 125 & 10 @ 250         | .84 Dia. x .80               | .28        | —   | Green illum.   | .187" quick connect | 1.09    | .99    | .85    |
| 2267295  | MSW  | 103-7056-EV             | 11   | 3    | SPST on-off                   | 16 @ 125 & 10 @ 250         | .84 Dia. x .80               | .28        | —   | Red illum.     | .187" quick connect | 1.49    | 1.25   | 1.09   |
| 2267519  | MSW  | 103-R13-112LP-02Y-E     | 17   | 4    | SPST on-off                   | 16 @ 125 & 10 @ 250         | .80 Dia. x .89               | —          | .28 | Yellow illum.  | .187" quick connect | 2.95    | 2.59   | 2.29   |
| 2267335  | MSW  | 103-7063-EV             | 18   | 2    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.4 x .69 x .96              | —          | .38 | Black          | .250" quick connect | 1.25    | 1.09   | .99    |
| 2267343  | MSW  | 103-7063-EVX            | 18   | 2    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.4 x .69 x .96              | —          | .39 | Black          | .250" quick connect | 1.25    | 1.09   | .99    |
| 2268007  | MSW  | 103-7081-EV             | 5    | 2    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.2 x .43 x 1.1              | —          | .34 | Black          | .250" quick connect | 1.25    | 1.09   | .99    |
| 2267351  | MSW  | 103-7064-EV             | 18   | 3    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.4 x .69 x .96              | —          | .18 | Red illum.     | .250" quick connect | 1.49    | 1.25   | 1.09   |
| 2267359  | MSW  | 103-7065-EV             | 18   | 3    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.4 x .69 x .96              | —          | .39 | Red illum.     | .250" quick connect | 1.49    | 1.25   | 1.09   |
| 2267399  | MSW  | 103-7075-EV             | 19   | 6    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.0 x .87 x 1.13             | .43        | .43 | Red/Red illum. | .250" quick connect | 2.95    | 2.59   | 2.29   |
| 2267407  | MSW  | 103-7076-EV             | 20   | 5    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.0 x .87 x 1.13             | .43        | .43 | Yellow illum.  | .250" quick connect | 3.95    | 3.59   | 3.29   |
| 2267447  | MSW  | 103-7082-EV             | 12   | 3    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.0 x .43 x 1.08             | —          | .34 | Red illum.     | .250" quick connect | 1.95    | 1.75   | 1.49   |
| 2267455  | MSW  | 103-7083-EV             | 12   | 3    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.0 x .43 x 1.08             | —          | .34 | Yellow illum.  | .250" quick connect | 1.95    | 1.75   | 1.49   |
| 2267463  | MSW  | 103-7084-EV             | 12   | 3    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.0 x .43 x 1.08             | —          | .34 | Green illum.   | .250" quick connect | 1.95    | 1.75   | 1.49   |
| 2267471  | MSW  | 103-R13-91A-EV          | 12   | 2    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.0 x .43 x 1.1              | —          | .42 | Black          | .250" quick connect | 1.25    | 1.09   | .99    |
| 2267487  | MSW  | 103-R13-205B-01R-EV     | 6    | 3    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.2 x .73 x 1.22             | —          | .37 | Red illum.     | .250" quick connect | 1.95    | 1.75   | 1.49   |
| 2267999  | MSW  | 103-R13-205L-01G-EV     | 6    | 4    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.2 x .73 x 1.22             | —          | .36 | Green illum.   | .250" quick connect | 1.95    | 1.75   | 1.49   |
| 2267527  | MSW  | 103-R13-205A2-01-EV     | 6    | 2    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.2 x .73 x 1.22             | —          | .36 | Black/Red      | .250" quick connect | 1.95    | 1.75   | 1.49   |
| 2267551  | MSW  | 103-R13-238A-01W-EV     | 15   | 2    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.1 x .54 x 1.1              | —          | .37 | White illum.   | .250" quick connect | 1.95    | 1.75   | 1.49   |
| 2267559  | MSW  | 103-R13-238B-01G-EV     | 15   | 3    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.1 x .54 x 1.1              | —          | .37 | Green illum.   | .250" quick connect | 1.95    | 1.75   | 1.49   |
| 2267567  | MSW  | 103-R13-238B-01R-EV     | 15   | 3    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.1 x .54 x 1.1              | —          | .37 | Red illum.     | .250" quick connect | 1.95    | 1.75   | 1.49   |
| 2268023  | MSW  | 103-7047-EV             | 5    | 3    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.1 x .43 x 1.0              | —          | .43 | Red illum.     | .250" quick connect | 2.49    | 2.25   | 1.95   |
| 2268039  | JVP  | R13-66L-02-BBGG-L1      | 6    | 4    | SPST on-off                   | 16 @ 125 & 10 @ 250         | .73 x .51 x .74              | —          | .36 | Green illum.   | Solder lugs         | 1.95    | 1.75   | 1.49   |
| 2268207  | MSW  | 103-R13-205L-01R-EV     | 14   | 4    | SPST on-off                   | 16 @ 125 & 10 @ 250         | 1.1 x .54 x 1.2              | .37        | —   | Black          | .250" quick connect | 1.95    | 1.75   | 1.49   |
| 2182389  | ARN  | 160112E                 | 6    | 2    | SPST (on)-off                 | 6 @ 125 & 16 @ 250          | 1.0 x .48 x .98              | .38        | .38 | White          | .250" quick connect | .69     | .59    | .49    |
| 2269815  | JVP  | R13-213C-03-B           | 1    | 3    | SPDT on-on                    | 6 @ 125 & 3 @ 250           | .48 x .43 x .65              | —          | .13 | Black          | .110" quick connect | 1.49    | 1.25   | 1.09   |
| 2178566  | CWI  | GRS-4012-0050           | 14   | 3    | SPDT on-on                    | 8 @ 125 & 4 @ 250           | .74 x .50 x .46              | .22        | —   | Red            | .187" quick connect | 1.75    | 1.49   | 1.25   |
| 2267191  | MSW  | 103-7037-EV             | 12   | 3    | SPDT on-on                    | 10 @ 125 & 6 @ 250          | 1.2 x .55 x .95              | .39        | .90 | Black          | .250" quick connect | 1.95    | 1.75   | 1.49   |
| 2269783  | JVP  | 112-R13-136C-05-B       | 21   | 3    | SPDT on-on                    | 10 @ 125 & 6 @ 250          | .71 Dia. x .62 (T)           | .21        | .20 | Black          | Solder lugs         | 1.49    | 1.25   | 1.09   |
| 2268303  | JVP  | R13-136C-05-BB          | 21   | 3    | SPDT on-on                    | 10 @ 125 & 6 @ 250          | .72 Dia. x .76               | —          | .18 | Black          | Solder lugs         | 2.25    | 1.95   | 1.75   |
| 2268319  | JVP  | R13-136C-05-BR          | 21   | 3    | SPDT on-on                    | 10 @ 125 & 6 @ 250          | .72 Dia. x .76               | —          | .18 | Red            | Solder lugs         | 2.25    | 1.95   | 1.75   |
| 2268151  | MSW  | R13-228C-05-BB          | 1    | 3    | SPDT on-on                    | 10 @ 125 & 6 @ 250          | 1.1 x .71 x .67              | —          | .21 | Black          | Solder lugs         | 2.95    | 2.59   | 2.29   |
| 2267479  | MSW  | 103-R13-135C-02-EV      | 4    | 3    | SPDT on-on                    | 16 @ 125 & 10 @ 250         | .80 x .73 x .57              | .28        | .28 | Black          | .187" quick connect | 2.25    | 1.95   | 1.75   |
| 2267391  | MSW  | 103-7074-EVX            | 20   | 5    | SPDT on-on                    | 16 @ 125 & 10 @ 250         | 1.0 x .87 x 1.13             | .43        | .43 | Yellow illum.  | .250" quick connect | 2.95    | 2.59   | 2.29   |
| 2267671  | MSW  | R-13-1238-C-01          | 15   | 3    | SPDT on-on                    | 16 @ 125 & 10 @ 250         | 1.3 x .50 x 1.1              | —          | .36 | White          | .250" quick connect | 1.95    | 1.75   | 1.49   |
| 2267575  | MSW  | 103-R13-238C-01B-EV     | 15   | 3    | SPDT on-on                    | 16 @ 125 & 10 @ 250         | 1.1 x .54 x 1.1              | —          | .37 | Black          | .250" quick connect | 1.95    | 1.75   | 1.49   |
| 2267583  | MSW  | 103-R13-238C-01W-EV     | 15   | 3    | SPDT on-on                    | 16 @ 125 & 10 @ 250         | 1.1 x .54 x 1.1              | —          | .37 | White          | .250" quick connect | 1.95    | 1.75   | 1.49   |
| 2267383  | MSW  | 103-7073-EV             | 19   | 6    | SPDT on-on                    | 16 @ 125 & 10 @ 250         | 1.0 x .87 x 1.13             | .43        | .43 | Black/Black    | .250" quick connect | 2.95    | 2.59   | 2.29   |
| 2268167  | JVP  | R13-66C-10-BBNN         | 6    | 3    | SPDT on-on                    | 16 @ 125 & 10 @ 250         | .71 x .51 x .74              | —          | .28 | Red            | PC right angle      | 1.95    | 1.75   | 1.49   |
| 2268183  | MSW  | 103-R13-205C3-01-EV     | 12   | 3    | SPDT on-on                    | 16 @ 125 & 10 @ 250         | 1.1 x .54 x 1.2              | —          | .28 | Black          | .250" quick connect | 1.75    | 1.49   | 1.25   |
| 2267167  | MSW  | 103-7032-EVX            | 22   | 3    | SPDT on-off-on                | .4VA @ 20VAC/VDC            | .32 x .30 x .22              | .20        | —   | Black          | SMD                 | 1.95    | 1.75   | 1.49   |
| 2267175  | MSW  | 103-7034-EVX            | 22   | 3    | SPDT on-off-on                | .4VA @ 20VAC/VDC            | .32 x .30 x .22              | .20        | —   | Black          | SMD                 | 1.95    | 1.75   | 1.49   |
| 2267159  | MSW  | 103-7027-EVX            | 23   | 3    | SPDT on-off-on                | 3 @ 120 & 1 @ 250           | .32 x .22 x .25              | 1.2        | .10 | Black          | PC right angle      | 3.95    | 3.59   | 3.29   |
| 2267103  | MSW  | 103-7017-EVX            | 24   | 3    | SPDT on-off-on                | 5 @ 120 & 2 @ 250           | .50 x .26 x .57              | .185       | —   | Black          | Solder lugs         | 2.49    | 2.25   | 1.95   |
| 2267047  | MSW  | 103-7009-EVX            | 25   | 3    | SPDT on-off-on                | 5 @ 120 & 2 @ 250           | .50 x .27 x .45              | .20        | .15 | Black - Paddle | PC right angle      | 2.49    | 2.25   | 1.95   |
| 2182418  | DIA  | 570-12574-1212-0104-007 | 26   | 3    | SPDT on-off-on                | 5 @ 125 & 2 @ 250           | .50 x .28 x .37              | —          | .19 | Black          | PC terminal         | .49     | .39    | .35    |
| 2268159  | JVP  | R13-241D05BB            | 7    | 3    | SPDT on-off-on                | 6 @ 125 & 3 @ 250           | .59 x .54 x .76              | .185       | —   | Black          | Solder lugs         | 2.49    | 2.25   | 1.95   |
| 2267543  | MSW  | 103-R13-211D-02-EV      | 13   | 3    | SPDT on-off-on                | 10 @ 125 & 6 @ 250          | .76 x .51 x .74              | —          | .28 | Black          | .187" quick connect | 1.49    | 1.25   | 1.09   |
| 2267367  | MSW  | 103-7066-EVX            | 16   | 5    | SPDT on-off-on                | 12 @ 125 & 10 @ 277         | 1.45 x .75 x 1.81            | .60        | .47 | Red            | .250" quick connect | 1.49    | 1.25   | 1.09   |
| 316072   | JVP  | R13-66D-02              | 6    | 3    | SPDT on-off-on                | 16 @ 125 & 10 @ 250         | .83 x .59 x .47              | .31        | .31 | Black          | .187" quick connect | 1.49    | 1.25   | 1.09   |
| 2267591  | MSW  | 103-R13-238D-01B-EV     | 15   | 3    | SPDT on-off-on                | 16 @ 125 & 10 @ 250         | 1.1 x .54 x 1.1              | —          | .35 | Black          | .250" quick connect | 1.95    | 1.75   | 1.49   |
| 2267495  | MSW  | 103-R13-205D3-01-EV     | 5    | 3    | SPDT on-off-on                | 16 @ 125 & 10 @ 250         | 1.2 x .73 x 1.22             | —          | .36 | Black          | .250" quick connect | 1.09    | .99    | .85    |
| 2268215  | MSW  | 103-R13-238D-01W-EV     | 15   | 3    | SPDT on-off-on                | 16 @ 125 & 10 @ 250         | 1.0 x .50 x 1.1              | —          | .35 | White illum.   | .250" quick connect | 1.95    | 1.75   | 1.49   |
| 1945241  | ITW  | 163-099-029             | 12   | 3    | SPDT on-off-on                | 16 @ 125 & 12 @ 250         | 1.2 x .55 x .59              | .26        | .26 | Black          | .250" quick connect | 1.75    | 1.49   | 1.25   |

\* ALC = Alcoswitch | ARN = Arndt | CWI = CW Industries | DIA = Dialight | ITW = Illinois Tool | JVP = Jameco ValuePro | MSW = Mountain Switch