



[Click Here to Request a Large Quantity Quote](#)

[AC Tubeaxial Fans](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Voltage Rating AC	Height - mm	Width - mm	Depth - mm	Air Flow (CFM)	Bearing	Current (mA)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1
213867	Fulltech Electric	UF-60D11HBWH-R	115	60	60	30	10.2	Ball	35	UL/CUL/VDE/CE	28	12	\$15.95
2290351	Common Wealth	FP-108AX(S-2)120BW	115	80	80	25	18	Ball	100	UL/CSA	29	12"	\$13.95
2231734	ADDA Corporation	AA8251HB-AT	115	80	80	25	21	Ball	70	UL/CUL/TUV/CE	27	Terminals	\$12.95
146078	Common Wealth	FP-108AX(S-1)120BW	115	80	80	25	23	Ball	140	UL/CE	29	12"	\$15.95
2230660	Thermocool Fans	G8025HAS	115	80	80	25	23	Sleeve	160	UL/CUL/TUV/CE	32	12"	\$10.95
2290343	Common Wealth	FP-108AX(S-1)120SW	115	80	80	25	23	Sleeve	170	UL/CSA	33	12"	\$12.95
2290359	Common Wealth	FP-108AX(S-1)120SW-14	115	80	80	25	23	Sleeve	170	UL/CSA	33	15" (14 AWG)	\$13.95
300557	Fulltech Electric	UF80B11SWH-R	115	80	80	25	24	Sleeve	140	UL/CUL/TUV/CE	35	12"	\$13.95
2133819	ADDA Corporation	AA8381MS-AT	115	80	80	38	24	Sleeve	75	UL/CUL/TUV/CE	26.2	Terminals	\$10.95
2228279	Mechatronics	80A12BWL	115	80	80	38	25	Ball	100	UL/CSA/CE	32	11"	\$12.95
300600	Fulltech Electric	UF80A11BWH-R	115	80	80	38	29	Ball	120	UL/CUL/TUV/CE	36	12"	\$14.95
2290375	Common Wealth	FP-108A(S-1)120BT*	115	80	80	38	30	Ball	120	UL/CSA/CE	35	72" with AC power plug	\$15.95
300389	Fulltech Electric	UF80A11BTH-R	115	80	80	38	30	Ball	120	UL/CUL/TUV/CE	36	Terminals	\$14.95
303467	Sunon	SF11592A-1092HBL-GN	115	92	92	25	37	Ball	110	UL/CSA/TUV/CE	40	12"	\$19.95
2271255	Common Wealth	FP-108JC(S-1)120BW	115	92	92	38	45	Ball	150	UL/CSA/CE	37	12" w/ 2P connector	\$14.95
2135275	Common Wealth	FP-108JC(S-1)120SW	115	92	92	38	45	Sleeve	150	UL/CSA/CE	37	12"	\$14.95
124063	Sunon	SP101AT1122HBT-R	115	120	120	25	78	Ball	180	CSA/TUV/CE	46	Terminals	\$16.95
1810048	Sunon	SP101AT1122HBL.GN	115	120	120	25	78	Ball	210	UL/CUL/TUV/CE	46	12"	\$16.95
2290383	Common Wealth	FP-108-1(S-3)120BT	115	120	120	38	54	Ball	110	UL/CSA/CE	34	Terminals	\$13.95
2230379	EBM Papst	4800N	115	120	120	38	57.1	Sleeve	78	UL/CSA/CE	32	Terminals	\$11.95
303361	Fulltech Electric	UF12A11BTL1-R	115	120	120	38	64	Ball	200	UL/CSA/TUV/CE	37	Terminals	\$15.95
2290391	Common Wealth	FP-108-1(S-2)120BT	115	120	120	38	71	Ball	120	UL/CSA/CE	39	Terminals	\$14.95
2231718	Sunon	SP102A-1123MBL.GN	115	120	120	38	88	Ball	160	UL/CUL/TUV/CE	40	12"	\$17.95
2230686	Thermocool Fans	G12038HAS	115	120	120	38	95	Sleeve	0.34	UL/CUL/TUV	122	Terminals	\$14.95

Jameco Part #	Manufacturer	Manufacturer Part #	Voltage Rating AC	Height - mm	Width - mm	Depth - mm	Air Flow (CFM)	Bearing	Current (mA)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1
2290399	Common Wealth	FP-108-1(S-1)120BW	115	120	120	38	105	Ball	180	UL/CSA/CE	47	12"	\$13.95
16935	Common Wealth	FP108-1(S1)120BT*	115	120	120	38	105	Ball	240	UL/CSA	47	Terminals	\$12.95
2125931	Common Wealth	FP-108-1(S-1)120BT	115	120	120	38	105	Ball	250	UL/CSA/TUV/CE	45	Terminals	\$13.95
106586	Common Wealth	FP-108-1(S-1)120ST	115	120	120	38	105	Sleeve	180	UL/CSA/CE	47	Terminals	\$12.95
1707163	Sunon	SP101A-1123HBL-GN	115	120	120	38	107	Ball	180	UL/CSA/TUV	50	12"	\$17.95
2067444	Sunon	SP101A-1123HBT.GN	115	120	120	38	108	Ball	180	UL/CUL/TUV/CE	50	Terminals	\$16.95
2292407	Sunon	SP100A-1123XST.GN	115	120	120	38	115	Sleeve	240	UL/CSA/TUV/CE	49	Terminals	\$13.95
2231726	Sunon	SP100A-1123XBL.GN	115	120	120	38	117	Ball	240	UL/CUL/TUV/CE	50	12"	\$16.95
102884	Sunon	SP100A-1123XBT.GN	115	120	120	38	117	Ball	240	UL/CUL/TUV/CE	50	Terminals	\$14.95
2290479	Common Wealth	EP-108-1(ULTRA)120TB	115	120	120	38	120	Ball	240	UL/CSA/CE	47	Terminals	\$14.95
2290367	Common Wealth	FP-108-7(S-1)120BT	115	127	127	38	140	Ball	240	UL/CSA/TUV/CE	47	Terminals	\$19.95
2290295	Common Wealth	FP-108CX(120BW)	115	150	150	38	140	Ball	260	UL/CUL	31	8"	\$29.95
2290319	Common Wealth	FP-108EXM(120BW)	115	172	150	38	230	Ball	400	UL/CUL/TUV/CE	49	16"	\$29.95
2271263	Common Wealth	FP-108EX(S-2)120BW	115	172	150	51	170	Ball	370	UL/CSA/CE	33	12"	\$19.95
212582	Fulltech Electric	UF15PC11BWH-R	115	172	150	51	226	Ball	250	UL/CUL/TUV/CE	58	12" wires	\$29.95
189684	Fulltech Electric	UF15PC11BTH	115	172	150	51	226	Ball	250	UL/CUL/TUV/CE	58	Terminals	\$32.95
2306615	Orion Fans	OA172AP11-1TBXC	115	172	150	51	300	Ball		UL/CUL	61	Terminals	\$29.95
2230723	Thermocool Fans	G17050HASB	115	172	172	51	198	Ball	400	UL/CUL/TUV/CE/CCC	59	Terminals	\$27.95
2290287	Common Wealth	FP-108K(S-1)120BW	115	220	220	60	360	Ball	700	TUV, CE	56	12"	\$29.95
2298119	Orion Fans	OA109AP-11/22-3WB	115/220	120	120	38	51	Ball	67	UL, CUL, CE	25	(4) 12"	\$17.95
2258419	Fulltech Electric	UF-12A12/23-BWH	115/220	120	120	38	92	Ball	260	UL/CUL/TUV/CE	42	(4) 12"	\$16.95
2230117	ADDA Corporation	AA8252HB-AT	220	80	80	25	17	Ball	60	UL/CUL/CE/TUV	27.8	Terminals	\$14.95
355630	Fulltech Electric	UF-80A23-BTH-R	220	80	80	38	30	Ball	60	UL/CSA/VDE/CE	36	Terminals	\$13.95
100918	Sunon	SF23080A/2083HSL.GN	220	80	80	38	30	Sleeve	60	UL/CSA/CE/TUV	35	12"	\$17.95
2210837	Comair Rotron	SU3G1	220	80	80	38	32	Sleeve	70	UL/CSA	39	12"	\$9.95
2234177	NMB Technologies	3115FS-23T-B10-A00	220	80	80	38	33	Ball	87	UL/CSA	36	Terminals	\$12.95
2306527	Qualtek	FAA1-09225QBMT31	220	92	92	25	30.5	Ball	150	UL/CSA/TUV/CE	28	Terminals	\$15.95
2231566	ADDA Corporation	AA1252MB-AT	220	120	120	25	65	Ball	100	UL/CUL/TUV/CE	38	Terminals	\$14.95
2290415	Common Wealth	FP-108-1(S-1)220BT	220	120	120	38	105	Ball	110	UL/CSA/CE	47	Terminals	\$14.95
2290423	Common Wealth	FP-108-1(S-1)220BW	220	120	120	38	105	Ball	110	UL/CSA/TUV/CE	47	38"	\$14.95
2290407	Common Wealth	FP-108-1(S-1)220ST	220	120	120	38	105	Sleeve	110	UL/CSA/CE	47	Terminals	\$13.95
2271015	ADDA Corporation	AA1282US-AT(CF)	220	120	120	38	107	Sleeve	170	UL/CUL/TUV/CE	46	Terminals	\$14.95

Jameco Part #	Manufacturer	Manufacturer Part #	Voltage Rating AC	Height - mm	Width - mm	Depth - mm	Air Flow (CFM)	Bearing	Current (mA)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1
2293511	Thermactive Electronics	RAH1238B1	220	120	120	38	111	Ball	20	UL/CSA/TUV/CE	44	12"	\$12.95
303459	Sunon	DP200A-2123XBL.GN	220	120	120	38	117	Ball	120	UL/CSA/TUV/CE	50	12"	\$17.95
102892	Sunon	DP200A-2123XBT-R	220	120	120	38	117	Ball	140	UL/CSA/TUV	50	Terminals	\$17.95
2265879	Orion Fans	OA172SAP-22-1TB	220	172	150	51	235	Ball	230	UL/CUL/TUV/CE	52	Terminals	\$24.95
2292615	Thermactive Electronics	RAH1751B1-C-T	220	172	150	51	250	Ball	200	UL/CUL/TUV/CE	56	Terminals	\$24.95
2293503	Thermactive Electronics	RAH1751B1	220	172	150	51	250	Ball	200	UL/CUL/TUV/CE/VDE	56	12"	\$24.95