



[Click Here to Request a Large Quantity Quote](#)

[Relays-General Purpose](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Contact Form	Coil Voltage	Contact Rating	Coil Resistance (ohms)	Coil Current	Mating Socket (Standard)	Mating Socket (DIN Rail)	Price 1
2288351	Major Brands	MT326127(9-1415013-1)	3PDT	127VAC	10A@250VAC	2000	17 mA	P/N: 187602	P/N: 187602	\$9.95
2288359	Major Brands	RH4B-ULDC12V	4PDT	12VDC	10A@110VAC	96	125 mA	SH4B-51 or SH4B-62	SH4B-05 or SH4B-05C	\$11.95
291507	Jameco Valuepro	LB4H-12DS-R	4PDT	12VDC	5A@30VDC , 5A@240VAC	160	75 mA	P/N: 175557	P/N: 175557	\$4.95
2302391	Omron	MY4E-AC24	4PDT	24VAC	5A@220VAC, 5A@24VDC	180	46 mA	P/N: 175557	P/N: 175557	\$14.95
175602	Rayex Electronics	LB4H-24DS-R	4PDT	24VDC	5A@30VDC , 5A@240VAC	650	37 mA	P/N: 175557	P/N: 175557	\$5.49
2218214	Omron	LY2-UA-006244	DPDT	110/120VAC	10A@24VDC, 10A@110VAC	4430	9.9 mA/10.8 mA	n/a	P/N: 175531	\$4.95
2283359	Rayex Electronics	LB2H-110AS	DPDT	110VAC	10A@30VDC, 10A@240VAC	3900	10 A	P/N: 175531	P/N: 282191	\$4.95
175573	Jameco Valuepro	LB2-110A-S-R	DPDT	110VAC	12A@30VDC, 12A@240VAC	3900	28 mA	P/N: 175531	P/N: 282191	\$5.49
2273199	Guardian	1225-2C-11DC	DPDT	110VDC	10A@110VDC	6500	10 A	n/a	n/a	\$44.95
2295703	Omron	LY2-DC100/110	DPDT	110VDC	10A@125VDC, 10A@250VAC	11000	10 mA	P/N: 175531	P/N: 282191	\$8.95
2224112	Picker Components	PC703-2C-M-120VAC	DPDT	120VAC	10A@28VDC, 5A@240VAC	2250	29.8 mA	P/N: 282132	P/N: 141145	\$4.95
282247	TE Connectivity	K10P-11A15-120	DPDT	120VAC	15A@30VDC, 15A@120VAC	3900	11 mA	P/N: 282191	P/N: 282191	\$19.95
2231494	Jameco Valuepro	LB2H-12DS	DPDT	12VDC	10A@24VDC, 10A@240VAC	160	75 mA	P/N: 175557	P/N: 175557	\$5.95
172719	Rayex Electronics	LB2-12DS-R	DPDT	12VDC	12A@30VDC, 12A@240VAC	160	75 mA	P/N: 175531	P/N: 282191	\$6.15
2304879	Omron	G2R-2-DC12	DPDT	12VDC	5A@250VAC/30VDC	275	5 A	n/a	n/a	\$4.95
175565	Rayex Electronics	LB2-24D-S-R	DPDT	24VDC	12A@30VDC, 12A@240VAC	650	37 mA	P/N: 175531	P/N: 282191	\$5.95
2289527	Jameco Valuepro	SS6262Y	SPDT	120VAC	28VDC		5 mA	n/a	n/a	\$7.95
2278799	Keystudio	KS0011	SPDT	5VDC	10A@125VAC	70	71.4 mA	n/a	n/a	\$4.50