



[Click Here to Request a Large Quantity Quote](#)

[Circuit Protection-Varistors](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Continuous AC Voltage (Vm)	Continuous DC Voltage (Vm)	Transient Energy (J)	Clamping Voltage (V)	Clamping Current (A)	Maximum Surge Current	Lead Style	Price 1
2280847	Littelfuse	V12ZT05P	6	8	0.14	37	1	50	Radial	\$0.39
2285479	Littelfuse	V18ZA3P	10	14	3.5	36	10	1000	Radial	\$0.59
1990739	Panasonic	ERZ-V05D180	11	14	0.6	40	1	250	Radial	\$0.39
1776011	Littelfuse	V39ZA6	25	31	6	76	10	1000	Radial	\$0.45
2285807	Littelfuse	V39ZC6	25	31	6	76	10	1000	Radial	\$0.55
2285751	Littelfuse	V39ZT6P	25	31	6	76	10	1000	Radial	\$0.59
1911957	EPCOS	B72214S0250K101(S14K25)	25	31	7	77	10	1000	Radial	\$0.49
2296671	Jameco Valuepro	0056ZR10D	35	45	5.5	56	5	5	Radial	\$0.49
2296663	HARRIS SEMICONDUCTOR	V68ZT05	40	56	0.6	68	100	100	Radial	\$0.35
1765110	Littelfuse	V82ZA05	50	68	2	82	400	400	Radial	\$0.49
2285079	Littelfuse	V82ZT12	50	68	15	145	50	4500	Radial	\$0.49
2296527	Littelfuse	V100ZA05	60	81	2.5	165	5	400	Radial	\$0.39
2296863	Gulf Electrics	V120ZT05	75	102	3	120	400	400	Radial	\$0.39
1763499	Littelfuse	V180ZA10P	115	153	35	300	50	4500	Radial	\$0.59
34446	Jameco Valuepro	V130LA10A	130	175	38	340	50	4500	Radial	\$0.29
2296831	Major Brands	0216NR05DTOK	135	175	4.5	370	5	400	Radial	\$0.39
1763229	Littelfuse	V150LA20AP	150	200	80	395	100	6500	Radial	\$0.89
2280503	TYCO Power Systems	ROV-07-271K-S-2	175	225	19.8	455	10	1200	Radial	\$0.35
2285471	Jameco Valuepro	V275LS40BX10	275	369	140	710	100	6500	Radial	\$0.69
1911631	EPCOS	S07K300	300	385	23	775	10	1200	Radial	\$0.49
2296695	Jameco Valuepro	GNR10D471K	300	385	85	775	5	150	Radial	\$0.49
2285759	Littelfuse	V14E320	320	420	136	840	50	6000	Radial	\$0.55
2208809	Jameco Valuepro	DNR20D751K	460	615	175	1240	100	100	Radial	\$0.29