



[Click Here to Request a Large Quantity Quote](#)

[.100" \(2.54mm\) Right Angle Single Row Male Headers](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Pitch (mm)	No. of Rows	No. of Contacts	Board Mount Length	Contact Length (in.)	Body Orientation	Contact Material	Contact Plating	Housing Material	Gender	Price 1
2294575	Jameco Valuepro	7000-1X2RG-A	2.54	1	2	0.12	0.25	Right Angle	Brass	Gold Over Nickel	Polybutylene Terephthalate	Male	\$0.25
2294583	Jameco Valuepro	7000-1X3RG-A	2.54	1	3	0.12	0.25	Right Angle	Brass	Gold Over Nickel	Polybutylene Terephthalate	Male	\$0.25
2294591	Jameco Valuepro	7000-1X4RG-A	2.54	1	4	0.12	0.25	Right Angle	Brass	Gold Over Nickel	Polybutylene Terephthalate	Male	\$0.35
2294599	Jameco Valuepro	7000-1X7RG-A	2.54	1	7	0.12	0.25	Right Angle	Brass	Gold Over Nickel	Polybutylene Terephthalate	Male	\$0.35
153728	Jameco Valuepro	7000-1X8RG-B	2.54	1	8	0.12	0.23	Right Angle	Brass	Gold Over Nickel	Polybutylene Terephthalate	Male	\$0.35
2294607	Jameco Valuepro	7000-1X9RG-A	2.54	1	9	0.12	0.25	Right Angle	Brass	Gold Over Nickel	Polybutylene Terephthalate	Male	\$0.39
2294615	Jameco Valuepro	7000-1X10RG-A	2.54	1	10	0.12	0.25	Right Angle	Brass	Gold Over Nickel	Polybutylene Terephthalate	Male	\$0.49
2294623	Jameco Valuepro	7000-1X11RG-A	2.54	1	11	0.12	0.25	Right Angle	Brass	Gold Over Nickel	Polybutylene Terephthalate	Male	\$0.55
2294631	Jameco Valuepro	7000-1X12RG-A	2.54	1	12	0.12	0.25	Right Angle	Brass	Gold Over Nickel	Polybutylene Terephthalate	Male	\$0.59
2294639	Jameco Valuepro	7000-1X14RG-A	2.54	1	14	0.12	0.25	Right Angle	Brass	Gold Over Nickel	Polybutylene Terephthalate	Male	\$0.69
2294647	Jameco Valuepro	7000-1X16RG-A	2.54	1	16	0.12	0.25	Right Angle	Brass	Gold Over Nickel	Polybutylene Terephthalate	Male	\$0.79
2294655	Jameco Valuepro	7000-1X19RG-A	2.54	1	19	0.12	0.25	Right Angle	Brass	Gold Over Nickel	Polybutylene Terephthalate	Male	\$0.49
2076869	Jameco Valuepro	RMH26	2.54	1	26	0.12	0.25	Right Angle	Brass	Gold Over Nickel	Polybutylene Terephthalate	Male	\$0.79
103271	Jameco Valuepro	7000-1X36RG-R (B TYPE)	2.54	1	36	0.12	0.23	Right Angle	Brass	Gold Over Nickel	Polybutylene Terephthalate	Male	\$0.99
1946041	Jameco Valuepro	7000-1X36RG-R(A TYPE)	2.54	1	36	0.12	0.25	Straight	Brass	Gold Over Nickel	Polybutylene Terephthalate	Male	\$0.89

Jameco Part #	Manufacturer	Manufacturer Part #	Pitch (mm)	No. of Rows	No. of Contacts	Board Mount Length	Contact Length (in.)	Body Orientation	Contact Material	Contact Plating	Housing Material	Gender	Price 1
2294663	Jameco Valuepro	7000-1X40RG-A	2.54	1	40	0.12	0.25	Right Angle	Brass	Gold Over Nickel	Polybutylene Terephthalate	Male	\$1.19