



[Click Here to Request a Large Quantity Quote](#)

[AC Power Cords-2-Conductor](#)

Jameco Part #	Manufacturer	Manufacturer Part #	1st Connector	2nd Connector	AWG/Conductor	Cord Type	Length (feet)	Certifications	Jacket Color	Weight (lbs.)	Voltage Rating	Current Rating	Price 1
<a href="#">2303663</a>	Quail Electronics	8530-2-6.6	AS 3112 Australia	IEC 60320 C7	0.75mm <sup>2</sup> /2	H03VVH2-F	6.6	D, S, CEBEC, KEMA-KEUR, FI, N, OVE, VDE, CB, CE	Black	0.48	250 V	10 A	\$6.49
<a href="#">2228666</a>	Jameco Valuepro	EP-1	CEE 7/16	IEC 60320 C7	18/2	SPT-2	6	D, S, CEBEC, KEMA-KEUR, FI, N, OVE, VDE, CB, CE	Black	0.2	250 V	2.5 A	\$1.49
<a href="#">2291935</a>	Quail Electronics	8002.079	CEE 7/16 Euro 2	IEC 60320 C7	0.75mm <sup>2</sup> /2	H03VVH2-F	6.6	VDE, D, S, N, FI, S+	Black		250 V	2.5 A	\$2.49
<a href="#">189587</a>	Jameco Valuepro	1062.072	NEMA 1-15P	IEC 60320 C7	18/2	SPT-2	6	UL, CSA	Black	0.2	125 V	10 A	\$2.95
<a href="#">2290439</a>	Jameco Valuepro	SPT-1-8	NEMA 1-15P	Pigtails	18/2	SPT-1	8	UL	Black	0.21	125 V	10 A	\$2.25
<a href="#">42042</a>	Jameco Valuepro	SY-001-R	NEMA 1-15P	Pigtails	18/2	SPT-2	6	UL, CSA	Black	0.19	125 V	10 A	\$3.49
<a href="#">2230803</a>	Jameco Valuepro	SPT-6-C	NEMA 1-15P	Pigtails	18/2	SPT-2	6	UL, CSA	Black	0.19	300 V	10 A	\$1.95
<a href="#">124434</a>	Jameco Valuepro	GPC001-UB-6FT-R	NEMA 1-15P Polarized	Pigtails	18/2	SPT-2	6	UL, CSA	Black	0.19	300 V	10 A	\$2.49
<a href="#">2228623</a>	Jameco Valuepro	SY-002RSR	NEMA 1-15P Polarized	Pigtails	18/2	SPT-2	6.6	UL, CSA	Black	0.21	125 V	10 A	\$2.25