



[Click Here to Request a Large Quantity Quote](#)

[Capacitors-Electrolytic Snap Mount](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Capacitance	Package	Voltage Rating	Nominal Zener Voltage	Tolerance	Power Dissipation	Vertical/Horizontal	Zener Voltage Tolerance	Dimensions	Test Current	Price 1
<a href="#">2279991</a>	Rubycon	360CDF150VR	150 µF		360 VDC		20%		H		26 x 56 x 12 mm		\$2.95
<a href="#">2234994</a>	Vishay	80D330/200	330 µF		200 VDC		20%		V		30 x 37 x 10 mm		\$0.99
<a href="#">2296471</a>	Nippon Chemi Con	EC10K25LP	10000 µF		25 VDC		20%		V		35 x 31.5 x 12 mm		\$2.95
<a href="#">157738</a>	Jameco Valuepro	EC10K50LP-R	10000 µF		50 VDC		20%		V		35 x 40 x 10 mm		\$3.95
<a href="#">2215777</a>	Panasonic	ECE-T16R332SW	3300 µF		16 VDC		20%		V		22 x 25 x 11 mm		\$0.99
<a href="#">2289463</a>	Arndt Electronics	EKMS421VSN681MA50S	680 µF		420 VDC		20%		V		35 x 50 x 10 mm		\$6.95
<a href="#">2280095</a>	Nichicon	ESMH630VNN392MP40T	3900 µF		63 VDC		20%		V		22 x 41 x 10 mm		\$1.95
<a href="#">2302135</a>	United CHEMI CON	KMH35VN103M30X35T2	10000 µF		35 VDC		20%		V		30 x 35 x 10 mm		\$3.95
<a href="#">2234986</a>	Illinois Capacitor	LBAM470/250	470 µF		250 VDC		20%		V		30 x 31 x 12 mm		\$2.49
<a href="#">2323079</a>	Nichicon	LGR2W470MELZ30	47 µF		450 VDC		20%		V		30 x 31 x 12 mm		\$3.49
<a href="#">2323199</a>	Nichicon	LGR821/450	820 µF		450 VDC		20%		V		35 x 52 x 9 mm		\$10.95
<a href="#">2323951</a>	Fairchild Semiconductor	P6KE62A		DO-204		53		600W		5%		1mA	\$0.49
<a href="#">2235137</a>	Arndt Electronics	S1500/50	1500 µF		50 VDC		20%		V		25 x 27 x 10 mm		\$1.95
<a href="#">2235153</a>	Arndt Electronics	S15000/50	15000 µF		50 VDC		20%		V		35 x 40 x 10 mm		\$3.95

Jameco Part #	Manufacturer	Manufacturer Part #	Capacitance	Package	Voltage Rating	Nominal Zener Voltage	Tolerance	Power Dissipation	Vertical/Horizontal	Zener Voltage Tolerance	Dimensions	Test Current	Price 1
<a href="#">2235145</a>	Arndt Electronics	S2200/80	2200 $\mu$ F		80 VDC		20%		V		22 x 41 x 10 mm		\$1.95
<a href="#">2313623</a>	Cornell Dubilier	SLP222M100C4P3	2200 $\mu$ F		100 VDC		20%		V		24 x 45 x 10 mm		\$3.49
<a href="#">331716</a>	Jameco Valuepro	SNA15000/25-R	15000 $\mu$ F		25 VDC		20%		V		35 x 40 x 9 mm		\$2.95
<a href="#">115378</a>	Jameco Valuepro	SNB4700/35	4700 $\mu$ F		35 VDC		20%		V		23 x 40 x 9 mm		\$1.95
<a href="#">331901</a>	Jameco Valuepro	SNB6800/50-R	6800 $\mu$ F		50 VDC		20%		V		25 x 40 x 10 mm		\$3.95