



Click Here to Request a Large Quantity Quote

Relays-Solid State

Jameco Part #	Manufacturer	Manufacturer Part #	Product Type	Contact Form	Contact Voltage	Contact Current	Control Voltage	Pins	Terminal Type	Size (L" x W" x H")	Product Length	Product Width	Price 1
2302791	Sharp Electronic Components	S208T02	AC	SPST-NO	80 - 240 VAC	0.05	1.2 VDC	4	SIP-4	.90 x .16 x .63	23mm	4.0mm	\$19.95
162342	Excel Cell Electronics	ESR5102401000Z	DC/AC	SPST	240 VAC	10	3-32VDC	4	Screw Terminal	1.7 x 1.1 x 2.3	57mm	43.0mm	\$16.95
175214	Kyotro	KB20C02A	DC/AC	SPST	280 VAC	2	3-32VDC	4	SIP-4	1.4 x 0.3 x 1.5	30.7mm	8.0mm	\$7.95
176719	Kyotro	KD20C40AX	DC/AC	SPST	280 VAC	40	4-32VDC	4	Screw Terminal	1.7 x 0.9 x 2.3	57mm	43.5mm	\$19.95
176698	Kyotro	KB20C06A	DC/AC	SPST	280 VAC	6	3-32VDC	4	SIP-4	1.4 x 0.3 x 0.9	37mm	8.0mm	\$8.95
1583156	Clare/LXYS Corporation	PD2401	DC/AC	SPST	500 V Load	1	1.2 VDC	4	DIP-16	.76 x .25 x .14	19.2mm	6.35mm	\$6.59
2273167	Crydom	D4825	DC/AC	SPST	530 VAC	25	3-32VDC	4	Screw Terminal	2.25 x 1.75 x .89	57.3mm	44.5mm	\$29.95
164996	Sharp Electronic Components	S202TA1	DC/AC	SPST	80 to 240 VAC	2.5	1.2 VDC	4	SIP-4	.91 x .16 x .45	23.0mm	4.0mm	\$1.95
2313663	Crydom	CX241	DC/AC	SPST-NO	12 - 280 VAC	1.5	4-10 VDC	4	SIP-4	1.62 x 0.3 x 0.68	41.7mm	7.76mm	\$9.95
2307887	Rayex Electronics	RSR1ND-A24025	DC/AC	SPST-NO	240 VAC	25	3-32 VDC	4	Screw Terminal	2.26 x 1.57 x 1.10	57.4mm	40mm	\$29.95
2307895	Rayex Electronics	RSR1ND-A24050	DC/AC	SPST-NO	240 VAC	50	3-32 VDC	4	Screw Terminal	2.26 x 1.57 x 1.10	57.4mm	40mm	\$34.95
2302327	Magnecraft Corporation	70S2-04-D-02-H	DC/AC	SPST-NO	24VAC	2.5	3-30VDC	4	4-Pin				\$19.95
1582903	Clare/LXYS Corporation	LAA110	DC/AC	SPST-NO	350 V Load	0.05	1.2 VDC	8	DIP-8	.36 x .25 x .15	9.6mm	6.35mm	\$3.95
1582997	Clare/LXYS Corporation	LCA110	DC/AC	SPST-NO	350 V Load	0.12	1.2 VDC	6	DIP-8	.33 x .25 x .13	8.38mm	6.35mm	\$1.65
1583041	Clare/LXYS Corporation	LCA710	DC/AC	SPST-NO	60 V Load	1	1.2 VDC	6	DIP-6	.33 x .25 x .13	8.38mm	6.35mm	\$4.49
842591	Panasonic	AQV212	DC/AC	SPST-NO	60 VDC	0.55	1.14 VDC	6	DIP-6	.35 x .25 x .15	8.8mm	6.4mm	\$3.95
176655	Kyotro	KG1010D	DC/DC	SPST	120 VDC	10	3-32VDC	4	Screw Terminal	2.3 x 1.7 x 0.9	57mm	43.5mm	\$19.95
176648	Kyotro	KG1005D-R	DC/DC	SPST	120 VDC	5	3-32VDC	4	Screw Terminal	2.3 x 1.7 x 0.9	57mm	43.5mm	\$17.95
2218126	Crydom	CMX60D10-6454	DC/DC	SPST	60 VDC	10	3-10VDC	4	SIP-4	1.60 x 0.3 x 0.9	43.1mm	7.6mm	\$14.95

Jameco Part #	Manufacturer	Manufacturer Part #	Product Type	Contact Form	Contact Voltage	Contact Current	Control Voltage	Pins	Terminal Type	Size (L" x W" x H")	Product Length	Product Width	Price 1
175222	Kyotto	KF0604D	DC/DC	SPST	60 VDC	4	3-32VDC	4	SIP-4	1.5 x 0.3 x 0.9	38.8mm	8.7mm	\$9.95
2144737	Teledyne Relays	C47F-20	DC/DC	SPST	90 VDC	1	3-32VDC	4	DIP-4	.75 x .25 x .17	19.05mm	7.62mm	\$4.95
2307903	Rayex Electronics	RSR1ND-D24010	DC/DC	SPST-NO	240 VDC	10	3-32 VDC	4	Screw Terminal	2.26 x 1.57 x 1.10	57.4mm	40mm	\$34.95
2307911	Rayex Electronics	RSR1ND-D24040	DC/DC	SPST-NO	240 VDC	40	3-32 VDC	4	Screw Terminal	2.26 x 1.57 x 1.10	57.4mm	40mm	\$49.95
2307919	Rayex Electronics	RSR1ND-D24060	DC/DC	SPST-NO	240 VDC	60	3-32 VDC	4	Screw Terminal	2.26 x 1.57 x 1.10	57.4mm	40mm	\$64.95
172591	Kyotto	KF0602D	DC/DC	SPST-NO	60 VDC	2	3-32VDC	4	SIP-4	1.5 x 0.3 x 0.9	37mm	8.0mm	\$8.25
1583181	Clare/LXYS Corporation	TS117	Telecom	SPST-NO	350 VDC	0.12	0.9-1.4 VDC	8	DIP-8	.35 x .25 x .15	8.35mm		\$2.49