



[Click Here to Request a Large Quantity Quote](#)

[RF Connectors](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Family	Gender	Body Orientation	Impedance	Contact Plating	Contact Material	Body Plating	Body Material	Operating Frequency	Termination Method	Price 1
<a href="#">2077618</a>	Jameco Valuepro	BNC-CR	BNC	Female	Right Angle	50 Ohm	Tin	Tin	Nickel	Brass	0Hz to 4GHz	PCB	\$0.75
<a href="#">174290</a>	Jameco Valuepro	TBC-090-R	BNC	Female	Straight	50 Ohm	Gold	Bass	Nickel	Brass	0Hz to 4GHz	Solderable Cup	\$1.25
<a href="#">111561</a>	Steren Electronics	200-148	BNC	Female	Straight	50 Ohm	Gold	Brass	Nickel	Brass/Zinc	0Hz to 4GHz	Solderable Lug	\$2.25
<a href="#">71590</a>	Jameco Valuepro	G1B235-R	BNC	Female	Straight	50 Ohm	Gold	Brass	Nickel	Steel	0Hz to 4GHz	Solderable Lug	\$1.75
<a href="#">2161297</a>	Jameco Valuepro	B-235-1-R	BNC	Female	Straight	50 Ohm	Gold	Phosphor Bronze	Nickel	Brass	0Hz to 4GHz	Solderable Cup	\$1.09
<a href="#">421331</a>	TE Connectivity	227726-3	BNC	Female	Straight	50 Ohm	Gold	Phosphor Bronze	Nickel	Brass	0Hz to 4GHz	Solderable Cup	\$4.25
<a href="#">223360</a>	Amphenol	31-5	BNC	Female	Straight	50 Ohm	Gold	Silver	Nickel	Brass	0Hz to 4GHz	Compression	\$3.95
<a href="#">355178</a>	Jameco Valuepro	31-221-VP	BNC	Female	Straight	50 Ohm	Gold Over Nickel	Phosphor Bronze	Nickel	Brass	0Hz to 4GHz	Solderable Cup	\$1.75
<a href="#">223520</a>	Amphenol	31-236-RFX	BNC	Female	Straight	50 Ohm	Silver	Silver	Nickel	Brass	0Hz to 4GHz	Solderable Cup	\$1.49
<a href="#">2280239</a>	Amphenol	112495	BNC	Female	Straight	75 Ohm	Gold	Phosphor Bronze	Nickel	Zinc	0Hz to 4GHz		\$2.95
<a href="#">2185811</a>	Amphenol	31-5500	BNC	Female/Female	Straight	50 Ohm	Gold	Brass	Nickel	Brass	0Hz to 4GHz	PCB	\$0.29
<a href="#">2225924</a>	Jameco Valuepro	MCI-7062 50OHM	BNC	Female/Female	Straight	50 Ohm	Gold	Brass	Nickel	Zinc	0Hz to 4GHz	Panel	\$2.49
<a href="#">71909</a>	Steren Electronics	200-160	BNC	Female/Female	Straight	50 Ohm	Gold	Brass/Zinc	Nickel	Brass/Zinc	0Hz to 4GHz	Cable or Panel	\$1.19
<a href="#">658451</a>	Amphenol	112437	BNC	Female/Female	Straight	50 Ohm	Gold	Phosphor Bronze	Nickel	Brass	0Hz to 4GHz	Panel	\$5.49
<a href="#">355152</a>	Jameco Valuepro	31-219-RFX-VP-R	BNC	Female/Female	Straight	50 Ohm	Silver	Beryllium Copper	Nickel	Brass	0Hz to 4GHz	Cable or Panel	\$2.95
<a href="#">2258611</a>	Jameco Valuepro	FFF-T-BNC	BNC	Female/Female/Female	Tee Style	50 Ohm	Gold	Brass	Nickel	Brass	0Hz to 4GHz	Cable or Panel	\$0.79

Jameco Part #	Manufacturer	Manufacturer Part #	Family	Gender	Body Orientation	Impedance	Contact Plating	Contact Material	Body Plating	Body Material	Operating Frequency	Termination Method	Price 1
<a href="#">118594</a>	Steren Electronics	200-155	BNC	Female/Male/Female	Tee Style	50 Ohm	Gold	Brass/Zinc	Nickel	Brass/Zinc	0Hz to 4GHz		\$1.75
<a href="#">2084341</a>	Amphenol	MX-554A/U-100	BNC	Male	Straight	100 Ohm	Silver	Brass	Nickel	Brass	0Hz to 4GHz	Panel	\$0.79
<a href="#">188306</a>	Amphenol	31-320-RFX	BNC	Male	Straight	50 Ohm	Gold	Brass	Nickel	Brass	0Hz to 4GHz	Crimp	\$2.49
<a href="#">2185731</a>	Amphenol	31-347	BNC	Male	Straight	50 Ohm	Gold	Brass	Nickel	Brass	0Hz to 4GHz	Crimp	\$0.39
<a href="#">2185820</a>	Amphenol	31-332	BNC	Male	Straight	50 Ohm	Gold	Brass	Nickel	Brass	0Hz to 4GHz	Crimp	\$0.39
<a href="#">71458</a>	Jameco Valuepro	B-611T	BNC	Male	Straight	50 Ohm	Gold	Brass	Nickel	Brass	0Hz to 4GHz	Panel	\$1.25
<a href="#">2185694</a>	Amphenol	31-321-1002	BNC	Male	Straight	50 Ohm	Gold	Brass	Nicel	Brass	0Hz to 4GHz	Crimp	\$1.09
<a href="#">71482</a>	Steren Electronics	200-145	BNC	Male	Straight	50 Ohm	Gold	Brass/Zinc	Nickel	Brass/Zinc	0Hz to 1GHz	Crimp	\$1.09
<a href="#">112110</a>	Jameco Valuepro	G7409-R	BNC	Male	Straight	50 Ohm	Gold Over Nickel	Brass	Nickel Over Copper	Brass	0Hz to 4GHz	Crimp	\$1.25
<a href="#">2185723</a>	Amphenol	31-206	BNC	Male	Straight	50 Ohm	Silver	Beryllium Copper	Silver	Brass	0Hz to 4GHz	Compression	\$6.95
<a href="#">223394</a>	Amphenol	31-212	BNC	Male	Straight	50 Ohm	Silver	Brass	Nickel	Brass	0Hz to 4GHz	Cable-Clamp	\$3.95
<a href="#">2085052</a>	Amphenol	31-71013	BNC	Male	Straight	75 Ohm	Gold	Brass	Nickel	Brass	0Hz to 4GHz	Crimp	\$1.25
<a href="#">2258638</a>	Jameco Valuepro	RG-59U-BNC	BNC	Male	Straight	75 Ohm	Gold	Brass	Nickel	Brass	0Hz to 4GHz	Crimp	\$0.99
<a href="#">2258620</a>	Jameco Valuepro	RG-6U-BNC	BNC	Male	Straight	75 Ohm	Gold	Brass	Nickel	Brass	0Hz to 4GHz	Crimp	\$0.79
<a href="#">2185993</a>	Amphenol	MX554A/U	BNC	Male	Straight	91 Ohm	Gold	Brass	Nickel	Brass	0Hz to 4GHz	Panel	\$1.49
<a href="#">2277023</a>	Amphenol	31-6-RFX	BNC	Male Cap	Straight	50/75 Ohm	-	-	Nickel	Zinc	0Hz to 4GHz	Panel	\$1.49
<a href="#">127352</a>	Jameco Valuepro	B-412-R	BNC	Male/Female	Right Angle	50 Ohm	Gold	Brass	Nickel	Brass	N/A		\$3.59
<a href="#">2115928</a>	Arndt	MX575A/U	BNC	Male/Female	Straight	75 Ohm	Gold	Brass	Tarnish Resistant	Brass	0Hz to 4GHz		\$1.49
<a href="#">127343</a>	Jameco Valuepro	B-311	BNC	Male/Male	Straight	50 Ohm	Gold	Brass	Nickel	Brass	0Hz to 4GHz		\$2.49
<a href="#">114753</a>	Jameco Valuepro	RB312	BNC-RCA	Male/Female	Straight	50 Ohm	Nickel	Brass	Nickel	Brass	0Hz to 1GHz	Cable	\$1.49
<a href="#">114789</a>	Jameco Valuepro	BR312-R	BNC-RCA	Male/Male	Straight	50 Ohm	Nickel	Brass	Nickel	Zinc	0Hz to 1GHz	Cable	\$1.95
<a href="#">2284807</a>	Pomona Electronics	1452	BNC/Binding Post	Female/Male	Straight	50 Ohm	Nickel	Brass	Nickel	Zinc	N/A		\$16.49

Jameco Part #	Manufacturer	Manufacturer Part #	Family	Gender	Body Orientation	Impedance	Contact Plating	Contact Material	Body Plating	Body Material	Operating Frequency	Termination Method	Price 1
<a href="#">2284799</a>	Pomona Electronics	1296	BNC/Binding Post	Male/Female	Straight	50 Ohm	Nickel	Brass	Nickel	Brass	N/A		\$18.49
<a href="#">2284791</a>	Pomona Electronics	1269	BNC/Double Banana	Female/Male	Straight	50 Ohm	Nickel	Brass	Nickel	Brass	N/A		\$10.29
<a href="#">2272079</a>	Kobiconn	17PF059	F-Type	Male	Straight	75 Ohm	Nickel	Brass	Nickel	Brass	0Hz to 1GHz	Crimp	\$0.29
<a href="#">2272143</a>	Jameco Valuepro	SNS1P6-VP	F-Type Seal	Male	Straight	75 Ohm	-	-	Brass	Brass	0Hz to 1GHz	Crimp	\$0.49
<a href="#">2276943</a>	Amphenol	172300	N-Type	Male	Straight	50 Ohm	Gold	Phosphor Bronze	Nexcote	Brass	0Hz to 11GHz	Compression	\$12.95
<a href="#">2276951</a>	Amphenol	17312	N-Type	Male	Straight	50 Ohm	Gold	Phosphor Bronze	Nickel	Brass	0Hz to 11GHz	Compression	\$9.95
<a href="#">2277047</a>	Huber & Suhner	32 N-716-50-2/133 WE	N-Type	Male/Male	Straight	50 Ohm	Gold	Brass	Silver	Brass	0Hz to 7.5GHz	Cable or Panel	\$119.95
<a href="#">2091541</a>	Amphenol	132119RP	SMA	Female	Straight	50 Ohm	Gold	Beryllium Copper	Gold	Brass	0Hz to 12.4GHz	Crimp	\$3.95
<a href="#">145382</a>	Jameco Valuepro	S-P215-10A-HI-R GGT	SMA	Female	Straight	50 Ohm	Gold	Beryllium Copper	Gold	Brass	0Hz to 18GHz	Solderable Cup	\$2.25
<a href="#">159531</a>	Jameco Valuepro	S-2454-GGT	SMA	Female	Straight	50 Ohm	Gold	Brass	Gold	Brass	0Hz to 18GHz	Solderable Cup	\$2.95
<a href="#">659059</a>	Amphenol	132170	SMA	Female/Female	Straight	50 Ohm	Gold	Beryllium Copper	Gold	Brass	0Hz to 18GHz	Cable or Panel	\$7.49
<a href="#">160013</a>	Jameco Valuepro	CH-7818-N-R	SMA	Female/Female	Straight	50 Ohm	Gold	Brass	Nickel	Brass	0Hz to 18GHz	Cable or Panel	\$3.29
<a href="#">153366</a>	Jameco Valuepro	4804-R	SMA	Male	Straight	50 Ohm	Gold	Brass	Nickel	Brass	0Hz to 18GHz	Crimp	\$2.95
<a href="#">153286</a>	Jameco Valuepro	SMA-7813-R	SMA	Male	Straight	50 Ohm	Gold Over Nickel	Phosphor Bronze	Gold Over Nickel	Brass	0Hz to 18GHz	Solderable Cup	\$2.95
<a href="#">161307</a>	Jameco Valuepro	S-412-G-R	SMA	Male/Female	Right Angle	50 Ohm	Gold	Brass	Gold	Brass	0Hz to 18GHz	Cable or Panel	\$4.49
<a href="#">161294</a>	Jameco Valuepro	S-311-G-R	SMA	Male/Male	Straight	50 Ohm	Gold	Brass	Gold	Brass	0Hz to 18GHz	Cable or Panel	\$2.75
<a href="#">159469</a>	Jameco Valuepro	CH7830-N-R	SMA-BNC	Female/Female	Straight	50 Ohm	Gold	Brass	Nickel	Brass	0Hz to 4GHz	Cable or Panel	\$2.95
<a href="#">153454</a>	Jameco Valuepro	SB-321-R	SMA-BNC	Female/Male	Straight	50 Ohm	Gold	Brass	Nickel	Brass	0Hz to 4GHz	Cable or Panel	\$2.25

Jameco Part #	Manufacturer	Manufacturer Part #	Family	Gender	Body Orientation	Impedance	Contact Plating	Contact Material	Body Plating	Body Material	Operating Frequency	Termination Method	Price 1
<a href="#">159477</a>	Jameco Valuepro	CH-7820-N-R	SMA-BNC	Male/Female	Straight	50 Ohm	Gold	Brass	Nickel	Brass	0Hz to 4GHz	Cable or Panel	\$2.95
<a href="#">153593</a>	Jameco Valuepro	4288-R	SMA-BNC	Male/Male	Straight	50 Ohm	Gold	Brass	Gold	Brass	0Hz to 4GHz	Cable or Panel	\$2.95
<a href="#">2085204</a>	Amphenol	82-5590	Twinax	Female	Straight	110 Ohm	Gold	Phospher Bronze	Nickel	Brass	0Hz to 500MHz	Solderable Cup	\$5.95