



[Click Here to Request a Large Quantity Quote](#)

Crimp Terminals

Jameco Part #	Manufacturer	Manufacturer Part #	Family	Gender	Maximum Current Rating (A)	Wire Gauge (AWG)	Voltage Rating	Product Type	Contact Plating	Contact Material	Price 1
78319	Jameco Valuepro	JS-5001-T-R	.156" Terminals	Female	1.5	24-18	250 VAC/VDC	Crimp	Tin	Brass	\$0.06
185421	Jameco Valuepro	1006-PP	1006	Male		28-24		Crimp	Nickel	Brass	\$0.05
181673	Jameco Valuepro	25403-T	25403	Female	3	30-22	250 VAC	Crimp	Tin	Phosphor Bronze	\$0.09
895844	TE Connectivity	104480-3	AMPMODU	Female		26-22		Crimp	Gold	Brass	\$0.25
147395	Jameco Valuepro	C4202TOB02	ATX Disk	Female	1	22-18	250 VAC	Crimp	Tin	Brass	\$0.12
42650	Jameco Valuepro	JS-1114-04WT-R	ATX Disk	Female	1.5	24-18	250 VAC	Crimp	Tin	Brass	\$0.15
114922	Jameco Valuepro	CT256	ATX Disk	Female	3	26-22	250 VAC/VDC	Crimp	Tin	Brass	\$0.19
42730	Jameco Valuepro	JS-1114-04HT-R	ATX Disk	Male	1.5	24-18	250 VAC	Crimp	Tin	Brass	\$0.22
2232593	Delphi	120484913	Automotive	Female	7	22-20	14 VDC	Crimp	Nickel, Tin & Gold	Phosphor Bronze	\$0.29
2232606	Delphi	12129493	Automotive	Female	30	14	14 VDC	Crimp	Tin	Copper Alloy	\$0.25
2231224	Banner Engineering	7116-4112-02	Automotive	Female		14		Crimp	Tin	Copper Alloy	\$1.95
2231267	Yazaki	7116-4110-02	Automotive	Female		22-20		Crimp	Tin	Copper Alloy	\$1.49
2231232	Banner Engineering	7116-4111-02	Automotive	Female		18-16		Crimp	Tin	Copper Alloy	\$0.79
2231275	Banner Engineering	7114-4112-02	Automotive	Male		14		Crimp	Tin	Copper Alloy	\$0.59
2231283	Banner Engineering	7114-4111-02	Automotive	Male		18-16		Crimp	Tin	Copper Alloy	\$0.59
2232614	Delphi	54001845	Automotive	Male		22-18		Crimp	Gold	Copper Alloy	\$0.79
2231259	Banner Engineering	7114-4110-02	Automotive	Male		22-20		Crimp	Tin	Copper Alloy	\$0.49
2232411	Yazaki	7114-4212-02	Automotive	Male		14		Crimp	Tin	Copper Alloy	\$0.29
2231241	Arndt	7114-4120-02	Automotive	Male		20-16		Crimp	Tin	Copper Alloy	\$0.59
2232631	Delphi	54001819	Automotive	Male		20-18		Crimp	Gold Over Nickel	Copper Alloy	\$0.49

Jameco Part #	Manufacturer	Manufacturer Part #	Family	Gender	Maximum Current Rating (A)	Wire Gauge (AWG)	Voltage Rating	Product Type	Contact Plating	Contact Material	Price 1
2232681	TE Connectivity	1326032-5	Blade .110"	Female		14		Crimp	Tin	Copper Alloy	\$0.25
43369	Steren Electronics	500-155	D-Sub	Female		28-24		Crimp	Gold	Copper Alloy	\$0.17
43377	Steren Electronics	500-055	D-Sub	Male		28-24		Crimp	Gold	Copper Alloy	\$0.17
337762	Adam Technologies	DMT-B-C-M-T-R	DMH	Male	1	30-20	250 VAC	Crimp	Tin	Phosphor Bronze	\$0.05
449351	TE Connectivity	205090-1	HD-20	Female		24-20		Crimp	Gold	Copper Alloy	\$0.55
449342	TE Connectivity	205089-1	HD-20	Male		24-20		Crimp	Gold	Copper Alloy	\$0.39
223298	TE Connectivity	66504-9	HDP-20	Female		24-20		Crimp	Gold	Phosphor Bronze	\$0.19
223191	TE Connectivity	66506-9	HDP-20	Male		24-20		Crimp	Gold	Brass	\$0.19
234982	TE Connectivity	66570-3	HDP-20	Male		18		Crimp	Gold	Brass	\$0.39
223108	TE Connectivity	66507-9	HDP-20	Male		28-24		Crimp	Gold	Brass	\$0.25
100766	Jameco Valuepro	JS-1105-T-R	Housing	Female	3	28-22	250 VAC/VDC	Crimp	Gold	Brass	\$0.15
145358	Jameco Valuepro	Y-1800-TX-R	Housing	Male	3	28-22	250 VAC/VDC	Crimp	Tin	Brass	\$0.15
2287239	TE Connectivity	927766-3	JPT	Female	7	17-13	250 VAC/VDC	Crimp	Tin	Brass	\$0.35
2234548	Adam Technologies	2CTC-R	JST	Female	1	30-24	100 VAC	Crimp	Tin	Phosphor Bronze	\$0.25
234931	Molex	08-55-0102	KK Series .100"	Female	2.5	30-22	250 VAC/VDC	Crimp	Gold	Brass	\$0.15
463005	Molex	08-65-0816	KK Series .100"	Female	4	30-22	250 VAC/VDC	Crimp	Gold	Phosphor Bronze	\$0.29
462969	Molex	08-65-0805	KK Series .100"	Female	4	30-22	250 VAC/VDC	Crimp	Tin	Phosphor Bronze	\$0.12
736595	Molex	08-52-0123	KK Series .100"	Female	4	30-22	250 VAC/VDC	Crimp	Tin	Phosphor Bronze	\$0.12
234923	Molex	08-50-0114	KK Series .100"	Female	5	30-22	250 VAC/VDC	Crimp	Tin	Brass	\$0.09
736501	Molex	08-50-0113	KK Series .100"	Female	5	30-22	250 VAC/VDC	Crimp	Tin	Brass	\$0.06
736481	Molex	08-50-0106	KK Series .156"	Female	5	24-18	250 VAC/VDC	Crimp	Tin	Brass	\$0.10
736544	Molex	08-50-0189	KK Series .156"	Female	5	24-18	250 VAC/VDC	Crimp	Tin	Brass	\$0.09
736587	Molex	08-52-0113	KK Series .156"	Female	5	26-18	250 VAC	Crimp	Tin	Phosphor Bronze	\$0.12

Jameco Part #	Manufacturer	Manufacturer Part #	Family	Gender	Maximum Current Rating (A)	Wire Gauge (AWG)	Voltage Rating	Product Type	Contact Plating	Contact Material	Price 1
736561	Molex	08-52-0072	KK Series .156"	Female	5	26-18	250 VAC/VDC	Crimp	Tin	Brass	\$0.10
734670	Molex	02-08-1002	MLX	Female	5	20-14	250 VAC/VDC	Crimp	Tin	Brass	\$0.25
2124630	Adam Technologies	MTC-C-R	MTC	Female	5	22-18	250 VAC	Crimp	Tin	Phosphor Bronze/Brass	\$0.25
2232585	Molex	33012-1002	MX150	Female		20-18	14 VDC	Crimp	Tin	High Performance Alloy	\$0.25
2232569	Molex	31296-0004	MX150	Male	22	20-18	500 VDC	Crimp	Gold Over Nickel	Brass	\$0.25
2232577	Molex	33000-1002	MX150	Male		20-16	14 VDC	Crimp	Tin	High Performance Alloy	\$0.25
1977403	TE Connectivity	770003-3	Mate-N-Lock	Male	19	12-10	600 VAC	Crimp	Tin	Phosphor Bronze	\$0.39
337746	Jameco Valuepro	43030-0010-VP	Micro Fit .118"	Female	5	24-20	250 VAC	Crimp	Tin	Phosphor Bronze	\$0.25
1969913	Molex	43030-0009	Micro Fit .118"	Female	5	24-20	250 VAC/VDC	Crimp	Gold	Phosphor Bronze	\$0.25
883093	Molex	43030-0007	Micro Fit .118"	Female	5	24-20	250 VAC/VDC	Crimp	Tin	Phosphor Bronze	\$0.09
337720	Jameco Valuepro	DMT-B-C-F-T-R	Micro Fit .118"	Female	5	24-20	250 VAC/VDC	Crimp	Tin	Phosphor Bronze	\$0.12
304733	Molex	39-00-0039	Mini Fit .165"	Female	9	24-18	600 VAC	Crimp	Tin Over Copper	Brass	\$0.11
304872	Molex	39-00-0047	Mini Fit .165"	Female	9	28-22	600 VAC	Crimp	Tin Over Copper	Brass	\$0.15
304725	Molex	39-00-0041	Mini Fit .165"	Male	9	24-18	600 VAC	Crimp	Tin Over Copper	Brass	\$0.14
304864	Molex	39-00-0049	Mini Fit .165"	Male	9	28-22	600 VAC	Crimp	Tin Over Copper	Brass	\$0.15
401701	Jameco Valuepro	DMH-B-C-F-R	Mini Fit Jr .122"	Female	9	24-18	600 VAC	Crimp	Tin	Brass	\$0.25
401808	Jameco Valuepro	4256TP3-G15-LP	Mini Fit Jr .165"	Female	9	16	600 VAC	Crimp	Tin	Phosphor Bronze	\$0.12
401736	Adam Technologies	DMH-B-C-F-G	Mini Fit Jr .165"	Female	9	24-18	600 VAC	Crimp	Gold Over Nickel	Brass	\$0.29
34155	Vector Electronics	T44/C	Mini-Klip	Male				Crimp	Tin		\$10.95
34147	Vector Electronics	T42-1/C	Mini-Klip	Male				Crimp	Tin		\$11.95
34163	Vector Electronics	T49/C	Mini-Klip	Male				Crimp	Tin		\$14.95
526432	TE Connectivity	66181-1	Multimate III+	Female		18-16		Crimp	Gold	Brass	\$1.29

Jameco Part #	Manufacturer	Manufacturer Part #	Family	Gender	Maximum Current Rating (A)	Wire Gauge (AWG)	Voltage Rating	Product Type	Contact Plating	Contact Material	Price 1
526379	TE Connectivity	66105-3	Multimate III+	Female		24-20		Crimp	Gold	Brass	\$0.59
526504	TE Connectivity	1-66105-6	Multimate III+	Female		24-20		Crimp	Tin-Lead	Brass	\$0.49
891376	TE Connectivity	1-66105-9	Multimate III+	Female		24-20		Crimp	Tin	Brass	\$0.55
526441	TE Connectivity	1-66361-1	Multimate III+	Male		18-14		Crimp	Gold	Brass	\$0.95
526459	TE Connectivity	66103-3	Multimate III+	Male		24-20		Crimp	Gold	Brass	\$0.49
526563	TE Connectivity	1-66103-5	Multimate III+	Male		24-20		Crimp	Tin-Lead	Brass	\$0.44
526361	TE Connectivity	1-66103-7	Multimate III+	Male		24-20		Crimp	Gold	Brass	\$0.55
526344	TE Connectivity	66099-4	Multimate III+	Male		18-16		Crimp	Gold	Brass	\$0.79
2232673	TE Connectivity	66740-7	Multimate XII	Female		16-12		Crimp	Tin-Lead	Copper	\$5.95
224557	Molex	02-06-1103	Power .062"	Female	5	24-18	250 VAC/VDC	Crimp	Tin	Brass	\$0.15
224573	Molex	02-06-1132	Power .062"	Female	5	24-18	250 VAC/VDC	Crimp	Tin	Brass	\$0.09
227387	Molex	02-06-7103	Power .062"	Female	5	24-18	250 VAC/VDC	Crimp	Tin	Brass	\$0.15
224565	Molex	02-06-2103	Power .062"	Male	5	24-18	250 VAC/VDC	Crimp	Tin	Brass	\$0.12
224581	Molex	02-06-2132	Power .062"	Male	5	24-18	250 VAC/VDC	Crimp	Tin	Brass	\$0.12
224215	Molex	02-09-1119	Power .093"	Female	5	20-14	250 VAC/VDC	Crimp	Tin	Brass	\$0.12
224231	Molex	02-09-1104	Power .093"	Female	5	20-14	250 VAC/VDC	Crimp	Tin	Brass	\$0.12
224207	Molex	02-09-2118	Power .093"	Male	5	20-14	250 VAC/VDC	Crimp	Tin	Brass	\$0.12
224223	Molex	02-09-2103	Power .093"	Male	5	20-14	250 VAC/VDC	Crimp	Tin	Brass	\$0.12
2290767	Cinch Connectors	42500-00-872	SHS	Female		20-18		Crimp	Tin	Copper Alloy	\$0.25
741685	Molex	16-02-0103	SL .100"	Female	3	24-22	250 VAC/VDC	Crimp	Gold Over Nickel	Copper Alloy	\$0.09
741677	Molex	16-02-0086	SL .100"	Female	3	24-22	250 VAC/VDC	Crimp	Tin Over Nickel	Copper Alloy	\$0.06
248903	TE Connectivity	770522-1	SL .156"	Cable Mount	10	24-18	250 VAC/VDC	Crimp	Tin Lead	Brass	\$0.15