



[Click Here to Request a Large Quantity Quote](#)

D-Sub Hardware

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Thread Size	Product Type	Length (inch)	Thickness (in.)	Material	Price 1
2185766	Amphenol	17-768	D-Sub Connector Hardware Kit (Hex jack screws, clips, washers & nuts) (12 Pcs.) For D-Sub Connectors	4-40	Jackscrew (set)	0.35	0.187	Steel	\$1.95
2228949	Abbatron HH Smith	7228-5	Jack Screw 0.187" Hex 4-40 Thread x 0.250"L (1 pc.) For D-Sub Connectors	4-40	Jackscrew	0.25	0.187	Steel	\$0.45
169931	Jameco Valuepro	14-556-L11.8	Jack Screw 0.187" Hex 4-40 x 0.275"L Chrome (1 pc.) For D-Sub Connectors	4-40	Jackscrew	0.275	0.187	Steel	\$0.25
2100283	Jameco Valuepro	JS4403LW	Jack Screw 0.187" Hex 4-40 x 0.315"L with Fixed Lock Washer (1 pc.) For D-Sub Connectors	4-40	Jackscrew	0.315	0.187	Steel	\$0.25
102816	Jameco Valuepro	14-556-L15.7	Jack Screw 0.187" Hex 4-40 x 0.437"L (1 pc.) For D-Sub Connectors	4-40	Jackscrew	0.437	0.187	Steel	\$0.35
108987	Jameco Valuepro	14-556-L18-R	Jack Screw 0.187" Hex 4-40 x 0.515"L (1 pc.) For D-Sub Connectors	4-40	Jackscrew	0.515	0.187	Steel	\$0.39
16548	Jameco Valuepro	14-522	Jack Screw and Nut Washers Set 0.187" Hex 4-40 x 0.315"L (4 pcs.) For D-Sub Connectors	4-40	Jackscrew (set)	0.315	0.187	Steel	\$0.69
2321463	Jameco Valuepro	SDG400A	Jack Screw, Nut and Split Washer Set 0.187" Hex 4-40 x 0.375"L (3 pcs.) For D-Sub Connectors	4-40	Jackscrew (set)	0.375	0.187	Steel	\$0.89
2291311	Jameco Valuepro	14-522LW	Jack Screw, Nut and Washers (Fixed Lock) Set 0.187" Hex 4-40 x 0.312"L (4 pcs.) For D-Sub Connectors	4-40	Jackscrew (set)	0.315	0.187	Steel	\$0.65
2321335	Jameco Valuepro	D20418-50	Jack Screw, Nut and Washers Set 0.187" Hex 4-40 x 0.315"L (5 pcs.) for D-Sub Connectors	4-40	Jackscrew (set)	0.187	0.187	Steel	\$3.95
2302487	Jameco Valuepro	H475127N44	Jackscrew 0.187" Hex 4-40 x 0.3125"L (1 pc.) For D-Sub Connectors	4-40	Jackscrew	0.315	0.187	Steel	\$0.29
2315087	Keystone Electronics	2071	Jackscrew Thumb Screw .215" Thread .51" Thread & Shaft 2.27" Overall Length For D-Sub Connectors	4-40	Thumbscrew	2.27	0.163	Steel	\$1.49
2314815	Keystone Electronics	7229-5	Jackscrew, Nuts and Washers 0.187" Hex 4-40 x 0.25"L (10 pcs. set) For D-Sub Connectors	4-40	Jackscrew (set)	0.25	0.187	Steel	\$0.95
2179438	SPC Technology	SPC15168	Slotted Metal Knurled Thumbscrew, 4-40 x 2.83"L (2 pack) For D-Sub Connectors	4-40	Knurl Thumbscrew (set)	2.83	0.164	Steel	\$0.89
125015	Jameco Valuepro	GTW520-R	Slotted Plastic Knurled Thumbscrew, 4-40 x 1.63"L (1 pc.) For D-Sub Connectors	4-40	Knurl Thumbscrew	1.63	0.27	Steel	\$0.59
175636	Jameco Valuepro	2052-440-S-0/CIC	Standoff 0.187" Hex 4-40 x 0.187" Female Chrome (1 pc.) For D-Sub Connectors	4-40	Hex Standoff	0.187	0.187	Steel	\$0.45

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Thread Size	Product Type	Length (inch)	Thickness (in.)	Material	Price 1
102796	Jameco Valuepro	14-552-R	Standoff 0.195" Hex 4-40 x 0.235"L Female Brass Nickel (1 pc.) For D-Sub Connectors	4-40	Hex Standoff	0.235	0.195	Steel	\$0.29