



[Click Here to Request a Large Quantity Quote](#)

[Interface-Motor / Motion Control](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Supplier Package	Maximum Operating Current	Minimum Operating Supply Voltage	Typical Operating Supply Voltage	Maximum Operating Supply Voltage	Price 1
2179016	Major Brands	A3958SB	IC A3958SB Dmos Full-Bridge PWM Motor Driver 50V 2A	DIP-24	20 uA	4.5 V	5 V	5.5 V	\$1.95
2308359	TI	ADXL345BCCZ	Accelerometer Digital 3-Axis +/-2g to 16g LGA-14	LGA-14	140 uA	2 V	2.5 V	3.6 V	\$4.95
2179147	Major Brands	BA6220	General Purpose DC Motor Control Governor	DIP-8	800 uA	3.5 V	-	16 V	\$0.29
2299623	Infineon Technologies AG	IR2153	Self-Oscillating Half-Bridge Gate Driver Synchronous 600V DIP-8	DIP-8	5 mA	10 V	-	15.6 V	\$1.59
323934	Saelig-Kerr	KAE-T0V10-DP	IC KAE-T0V10-DP DC Motor Servo Controller (RS232,RS485 or RS422)	DIP-28	n/a	5 V	5 V	5 V	\$30.00
2134432	Saelig-Kerr	KAE-T0V10-SO	IC KAE-T0V10-SO Servo Motion Control Chip (RS232,RS485 or RS422) SMD	SOIC-28	n/a	5 V	5 V	5 V	\$30.00
1341966	National Semiconductor	L293DNE	IC L293DNE Quadruple Half-H Drivers 4.5-to-36V 600mA	DIP-16	24 mA	4.5 V	7 V	36 V	\$3.59
1991563	STMicroelectronics	L293E	Bipolar Motor Driver Parallel PowerDIP-20	PowerDIP-20	24 mA	4.5 V	-	36 V	\$3.09
1342011	National Semiconductor	L293NE	IC L293NE Quadruple Channel Motor Driver 4.5-to-36V 1A	DIP-16	24 mA	4.5 V	7 V	36 V	\$3.59
288067	STMicroelectronics	L297	IC L297/1 Stepper Motor Controller 7V 80mA	DIP-20	80 mA	4.75 V	5 V	7 V	\$7.95
245403	STMicroelectronics	L298N	IC L298N Quaddruple Half-H Drivers 36V 600mA	Multiwatt15	3 A	2.5 V	5 V	46 V	\$3.75
288104	STMicroelectronics	L6203	IC L6203 DMOS Full Bridge Motor Driver 48V 5A	Multiwatt11	5 A	12 V	36V	48 V	\$6.95
1054684	National Semiconductor	SN754410NE	IC 754410NE Quadruple Half-H Driver 4.5-to-36V 1A	DIP-16	1 A	4.5 V	5 V	5.5 V	\$2.49
2285975	On Semiconductor	UC3843BN	IC UC3843BN High Performance Current Mode PWM Controller 30V 1A	DIP-8	30 mA	2.42 V	2.5 V	2.58 V	\$0.69