



[Click Here to Request a Large Quantity Quote](#)

[Dipped Mica Capacitors](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Capacitance (pF)	Voltage Rating	Tolerance	Maximum Operating Temperature	Width	Height	Depth	Lead Pitch	Price 1	Price 10
15991	Jameco Valuepro	DM15CD100D03	10	500 VDC	5%	125°C	11 mm	4 mm	9 mm	5.8 mm	\$1.79	\$1.39
2296719	Cornell Dubilier	DM150	15	500 VDC	5%	125°C	10.9 mm	3.6 mm	7.1 mm	3.6 mm	\$1.35	\$1.15
2296727	Cornell Dubilier	DM180	18	500 VDC	5%	125°C	10.9 mm	3.6 mm	7.1 mm	3.6 mm	\$1.49	\$1.25
16037	Jameco Valuepro	CD15ED220JO3F	22	500 VDC	5%	125°C	11 mm	4 mm	9 mm	5.8 mm	\$1.49	\$1.25
2296735	Cornell Dubilier	DM240	24	500 VDC	5%	125°C	10.9 mm	3.6 mm	7.1 mm	6 mm	\$1.49	\$1.25
2296743	Cornell Dubilier	DM270	27	500 VDC	5%	125°C	10.9 mm	3.6 mm	7.1 mm	6 mm	\$1.49	\$1.25
2313615	Cornell Dubilier	CD15ED300J03F	30	500 VDC	5%	125°C	11.4 mm	4.3 mm	9.1 mm	5.9 mm	\$1.75	\$1.49
2314951	Cornell Dubilier	CD5EC330G03	33	300 VDC	2%	125°C	6.9 mm	3.3 mm	5.1 mm	3 mm	\$2.95	\$2.49
2296751	Cornell Dubilier	DM330	33	500 VDC	5%	125°C	10.9 mm	3.6 mm	7.1 mm	6 mm	\$1.49	\$1.25
2296759	Cornell Dubilier	DM360	36	500 VDC	5%	125°C	10.9 mm	3.6 mm	7.1 mm	6 mm	\$1.49	\$1.25
2314943	Cornell Dubilier	CD5EC430G03	43	300 VDC	2%	125°C	6.9 mm	3.6 mm	5.3 mm	3 mm	\$2.95	\$2.75
2314599	General Instruments	CM05ED430J03	43	500 VDC	5%	125°C	11 mm	4 mm	9 mm	6 mm	\$1.95	\$1.75
16096	Jameco Valuepro	DM15ED470J03	47	500 VDC	5%	125°C	11 mm	4 mm	9 mm	5.8 mm	\$1.59	\$1.25
2296775	Cornell Dubilier	DM510	51	500 VDC	5%	125°C	10.9 mm	3.6 mm	7.1 mm	6 mm	\$1.49	\$1.25
2296783	Cornell Dubilier	DM560	56	500 VDC	5%	125°C	10.9 mm	3.6 mm	7.1 mm	6 mm	\$1.49	\$1.25
2314935	Cornell Dubilier	CD10ED680J03	68	500 VDC	5%	125°C	9.4 mm	5.1 mm	8.6 mm	3.6 mm	\$1.79	\$1.59
2314927	Cornell Dubilier	CD10ED750G03	75	500 VDC	2%	125°C	9.4 mm	5.1 mm	8.6 mm	3.6 mm	\$1.95	\$1.59
2320711	Cornell Dubilier	CM04ED820JO3	82	500 VDC	5%	125°C	9.4 mm	5.1 mm	8.9 mm	3.6 mm	\$1.95	\$1.59
2296543	Cornell Dubilier	CDS10FD910JO3	91	500 VDC	5%	125°C	3.3 mm	6.6 mm	7.9 mm	3.6 mm	\$1.79	\$1.39
16002	Jameco Valuepro	CD15FD101J03	100	500 VDC	5%	125°C	11 mm	4 mm	9 mm	6 mm	\$1.95	\$1.59
2314959	Cornell Dubilier	CD10FD131J03	130	500 VDC	5%	125°C	9.7 mm	5.1 mm	9.4 mm	6.6 mm	\$1.49	\$1.25
2296703	Arndt Electronics	DM15FA151G03	150	100 VDC	2%	125°C	6.3 mm	4 mm	4 mm	3.2 mm	\$1.95	\$1.59
2306951	Cornell Dubilier	CD15FD151JO3	150	500 VDC	5%	125°C	11.7 mm	9.4 mm	4.8 mm	6 mm	\$1.95	\$1.59
2306959	Cornell Dubilier	CD15FD181GO3F	180	500 VDC	2%	125°C	11.7 mm	9.4 mm	4.8 mm	6 mm	\$2.49	\$2.25
2314575	General Instruments	CM05FD181J03	180	500 VDC	5%	125°C	11.7 mm	9.4 mm	4.8 mm	6 mm	\$1.95	\$1.75
2320719	Arndt Electronics	DM-15-201-J	200	500 VDC	5%	125°C	11.7 mm	4.8 mm	9.7 mm	6 mm	\$1.95	\$1.59
2306831	Cornell Dubilier	CM05FD221K03	220	500 VDC	1%	125°C	11.7 mm	5.1 mm	9.7 mm	6 mm	\$1.95	\$1.59

Jameco Part #	Manufacturer	Manufacturer Part #	Capacitance (pF)	Voltage Rating	Tolerance	Maximum Operating Temperature	Width	Height	Depth	Lead Pitch	Price 1	Price 10
2306823	Cornell Dubilier	CD15FD221J03F	220	500 VDC	5%	125°C	11.7 mm	5.1 mm	9.7 mm	6 mm	\$2.79	\$2.29
2306967	Cornell Dubilier	CD15FD241JO3	240	500 VDC	5%	125°C	11.7 mm	9.7 mm	5.1 mm	6 mm	\$1.95	\$1.59
2320703	Cornell Dubilier	CM05FD271FO3	270	500 VDC	1%	125°C	11.9 mm	5.3 mm	9.9 mm	5.9 mm	\$1.95	\$1.59
2320903	Cornell Dubilier	CMD5ED271JO3	270	500 VDC	5%	125°C	11.7 mm	9.7 mm	5.1 mm	6 mm	\$1.95	\$1.59
2306975	Cornell Dubilier	CD15FD301G03	300	500 VDC	2%	125°C	11.9 mm	9.9 mm	5.3 mm	6 mm	\$2.49	\$2.25
16088	Jameco Valuepro	DM331	330	500 VDC	5%	125°C	11 mm	4 mm	9 mm	6 mm	\$2.79	\$2.29
2306983	Cornell Dubilier	CD15FD391JO3	390	500 VDC	5%	125°C	11.9 mm	9.9 mm	5.3 mm	6 mm	\$1.95	\$1.59
16109	Jameco Valuepro	DM471	470	500 VDC	5%	125°C	11 mm	4 mm	9 mm	6 mm	\$2.95	\$2.59
2296655	Cornell Dubilier	CDV19FF821J03	820	1000 VDC	5%	125°C	16 mm	3.8 mm	12 mm	8.9 mm	\$2.95	\$2.59
2314543	General Instruments	CM06ED821J03	820	500 VDC	5%	125°C	16. mm	3.8 mm	12 mm	8.7 mm	\$3.95	\$3.59
16011	Cornell Dubilier	DM15FA102J03	1000	100 VDC	5%	125°C	11 mm	4 mm	9 mm	5.8 mm	\$2.95	\$2.59
2306991	Cornell Dubilier	CD19FD122JO3	1200	500 VDC	5%	125°C	16.8 mm	13.2 mm	5.6 mm	5.8 mm	\$3.95	\$3.59
2314607	General Instruments	CM06FD132J03	1300	500 VDC	5%	125°C	16 mm	3.8 mm	12 mm	8.7 mm	\$4.95	\$4.49
2296791	Cornell Dubilier	DM222	2200	100 VDC	5%	125°C	5.5 mm	11 mm	4.1 mm	6 mm	\$2.95	\$2.59
2314551	General Instruments	CM06FD242J03	2400	500 VDC	5%	125°C	16. mm	3.8 mm	12 mm	8.7 mm	\$3.95	\$3.59
2314591	General Instruments	CM06FD272J03	2700	500 VDC	5%	125°C	16 mm	3.8 mm	12 mm	8.7 mm	\$4.95	\$4.49
2314583	General Instruments	CM05FD302J03	3000	500 VDC	5%	125°C	11.7 mm	9.4 mm	4.8 mm	6 mm	\$4.95	\$4.49
2296799	Cornell Dubilier	DM332	3300	100 VDC	5%	125°C	4.5 mm	7.2 mm	4 mm	6 mm	\$2.95	\$2.59
2296807	Cornell Dubilier	DM472	4700	100 VDC	5%	125°C	18.5 mm	9.5 mm	5 mm	6 mm	\$3.95	\$3.59
2314559	General Instruments	CM06FD682F03	6800	500 VDC	1%	125°C	16. mm	3.8 mm	12 mm	8.7 mm	\$4.95	\$4.49