



[Click Here to Request a Large Quantity Quote](#)

Electrolytic Axial Capacitors

Jameco Part #	Manufacturer	Manufacturer Part #	Capacitance (uF)	Construction	Voltage (VDC)	Tolerance (%)	Size	Operating Temperature-Max (Cel)	Mounting	Price 1	Price 10
<a href="#">10866</a>	Jameco Valuepro	A1/50	1	Axial	50	20	5 x 12 mm	85	Through Hole	\$0.59	\$0.39
<a href="#">93569</a>	Jameco Valuepro	A2.2/50	2.2	Axial	50	20	6 x 13 mm	85	Through Hole	\$0.59	\$0.39
<a href="#">11076</a>	Jameco Valuepro	A4.7/50	4.7	Axial	50	20	6 x 13 mm	85	Through Hole	\$0.59	\$0.39
<a href="#">2235786</a>	NIC Components	R6.8/50	6.8	Axial	50	20	5 x 11	85	Through Hole	\$0.10	\$0.05
<a href="#">1946199</a>	Jameco Valuepro	A10/16	10	Axial	16	20	4 x 7 mm	85	Through Hole	\$0.59	\$0.49
<a href="#">10882</a>	Jameco Valuepro	A10/50	10	Axial	50	20	6 x 12 mm	85	Through Hole	\$0.75	\$0.59
<a href="#">2296559</a>	Cornell Dubilier	600D106F250DG4	10	Axial	250	-10/+50	9.5 x 35	125	Through Hole	\$4.95	\$4.49
<a href="#">331425</a>	Jameco Valuepro	AB10/450-R	10	Axial	450	20	13 x 25 mm	85	Through Hole	\$1.75	\$1.49
<a href="#">199268</a>	Jameco Valuepro	EA2225H613-R	22	Axial	25	20	6 x 12.5 mm	85	Through Hole	\$0.59	\$0.39
<a href="#">2202520</a>	Spectrol/Vishay Corporation	A22/35/105	22	Axial	35	20	6.5 x 10.5 mm	105	Through Hole	\$0.75	\$0.55
<a href="#">10997</a>	Illinois Capacitor	A22/50	22	Axial	50	20	6 x 12	85	Through Hole	\$0.75	\$0.55
<a href="#">331433</a>	Jameco Valuepro	AB22/450-R	22	Axial	450	20	16 x 26 mm	85	Through Hole	\$1.75	\$1.49
<a href="#">135319</a>	Jameco Valuepro	A47/25	47	Axial	25	20	6.5 x 17 mm	85	Through Hole	\$0.75	\$0.55
<a href="#">11105</a>	Jameco Valuepro	A47/50	47	Axial	50	20	8 x 16 mm	85	Through Hole	\$0.69	\$0.59
<a href="#">199188</a>	Jameco Valuepro	EA10016H613-R	100	Axial	16	20	6 x 12.5 mm	85	Through Hole	\$0.75	\$0.55

Jameco Part #	Manufacturer	Manufacturer Part #	Capacitance (uF)	Construction	Voltage (VDC)	Tolerance (%)	Size	Operating Temperature-Max (Cel)	Mounting	Price 1	Price 10
<a href="#">93551</a>	Jameco Valuepro	A100/35	100	Axial	35	20	8 x 16 mm	85	Through Hole	\$0.79	\$0.65
<a href="#">10911</a>	Jameco Valuepro	A100/50	100	Axial	50	20	8 x 20 mm	85	Through Hole	\$0.89	\$0.79
<a href="#">331417</a>	Jameco Valuepro	AB100/250-R	100	Axial	250	20	16 x 32 mm	85	Through Hole	\$2.95	\$2.59
<a href="#">11019</a>	Jameco Valuepro	A220/50-VP-R	220	Axial	50	20	10 x 17 mm	85	Through Hole	\$0.79	\$0.69
<a href="#">2234943</a>	Illinois Capacitor	A330/50	330	Axial	50	20	10 x 25.5 mm	85	Through Hole	\$0.39	\$0.29
<a href="#">2235794</a>	Matsushita Electronic Comp.	A470/16	470	Axial	16	20	8 x 21	85	Through Hole	\$0.25	\$0.19
<a href="#">199381</a>	Jameco Valuepro	EA47035H1321-R	470	Axial	35	20	10 x 21 mm	85	Through Hole	\$1.39	\$1.19
<a href="#">11123</a>	Jameco Valuepro	A470/50-VP-R	470	Axial	50	20	13 x 21 mm	85	Through Hole	\$1.35	\$1.19
<a href="#">2215689</a>	Arndt	T200V680UF	680	Axial	200	20	25 x 51	85	Through Hole	\$2.95	\$2.59
<a href="#">10954</a>	Jameco Valuepro	A1000/25	1000	Axial	25	20	13 x 26 mm	85	Through Hole	\$1.25	\$1.09
<a href="#">93649</a>	Jameco Valuepro	A1000/35	1000	Axial	35	20	13 x 31.5 mm	85	Through Hole	\$1.75	\$1.59
<a href="#">147256</a>	Jameco Valuepro	A1000/50	1000	Axial	50	20	16 x 32 mm	85	Through Hole	\$3.49	\$2.95
<a href="#">11033</a>	Jameco Valuepro	A2200/16	2200	Axial	16	20	16 x 30 mm	105	Through Hole	\$1.95	\$1.75
<a href="#">93658</a>	Jameco Valuepro	A2200/35-R	2200	Axial	35	20	16 x 30 mm	85	Through Hole	\$1.49	\$1.25
<a href="#">2229520</a>	Arndt	A220UF-50V	2200	Axial	50	20	16 x 31	85	Through Hole	\$0.89	\$0.79
<a href="#">199479</a>	Jameco Valuepro	EA220050H1836-R	2200	Axial	50	20	18 x 33 mm	85	Through Hole	\$3.95	\$3.59
<a href="#">2144972</a>	Jameco Valuepro	A3300/16	3300	Axial	16	20	16 x 26	85	Through Hole	\$2.49	\$2.25
<a href="#">199487</a>	Jameco Valuepro	EA330050H2042-R	3300	Axial	50	20	22 x 43 mm	85	Through Hole	\$3.59	\$3.29

Jameco Part #	Manufacturer	Manufacturer Part #	Capacitance (uF)	Construction	Voltage (VDC)	Tolerance (%)	Size	Operating Temperature-Max (Cel)	Mounting	Price 1	Price 10
<a href="#">2229538</a>	Arndt	A4700/16	4700	Axial	16	20	16 x 36	85	Through Hole	\$2.95	\$2.59
<a href="#">93673</a>	Jameco Valuepro	140-TEA472M1EBK1837P	4700	Axial	25	20	18 x 37	85	Through Hole	\$3.25	\$2.95
<a href="#">158650</a>	Jameco Valuepro	HONJU A4700A25	4700	Axial	25	20	22 x 40	85	Through Hole	\$3.69	\$3.39
<a href="#">158811</a>	Jameco Valuepro	A4700A50-R	4700	Axial	50	20	25 x 43 mm	85	Through Hole	\$2.95	\$2.59
<a href="#">93681</a>	Jameco Valuepro	A10000/16	10000	Axial	16	20	22 x 21 mm	85	Through Hole	\$3.95	\$3.59
<a href="#">2215671</a>	Arndt	16V22000	22000	Axial	16	20	25 x 61	85	Through Hole	\$6.95	\$6.25