



[Click Here to Request a Large Quantity Quote](#)

[LED Displays-Dot-Matrix](#)

Jameco Part #	Manufacturer	Manufacturer Part #	LED Display Type	Matrix Pattern	Illuminated Color	Dot Size	Dimensions	Color	Configuration	Dominant Wavelength	Luminous Intensity	Typical Forward Voltage	Price 1
2276423	Lite-On Electronics	LTP2657AA	Dot Matrix	5x7	Bi-Color Red/Green	0.200"	2.09"L x 1.50"W	Grey	CC/AR	621nm, 569nm	4.8 mcd	2V	\$1.49
2005497	Lite-On Electronics	LTP-757G	Dot Matrix	5x7	Green	0.078"	0.70"L x 0.50"W	Grey	CC/AR	565nm	2.0 mcd	2.1V	\$1.25
2280807	Hewlett Packard	HDSP-L203	Dot Matrix	5x7	Hi-Efficiency Red	0.078"	0.70"L x 0.50"W	Grey	CC/AR	645nm	0.93 mcd	2.6V	\$0.99
2280399	Para Light	C-3571E	Dot Matrix	5x7	Hi-Efficiency Red	0.118"	1.25"L x 0.89"W	Grey	CC/AR	630nm	3.0 mcd	2V	\$1.75
2186048	Arndt Electronics	LTP2558AA	Dot Matrix	5x8	Bi-Color Red/Green	0.200"	2.4"L x 1.5"W	Grey	CC/AR	621nm, 569nm	4.8 mcd	2V	\$1.95
2306319	Super Bright	SBM-2388ASRG-GR	Dot Matrix	8x8	Bi-Color Green/Red	0.200"	2.38"L x 2.38"W x 0.37"H	Grey	CC/AR	573nm, 635nm	15 mcd, 7.5 mcd	2.15V, 1.8V	\$1.95
2306311	Super Bright	SBM-2388ASRG-RG	Dot Matrix	8x8	Bi-Color Red/Green	0.200"	2.38"L x 2.38"W x 0.37"H	Grey	CC/AR	635nm, 573nm	7.5 mcd, 15 mcd	1.8V, 2.15V	\$1.25
2132349	Jameco Valuepro	LD788BS-SS22	Dot Matrix	8x8	Hi-Efficiency Red	0.075"	0.78"L x 0.78"W	Black	CC/AR	631nm	25.9 mcd	2.01V	\$2.95
2309871	Adafruit Industries	1487	Dot Matrix	8x8	RGB (24-bit)	0.157"	2.75"L x 2.75"W x 0.13"H	RGB	NeoPixel	Variable	1000 mcd	5V	\$29.95
2306335	Light Key	LM15088BUY	Dot Matrix	8x8	Yellow	0.146"	1.5"L x 1.5"W x 0.41"H	Grey	CC/AR	595nm	45 mcd	2V	\$1.95
2320671	BROADCOM CORPORATION	HCMS-3964	Dot Matrix 4 Character	5x7	Orange	0.1" x 0.18" (4)	0.85"L x 0.45"W x 0.21"H	Black	CR/AC	592nm	128 mcd	3.3V	\$14.95
1551269	Avago Technologies	HDSP-2532	Dot Matrix 8 Character	5x7	Hi-Efficiency Red	0.1" x 0.18" (8)	1.69"L x 0.45"W x 0.21"H	High Efficiency Red	8-Bit	626nm	7.5 mcd	5V	\$49.95
2320679	BROADCOM CORPORATION	HCMS-3914	Dot Matrix 8 Character	5x7	Orange	0.1" x 0.15" (8)	1.40"L x 0.40"W x 0.20"H	Black	CR/AC	592nm	128 mcd	3.3V	\$24.95
32951	TI	TIL311	Hexadecimal Dot Matrix	4x7	Red	0.024"	0.76"L x 0.42"W x 0.14"H	Red	CG	660nm	0.1 mcd	5V	\$29.95