



[Click Here to Request a Large Quantity Quote](#)

[Audio Components-Buzzers](#) [Magnetic](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Frequency (Hz)	Operating Voltage (Vp-p/mA)	Voltage Range (Vp-p)	Sound (dB)	Size (H" x Dia.)	Price 1
<a href="#">140695</a>	Jameco Valuepro	63S1120LFLFLA	400	12/25	9 to 15	75	.60 x 1.3	\$1.79
<a href="#">2302415</a>	Jameco Valuepro	EMX-6B06L	400	6/20	4 to 12	90	.69 x 1.61	\$1.95
<a href="#">2302447</a>	Jameco Valuepro	AST-02308MR-R	1500	6/16	3 to 8	75	.33 x .91	\$1.95
<a href="#">2222408</a>	Jameco Valuepro	DB111FLF-PN	2048	1.5/15	1 to 5	80	.33 x .47	\$0.65
<a href="#">2222387</a>	Jameco Valuepro	TDB12LF-PN	2300	12/30	8 to 15	85	.37 x .47	\$1.09
<a href="#">76065</a>	Jameco Valuepro	TDB05LFPN	2300	5/30	4 to 7	85	.35 x .46	\$1.75
<a href="#">2286407</a>	CUI	CEM-1205C	2300	5/35	6 to 16	92	.37 x .47	\$1.49
<a href="#">2286415</a>	CUI	CEM-1212C	2300	8/16	8 to 16	85	.37 x .47	\$1.25
<a href="#">2222441</a>	Jameco Valuepro	DBX12LF-PN	2400	12/40	6 to 15	85	.35 x .47	\$0.99
<a href="#">138740</a>	Jameco Valuepro	DBX05LF-PN-R	2400	5/40	3 to 8	85	.35 x .46	\$1.09
<a href="#">2314279</a>	AATC	AC-1205G-N1LF	2400	5/40	4 to 8	85	.40 x .48	\$0.79
<a href="#">2302431</a>	Jameco Valuepro	EMX-7T06P	2400	6/40	4 to 8	86	.37 x .47	\$0.99
<a href="#">2222416</a>	Jameco Valuepro	MDB03BFLF-PN	2700	3/30	2 to 5	80	.20 x .37	\$1.95
<a href="#">2302471</a>	Jameco Valuepro	CB-09AW25	2730	5/70	2 to 5	85	.20 x .35	\$0.59
<a href="#">2222424</a>	Jameco Valuepro	CDX094A3BOLF-PP	2731	3/100	2 to 5	80	.20 x .37	\$0.55