



[Click Here to Request a Large Quantity Quote](#)

Metallized Polyester Film Mylar Capacitors

Jameco Part #	Manufacturer	Manufacturer Part #	Capacitance (uF)	Voltage (VDC)	Tolerance (%)	Size (L x W x T) mm	Lead Pitch - mm	Price 1	Price 10
26833	Jameco Valuepro	MY.001	0.001	100	10	9.5 x 4.5 x 2.1	2.9	\$0.35	\$0.25
2280463	NIC Components	NRP102K600	0.001	600	10	7.9 x 11.9 x 4.8	9.4	\$0.39	\$0.29
2159808	EPCOS	B32693A3152J-20	0.0015	2500	5	9.3 x 26 x 6	21.7	\$0.49	\$0.35
1946164	Jameco Valuepro	MY.0068	0.0068	100	10	10.1 x 5.5 x 2.7	3.8	\$0.35	\$0.29
2301263	Jameco Valuepro	ST12D103F	0.01	100	1	6.6 Dia x 12.7 W	12.85	\$0.29	\$0.25
26884	Jameco Valuepro	MY.01	0.01	100	10	8.6 x 5.2 x 2.7	3.4	\$0.39	\$0.29
2289903	Jameco Valuepro	MY.01/680	0.01	630	10	9.2 x 12.9 x 3.9	9.7	\$0.59	\$0.49
2280007	Cornell Dubilier	DMT2S123J	0.012	250	10	7.5 x 12.3 x 4.7	9.4	\$0.39	\$0.35
2302127	Cornell Dubilier	WMC08S15K-F	0.015	80	10	4.0 Dia x 11.4 W	11.76	\$0.25	\$0.17
207837	Jameco Valuepro	MY.018/50	0.018	50	10	11.3 x 5.5 x 3.4	3.6	\$0.29	\$0.19
2289871	Jameco Valuepro	MY0.022/50	0.022	50	5	10.8 x 6.7 x 3.8	4.6	\$0.29	\$0.25
26905	Jameco Valuepro	MY.022	0.022	100	10	7.2 x 11.2 x 3.6	9.3	\$0.39	\$0.29
2280015	Jameco Valuepro	MY.022/250	0.022	250	5	6.9 x 9.6 x 3.8	7.5	\$0.39	\$0.35
26921	Jameco Valuepro	MY.033	0.033	100	10	7.9 x 11.4 x 4.6	9.5	\$0.39	\$0.29
26930	Jameco Valuepro	MY.047	0.047	100	10	11.2 x 8.3 x 3.6	5.7	\$0.45	\$0.35
2236560	Jameco Valuepro	MPP473K/400	0.047	400	10	10.3 x 16 x 5.3	14	\$0.65	\$0.49
2280343	Vishay	BFC-238320473	0.047	630	5	11.8 x 17.5 x 5.8	14.1	\$1.95	\$1.75
1946172	Jameco Valuepro	MY.068	0.068	100	10	11.3 x 8.8 x 4.2	6.5	\$0.39	\$0.25
2261351	Jameco Valuepro	MER104J1HA0	0.1	50	5	7.9 x 6.8 x 4.2	4.8	\$0.45	\$0.29
26956	Jameco Valuepro	MY.1	0.1	100	10	9.8 x 9.0 x 5.1	4.7	\$0.49	\$0.39
93921	Jameco Valuepro	MY.1/250	0.1	250	10	7.2 x 11.5 x 4.6 / 7.6 x 12 x 4.5	9.5 / 9.5	\$0.29	\$0.19
2289887	Jameco Valuepro	MFA104K/250	0.1	250	10	8.7 x 14.9 x 5.3	14.5	\$0.49	\$0.39
2236586	Jameco Valuepro	MPP104K/400	0.1	400	10	11.4 x 16.8 x 6.1	14.5	\$0.69	\$0.59
1983424	Panasonic	ECQ-E6104KF	0.1	630	10	10.7 x 16.9 x 4.9	14.8	\$0.49	\$0.35
2280247	Philips Semiconductor	MKT365.18	0.18	100	10	7.2 x 9.6 x 4.5	4.8	\$0.25	\$0.15
920561	Panasonic	ECQ-V1H224JL	0.22	50	5	4.9 x 6.8 x 3.8	5	\$0.45	\$0.35
2203101	Jameco Valuepro	MY.22K	0.22	100	10	16 x 12.7 x 7.4	10	\$0.65	\$0.45

Jameco Part #	Manufacturer	Manufacturer Part #	Capacitance (uF)	Voltage (VDC)	Tolerance (%)	Size (L x W x T) mm	Lead Pitch - mm	Price 1	Price 10
26972	Jameco Valuepro	MY.22	0.22	100	10	7.6 x 9.2 x 4.8 / 11.8 x 10.9 x 5.6	4.7 / 7.2	\$0.79	\$0.69
2236607	Jameco Valuepro	MPP224K/400	0.22	400	10	11.4 x 23 x 6	20.7	\$0.69	\$0.59
2217351	Panasonic	ECQ-E6224JF	0.22	630	10	14.8 x 17.3 x 7.9	14.1	\$0.99	\$0.79
2208930	Nichicon	QXJ2J224KTPT	0.22	630	10	15 x 23.5 x 6.8	20.7	\$0.79	\$0.65
2280047	Vishay	MKP1841422135	0.22	1600	10	31.6 x 41.5 x 17.6	37	\$2.95	\$2.59
2289879	Jameco Valuepro	MFA334K/250	0.33	250	10	10.3 x 22.1 x 4.7	22.21	\$0.79	\$0.69
93964	Jameco Valuepro	MY.33/250	0.33	250	10	11.2 x 12.8 x 6.6	10.2	\$0.69	\$0.55
2236973	Jameco Valuepro	MER474J1HA0	0.47	50	5	8.1 x 6.9 x 4.5	4.8	\$0.89	\$0.75
26999	Jameco Valuepro	MY.47	0.47	100	10	9.3 x 9.6 x 5.7	7.3	\$0.89	\$0.75
2302239	Jameco Valuepro	MY.47/100/5	0.47	100	5	14.6 x 12.8 x 6.8	7.2	\$0.65	\$0.55
2280063	Wima	MKC-10-0.47/250V/5%	0.47	250	5	17.8 x 26.6 x 8.3	21.7	\$1.29	\$1.09
2236623	Jameco Valuepro	MPP474K/400	0.47	400	10	15.5 x 28.7 x 8.5	26.5	\$0.79	\$0.69
27001	Jameco Valuepro	MY1	1	100	10	10.3 x 6.4 x 5.9 / 12.7 x 11.2 x 4.4	4.5 / 8.8	\$0.85	\$0.69
2192691	Tecate Group	2101-1K0-155KF	1.5	1000	10	26.2 Dia x 56 W	56.27	\$0.99	\$0.85
93999	Jameco Valuepro	MY2.2/250	2.2	250	10	14.5 x 24.4 x 7.3	21.8	\$1.19	\$1.05
2129852	Vishay	ECQ-E1685KZ	6.8	100	10	18.8 x 27.7 x 10.8	26.1	\$1.19	\$1.05