

[Click Here to Request a Large Quantity Quote](#)

[Diodes & Rectifiers-Diodes Zener](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Package	Nominal Zener Voltage	Maximum Power Dissipation (W)	Zener Voltage Tolerance	Test Current	Price 1
804754	On Semiconductor	1N5349BG	Zener Diode 1N5349BG 12 Volt 5% 5W	017AA	12	5	5%	100 mA	\$0.45
743592	On Semiconductor	1N5355BG	Zener Diode 1N5355 18 Volt 5% 5W	017AA	18	5	5%	65 mA	\$0.45
804914	NXP Semiconductors	1N5359BG	Zener Diode 1N5359BG 24 Volt 5% 5W	017AA	24	5	5%	50 mA	\$0.47
2286703	Major Brands	BZW06-13	TVS Diode 27.2V Clamp 147A (8/20us) Ipp Through Hole DO-15	DO-15	13	600	5%	1 mA	\$0.39
2286223	Major Brands	1N5250BRL	20V 500mW Zener Diode DO-204 Through Hole	DO-204	20	0.5	5%	6.2 mA	\$0.25
179098	Fairchild Semiconductor	1N5242B	Zener Diode 1N5242B 12 Volt 5% 500mw	DO-35	12	0.5	5%	20 mA	\$0.25
2286511	Vishay	BZX55C18	16.8V 500mW Zener Diode DO-35 Through Hole	DO-35	16.8	0.5	5%	5 mA	\$0.25
782971	Fairchild Semiconductor	1N5221B	Zener Diode 1N5221B 2.4Volt 500mW 5%	DO-35	2.4	0.5	5%	20 mA	\$0.25
2286191	Motorola	1N5223BRL	2.7V 500mW Zener Diode DO-35 Through Hole	DO-35	2.7	0.5	5%	20 mA	\$0.25
784925	Motorola	BZX55C2V7	2.7V 500mW Zener Diode DO-35 Through Hole	DO-35	2.7	0.5	5%	5 mA	\$0.25
179004	Major Brands	1N5225B	Zener Diode 1N5225B 3 Volt 5% 500mw DO-35	DO-35	3	0.5	5%	20 mA	\$0.25
743488	Fairchild Semiconductor	1N5226B	Zener Diode 1N5226B 3.3 Volt 5% 500mW	DO-35	3.3	0.5	5%	20 mA	\$0.25
783009	Fairchild Semiconductor	1N5228B	Zener Diode 1N5228B 3.9 Volt 5% 500mW	DO-35	3.9	0.5	5%	20 mA	\$0.25
179039	Major Brands	1N5230B	Zener Diode 1N5230B 4.7 Volt 5% 500mw	DO-35	4.7	0.5	5%	20 mA	\$0.25
2286015	National Semiconductor	BZX55C4V7	4.7V 500mW Zener Diode DO-35 Through Hole	DO-35	4.7	0.5	5%	5 mA	\$0.25
2287751	Motorola	1N5337B	4.7V 5W 5% Zener Diode DO-35 Through Hole	DO-35	4.7	5	5%	260 mA	\$0.25
179047	Major Brands	1N5231B	Zener Diode 1N5231B 5.1 Volt 5% 500mw	DO-35	5.1	0.5	5%	20 mA	\$0.25
36290	Major Brands	1N751A	Zener Diode 1N751A 5.1 Volt 5% 500mw	DO-35	5.1	0.5	5%	20 mA	\$0.39
2286519	Philips Semiconductor	BZX79C7V5	7.5V 500mW Zener Diode DO-35 Through Hole	DO-35	7.5	0.5	5%	5 mA	\$0.225
2286207	Major Brands	BZX55C8V2	8.2V 500mW Zener Diode DO-35 Through Hole	DO-35	8.2	0.5	5%	5 mA	\$0.25
36169	Major Brands	1N4742A	Zener Diode 1N4742A 12 Volt 5% 1W	DO-41	12	1	5%	21 mA	\$0.25

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Package	Nominal Zener Voltage	Maximum Power Dissipation (W)	Zener Voltage Tolerance	Test Current	Price 1
672843	Fairchild Semiconductor	1N4743A	Zener Diode 1N4743A General Purpose 13 Volt 1 Watt	DO-41	13	1	5%	19 mA	\$0.25
36185	Major Brands	1N4744A	Zener Diode 1N4744A 15 Volt 5% 1W	DO-41	15	1	5%	17 mA	\$0.25
782891	Fairchild Semiconductor	1N4746A	Zener Diode 1N4746A 18 Volt 5% 1W	DO-41	18	1	5%	14 mA	\$0.25
2245909	New Jersey Semiconductor	1N4964	18V 5W Glass Zener Diode DO-41	DO-41	18	5	5%	65 mA	\$7.95
178896	Major Brands	1N4748A	22V 1W Zener Diode DO-41 Through Hole	DO-41	22	1	5%	11.5 mA	\$0.25
2245861	New Jersey Semiconductor	1N4473	Zener Diode 1N4473 22V 1.5W 5%	DO-41	22	1.5	5%	11.5 mA	\$4.95
782922	Fairchild Semiconductor	1N4749A	Zener Diode 1N4749 24 Volt 1 Watt 5%	DO-41	24	1	5%	10.5 mA	\$0.25
2245888	New Jersey Semiconductor	1N3824A	4.3V 1W Zener Diode DO-41	DO-41	4.3	1	5%	64 mA	\$5.95
1427031	Vishay	1N4731A	Diode Zener Single 4.3 Volt 5% 1.3W 2-Pin DO-41 Tape and Reel	DO-41	4.3	1.3	5%	58 mA	\$0.29
743349	Fairchild Semiconductor	1N4732A	Diode Zener Single 4.7 Volt 5% 1W 2-Pin DO-41 Bulk	DO-41	4.7	1	5%	53 mA	\$0.25
36097	Major Brands	1N4733A	Zener Diode 1N4733A 5.1 Volt 5% 1Watt	DO-41	5.1	1	5%	49 mA	\$0.25
36118	Major Brands	1N4734A	Zener Diode 1N4734A 5.6V 5% 1W	DO-41	5.6	1	5%	45 mA	\$0.25
36126	Major Brands	1N4735A	Zener Diode 1N4735A Single 6.2 Volt 5% 1 watt	DO-41	6.2	1	5%	41 mA	\$0.25
178837	Major Brands	1N4739A	Zener Diode 1N4739A 9.1 Volt 5% 1W	DO-41	9.1	1	5%	28 mA	\$0.25
2286175	Motorola	1N5948BRL	91V 3W Zener Diode DO-41 Through Hole	DO-41	91	3	5%	4.1 mA	\$0.35
2290719	Vishay	TZMB16-GS08	Zener Diode 16V 500mW 2% Surface Mount SOD-80 MiniMELF	SOD-80	16	0.5	2%	5 mA	\$0.25
2296079	Diodes Incorporated	BZX84C3V0-7	Zener Diode 3V 300mW ±7% Surface Mount SOT-23-3	SOT-23-3	3	0.3	7%	5 mA	\$0.25
2296311	On Semiconductor	NMBZ5V6ALTI	Dual Monolithic Silicon Zener Diode ESD Surge Protector 5.6V 225mW SOT-23	SOT-23-3	5.6	24	5%	20 mA	\$0.25
1579608	Major Brands	1N5350B	Zener Diode 13V 5W 5% Axial Through Hole	T-18	13	5	5%	100 mA	\$0.45
1304840	Major Brands	1N5333B	Zener Diode 3.3V 5W 5% Axial Through Hole	T-18	3.3	5	5%	380 mA	\$0.45
2018811	Major Brands	1N5338B	OP Amp Dual GP ±18V 8-Pin TSSOP	T-18	5.1	5	5%	240 mA	\$0.45