



[Click Here to Request a Large Quantity Quote](#)

Lithium batteries

Jameco Part #	Manufacturer	Manufacturer Part #	Cell Size	Volts (VDC)	Nominal Capacity (mAh)	Chemistry	Size	Termination	Features	Battery Type	Price 1
2287279	Sanyou Electrical	CR14250SE	1/2 AA	3	850	Lithium Manganese Dioxide	0.55"Dia. x 0.99"L	Button Top	Non-Rechargeable	Primary	\$3.49
33371	Tadiran	TL-5101/P	1/2 AA	3.6	950	Lithium-Thionyl Chloride	0.57"Dia. x 0.99"L	Axial Leads	Non-Rechargeable	Primary	\$5.95
263898	Jameco Valuepro	ER14250 W/LEADS	1/2 AA	3.6	1200	Lithium-Thionyl Chloride	0.57"Dia. x 1.00"L	Axial Leads	Non-Rechargeable	Primary	\$5.95
33398	Tadiran	TL-5104/P	AA	3.6	2100	Lithium-Thionyl Chloride	0.57"Dia. x 1.99"L	Axial Leads	Non-Rechargeable	Primary	\$7.29
146114	Tadiran	TL-5104/S	AA	3.6	2100	Lithium-Thionyl Chloride	0.57"Dia. x 1.99"L	Button Top	Non-Rechargeable	Primary	\$6.95
2295711	Renata Batteries	CR2032MFR-RV	CD2032	3	225	Lithium Manganese Dioxide	0.79"Dia. x 0.13"Th (20x3.2mm)	PC mount, vertical	Non-Rechargeable	Primary	\$1.19
2123784	Jameco Valuepro	CR1220	CR1220	3	38	Lithium Manganese Dioxide	0.49"Dia. x 0.08"Th (12x2.0mm)	Pressure Fit	Non-Rechargeable	Primary	\$0.59
2210010	Jameco Valuepro	CR1220/WIRE LEADS	CR1220	3	40	Lithium Manganese Dioxide	0.77"L x 0.49"W x 0.10"Th	2" wire leads	Non-Rechargeable	Primary	\$0.89
240258	Jameco Valuepro	CR123A	CR123A	3	1300	Lithium Manganese Dioxide	0.65"Dia. x 1.36"L	Button Top	Non-Rechargeable	Primary	\$2.25
2238362	Jameco Valuepro	CR2025-LEADS	CR2025	3	160	Lithium Manganese Dioxide	0.79"Dia. x 0.10"Th (20x2.5mm)	2" wire leads	Non-Rechargeable	Primary	\$1.19
2167509	Energizer Batteries	CR2025	CR2025	3	163	Lithium Manganese Dioxide	0.79"Dia. x 0.10"Th (20x2.5mm)	Pressure Fit	Non-Rechargeable	Primary	\$1.75
14162	Renata Batteries	CR2032	CR2032	3	210	Lithium Manganese Dioxide	0.79"Dia. x 0.13"Th (20x3.2mm)	Pressure Fit	Non-Rechargeable	Primary	\$0.79
2223443	Jameco Valuepro	CR2032-LEADS	CR2032	3	220	Lithium Manganese Dioxide	0.79"Dia. x 0.13"Th (20x3.2mm)	2" wire leads	Non-Rechargeable	Primary	\$1.49
2280655	Laird	CR2430F2AW3	CR2430	3	290	Lithium Manganese Dioxide	1.00"Dia. x 0.12"Th (25x3.0mm)	PC mount, vertical	Non-Rechargeable	Primary	\$1.75
2238371	Jameco Valuepro	CR2450-LEADS	CR2450	3	540	Lithium Manganese Dioxide	0.95"Dia. x 0.2"Th (24x5.0mm)	2" wire leads	Non-Rechargeable	Primary	\$1.25

Jameco Part #	Manufacturer	Manufacturer Part #	Cell Size	Volts (VDC)	Nominal Capacity (mAh)	Chemistry	Size	Termination	Features	Battery Type	Price 1
2280663	Laird	CR2450F2MX1HF	CR2450	3	550	Lithium Manganese Dioxide	1.00"Dia. x 0.22"Th (25x5.0mm)	PC mount	Non-Rechargeable	Primary	\$1.95
2158231	Arndt	CR927	CR927	3	30	Lithium Manganese Dioxide	0.37"Dia. x 0.10"Th	Pressure Fit	Non-Rechargeable	Primary	\$0.39
2284631	HCB Battery Co.	CP603146	Flat Pack	3	1950	Lithium Manganese Dioxide	1.81"L x 1.22"W x 0.24"Th	Solder Tab	Non-Rechargeable	Primary	\$9.95