



[Click Here to Request a Large Quantity Quote](#)

[LED Displays-Bar Array](#)

Jameco Part #	Manufacturer	Manufacturer Part #	LED Display Type	Number of LEDs	LED Size	Illuminated Color	Dimensions	Color	Dominant Wavelength	Luminous Intensity	Typical Forward Voltage	Forward Current	Price 1
<a href="#">2314695</a>	Hewlett Packard	HLMP-2400	Bar Graph	1	.35" x .15"	Yellow	0.40"W x 0.195"H	White	583 nm	20 mcd	2.1V	20 mA	\$1.25
<a href="#">2314703</a>	Arndt Electronics	HLMP-2655	Bar Graph	1	.35" x .35"	High-Efficiency Red	0.40"W x 0.40"H	White	634 nm	45 mcd	2V	90 mA	\$1.39
<a href="#">1860467</a>	Hewlett Packard	HLMP2755	Bar Graph	1	.35" x .35"	Yellow	0.40"W x 0.40"H	White	583 nm	70 mcd	2.1V	25 mA	\$1.59
<a href="#">2286095</a>	Agilent Technologies	HLMP-2885	Bar Graph	1	.35" x .75"	Green	0.80"W x 0.40"H	Green Diffused	572 nm	100 mcd	2.2V	25 mA	\$1.49
<a href="#">2281191</a>	Lite-On Electronics	LTL2785Y	Bar Graph	1	.35" x .75"	Yellow	0.794"W x 0.394"H	White	569 nm	16 mcd	2.1V	20 mA	\$1.25
<a href="#">1554259</a>	Hewlett Packard	HLMP-2500	Bar Graph	1	.75" x .15"	Green	0.80"W x 0.195"H	White	565 nm	25 mcd	2.2V	30 mA	\$1.09
<a href="#">2314647</a>	Hewlett Packard	HLMP-2550	Bar Graph	1	.75" x .15"	Green	0.80"W x 0.195"H	White	565 nm	50 mcd	2.2V	20 mA	\$1.49
<a href="#">1554195</a>	Avago Technologies	HLMP-2350	Bar Graph	1	.75" x .15"	Red	0.80"W x 0.195"H	White	635 nm	45 mcd	2V	20 mA	\$1.49
<a href="#">2314687</a>	Hewlett Packard	HLMP-2800	Bar Graph	2	.35" x .15"	Green	0.40"W x 0.40"H	White	565 nm	25 mcd	2.2V	20 mA	\$1.49
<a href="#">2322663</a>	Avago Technologies	HLCP-D100(HLMP-2600)	Bar Graph	2	.35" x .15"	Yellow	0.40"W x 0.40"H	White	645 nm	7.5 mcd	1.8V	20 mA	\$1.95
<a href="#">2314679</a>	Hewlett Packard	HLMP-2870	Bar Graph	2	.35" x .35"	Green	0.794"W x 0.40"H	White	565 nm	50 mcd	2.2V	20 mA	\$1.49
<a href="#">2314711</a>	Arndt Electronics	HLMP-2770	Bar Graph	2	.35" x .35"	Yellow	0.80"W x 0.40"H	White	583 nm	38 mcd	2.1V	20 mA	\$2.95
<a href="#">2314671</a>	Hewlett Packard	HLMP-2720-EF000	Bar Graph	4	.35" x .15"	Yellow	0.794"W x 0.40"H	White	583 nm	20 mcd	2.1V	25 mA	\$1.95
<a href="#">2230619</a>	Sunled Corporation	XGCBDX10D	Bar Graph	10	.20" x .07"	Blue	1.00"W x 0.40"H	Grey	460 nm	9.8 mcd	3V	10 mA	\$2.75

Jameco Part #	Manufacturer	Manufacturer Part #	LED Display Type	Number of LEDs	LED Size	Illuminated Color	Dimensions	Color	Dominant Wavelength	Luminous Intensity	Typical Forward Voltage	Forward Current	Price 1
<a href="#">697469</a>	Lite-On Electronics	LTA-1000G	Bar Graph	10	.20" x .07"	Green	1.00"W x 0.40"H	Grey	565 nm	2 mcd	2.1V	20 mA	\$1.09
<a href="#">2217596</a>	Seed Studios	304080004	Bar Graph	10	.20" x .07"	Green x8/Orange x1/Red x1	1.0"W x 0.40"H	Black	565 nm, 569 nm, 635 nm	n/a	5V	20 mA	\$1.49
<a href="#">334529</a>	Jameco Valuepro	UL10000-HR RRAK	Bar Graph	10	.20" x .07"	Orange	1.00"W x 0.40"H	Orange	635 nm	3.9 mcd	2.1V	20 mA	\$1.39
<a href="#">2318015</a>	Jameco Valuepro	LDA-B10AZX	Bar Graph	10	.20" x .07"	Red	1.00"W x 0.40"H	Black	623 nm	2 mcd	2V	20 mA	\$1.09
<a href="#">697477</a>	Lite-On Electronics	LTA-1000HR	Bar Graph	10	.20" x .07"	Red	1.00"W x 0.40"H	Red	623 nm	2 mcd	2V	25 mA	\$1.25
<a href="#">2227356</a>	Lite-On Electronics	LTA-10102KR	Bar Graph	10	.20" x .07"	Super Red	1.00"W x 0.40"H, 0.6"L pins	Black	639 nm	0.675 mcd	2V	25 mA	\$0.59