



[Click Here to Request a Large Quantity Quote](#)

[Bulk Cable-Multi-Conductor](#)

Jameco Part #	Manufacturer	Manufacturer Part #	No. of Conductors	Wire Gauge (AWG)	Stranding	Shielding	Length (FT)	Color	Material	Cable Type	Frequency (MHz)	Price 1
2119515	Jameco Valuepro	5574-100	2	18	16 x 30	Yes	100	Chrome	PVC	Multi-conductor		\$41.95
2234901	Belden	8442-060-25	2	22	16 x 30	No	25	Chrome	PVC	Audio, Control & Instrumentation		\$12.95
732996	Belden	8442 060100	2	22	7 x 30	No	100	Chrome	PVC	Audio, Control & Instrumentation		\$47.95
733008	Belden	8442 060500	2	22	7 x 30	No	500	Chrome	PVC	Audio, Control & Instrumentation		\$199.95
2310295	Jameco Valuepro	8442 060500-JVP	2	22	7 x 30	No	500	Gray	PVC	Audio, Control & Instrumentation		\$79.95
733112	Belden	8451 010100	2	22	7 x 30	Yes	100	Black	PVC	Line Level Analog Audio		\$34.95
734063	Belden	8451 010U500	2	22	7 x 30	Yes	500	Black	PVC	Line Level Analog Audio		\$136.95
733024	Belden	8443 060100	3	22	7 x 30	No	100	Chrome	PVC	Audio, Control & Instrumentation		\$55.95
733032	Belden	8443 060500	3	22	7 x 30	No	500	Chrome	PVC	Audio, Control & Instrumentation		\$279.95
2119531	Jameco Valuepro	5576-100	3	22	7 x 30	Yes	100	Chrome	PVC	Multi-conductor		\$31.49
2234898	Belden	8723 060 U25	4	22	16 x 30	Yes	25	Chrome	PVC	Audio, Control Interconnect		\$15.95
733059	Belden	8444 060100	4	22	7 x 30	No	100	Chrome	PVC	Audio, Control & Instrumentation		\$64.95
733067	Belden	8444 060500	4	22	7 x 30	No	500	Chrome	PVC	Audio, Control & Instrumentation		\$279.95
734180	Belden	8723 060100	4	22	7 x 30	Yes	100	Chrome	PVC	Audio, Control Interconnect		\$59.95
734184	Belden	8723 060-U500	4	22	7 x 30	Yes	500	Chrome	PVC	Audio, Control Interconnect		\$279.95
644383	Jameco Valuepro	SC4-25	4	24	7 x 30	Yes	25	Gray	PVC	Multi-conductor		\$9.95
644391	Jameco Valuepro	SC4-100	4	24	7 x 30	Yes	100	Gray	PVC	Multi-conductor		\$26.95

Jameco Part #	Manufacturer	Manufacturer Part #	No. of Conductors	Wire Gauge (AWG)	Stranding	Shielding	Length (FT)	Color	Material	Cable Type	Frequency (MHz)	Price 1
644404	Jameco Valuepro	SC4-1000	4	24	7 x 30	Yes	1000	Gray	PVC	Multi-conductor		\$209.95
2119494	Jameco Valuepro	5411-CL	5	22	7 x 30	No	100	Chrome	PVC	Multi-conductor		\$44.95
644631	Jameco Valuepro	GTP501-4P-BL-25VP	8	24	7x32	No	25	Blue	PVC	CAT 5	100	\$4.95
644615	Jameco Valuepro	10X5-804GR-100VP	8	24	7x32	No	100	Blue	PVC	CAT 5e	350	\$19.95
2230897	Jameco Valuepro	10X5-804TH-100	8	24	7x32	No	100	Gray	PVC	CAT 5e	350	\$17.95
644412	Jameco Valuepro	SC9-25	9	24	7 x 30	Yes	25	Gray	PVC	Multi-conductor		\$11.95
644421	Jameco Valuepro	SC9-100	9	24	7 x 30	Yes	100	Gray	PVC	Multi-conductor		\$44.95
644447	Jameco Valuepro	5719-CL-25	15	24	7 x 30	Yes	25	Gray	PVC	Multi-conductor		\$20.95
644455	Jameco Valuepro	5719-CL-100	15	24	7 x 30	Yes	100	Gray	PVC	Multi-conductor		\$62.95
644471	Jameco Valuepro	SC25-25VP	25	24	7 x 30	Yes	25	Gray	PVC	Multi-conductor		\$26.95
644480	Jameco Valuepro	SC25-100VP	25	24	7 x 30	Yes	100	Gray	PVC	Multi-conductor		\$99.95