



[Click Here to Request a Large Quantity Quote](#)

Slide Switches

| Jameco Part # | Manufacturer | Manufacturer Part # | Pins | Contact Form | Switch Function | Current Rating | Size (L" x W" x H") | Lead Spacing (inch) | Housing Material | Price 1 |
|-------------------------|-----------------|---------------------|------|--------------|-----------------|----------------------------|---------------------|---------------------|------------------|---------|
| 2276927 | Apem Components | 25346NA-6X693UL | 3 | DPDT | ON-NONE-ON | 4A@125VAC, 2A@250VAC | 0.56 x 0.47 x 0.70 | 0.1 | Plastic | \$0.49 |
| 2266919 | Mountain Switch | 103-5009-EVX | 3 | SPDT | ON-NONE-(ON) | 5A@120VAC, 2A@250VAC | 0.26 x 0.70 x 0.61 | 0.15 | Metal | \$0.39 |
| 2266879 | Mountain Switch | 103-5003-EV | 3 | SPDT | ON-NONE-ON | 3A@120VAC, 1A@250VAC | 0.55 x 0.49 x 0.40 | 0.1 | Plastic | \$0.49 |
| 2266895 | Mountain Switch | 103-5006-EVX | 3 | SPDT | ON-NONE-ON | 5A@120VAC, 2A@250VAC | 0.77 x 0.26 x 0.61 | 0.18 | Metal | \$0.59 |
| 2266935 | Mountain Switch | 103-5015-EVX | 3 | SPDT | ON-NONE-ON | 5A@120VAC/28VDC | 0.50 x 0.26 x 0.61 | 0.18 | Metal | \$0.59 |
| 2181124 | C&K | S102031MS02QE | 3 | SPDT | ON-OFF | 6A@250VAC | 1.38 x 0.53 x 0.28 | 0.25 | Plastic | \$1.95 |
| 2268231 | Jameco Valuepro | R13-608D1-02-BB5 | 3 | SPDT | ON-OFF-ON | 16@125VAC, 10A@250VAC | 1.47 x 0.88 x 1.05 | 0.28 | Plastic | \$1.49 |
| 2286055 | C&K | 1103M2S3W5QE2 | 3 | SPDT | ON-OFF-ON | 6A@120VAC/28VDC, 3A@250VAC | 0.50 x 1.02 x 0.91 | 0.19 | Metal | \$0.59 |
| 588220 | C&K | OS102011MA1QN1 | 3 | SPDT | ON-ON | 0.2A@30VDC | 0.34 x 0.17 x 0.15 | 0.08 | Metal | \$0.45 |
| 2258831 | Jameco Valuepro | SS-12E17 | 3 | SPDT | ON-ON | 0.3A@125VAC | 0.45 x 0.16 x 0.24 | 0.1 | Metal | \$0.69 |
| 2192384 | Jameco Valuepro | 3450XBB-4 | 3 | SPDT | ON-ON | 0.3A@125VAC | 0.45 x 0.22 x 0.23 | 0.12 | Metal | \$0.59 |
| 2184384 | Jameco Valuepro | SS60012F-0102-4V-NB | 3 | SPDT | ON-ON | 0.3A@125VAC | 0.75 x 0.22 x 0.52 | 0.14 | Metal | \$0.79 |
| 621325 | GC Electronics | 35-202-BU | 3 | SPDT | ON-ON | 0.3A@30VAC | 0.44 x 0.22 x 0.18 | 0.125 | Metal | \$2.25 |
| 2286119 | E Switch | EG1257 | 3 | SPDT | ON-ON | 0.3A@4VDC | 0.30 x 0.08 x 0.20 | 0.06 | Metal | \$0.39 |
| 2133704 | Jameco Valuepro | SS12D02 | 3 | SPDT | ON-ON | 0.3A@50VDC | 0.35 x 0.18 x 0.18 | 0.08 | Metal | \$0.39 |
| 109171 | Jameco Valuepro | SS-12F56-4 | 3 | SPDT | ON-ON | 0.5A@50VDC | 0.22 x 0.45 x 0.23 | 0.16 | Metal | \$0.59 |
| 2268175 | Jameco Valuepro | R13-608C1-02-BB5 | 3 | SPDT | ON-ON | 16@125VAC, 10A@250VAC | 1.47 x 0.88 x 1.05 | 0.28 | Plastic | \$0.59 |
| 2268239 | Jameco Valuepro | R13-608C1-05-BB5 | 3 | SPDT | ON-ON | 16@125VAC, 10A@250VAC | 1.47 x 0.88 x 1.05 | 0.28 | Plastic | \$0.79 |
| 2181061 | NKK Switches | SS-14SDP2 | 4 | SP3T | ON-ON-ON | 0.1A@30VDC | 0.62 x 0.16 x 0.18 | 0.1 | Plastic | \$0.49 |
| 2209191 | CW Industries | SS-5-125V | 4 | SP3T | ON-ON-ON | 0.5A@125VDC | 0.79 x 0.40 x 0.30 | 0.17 | Metal | \$0.49 |
| 2182442 | TE Connectivity | AS2DG-PC | 6 | DPDT | ON-NONE-ON | 0.02A@20VDC | 0.37 x 0.2 x 0.62 | 0.1 | Plastic | \$0.49 |
| 161817 | Jameco Valuepro | MS22D16 | 6 | DPDT | ON-ON | 0.1A@12VDC | 0.36 x 0.14 x 0.26 | 0.1 | Metal | \$0.69 |
| 2178591 | Switchcraft | 46206LFE | 6 | DPDT | ON-ON | 3A@125VAC | 1.38 x 0.53 x 0.95 | 0.28 | Metal | \$0.39 |
| 621472 | GC Electronics | 35-222-BU | 6 | DPDT | ON-ON | 6A@125VAC | 0.88 x 0.53 x 0.35 | 0.308 | Metal | \$0.99 |
| 2180818 | TE Connectivity | TSS11DG1RA | 6 | SPDT | ON-NONE-ON | 0.02A@20VDC | 0.4 x 0.4 x 0.2 | 0.1 | Metal | \$0.69 |
| 2180797 | TE Connectivity | MSSA214N | 6 | SPDT | ON-NONE-ON | 1.5@230VAC | 0.37 x 0.29 x 0.32 | 0.2 | Plastic | \$0.49 |