



[Click Here to Request a Large Quantity Quote](#)

[Li-Ion & Li-Po Rechargeable Batteries](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Cell Size	Volts (VDC)	Nominal Capacity (mAh)	Chemistry	Size	Termination	Features	Battery Type	Price 1
2291327	Jameco Reliapro	NCR20700B	20700	3.6	2600	Lithium-Ion	0.78"Dia. x 2.76"L	Button Top	Rechargeable, protected type	Primary	\$6.95
2315175	Adafruit Industries	LP503035(1578)	Flat Pack	3.7	500	Lithium Polymer	1.37"L x 1.18"W x 0.19"Th	(2) solder tabs	Rechargeable	Primary	\$7.49
2275319	Jameco Reliapro	LJ503035	Flat Pack	3.7	500	Lithium Polymer	1.40"L x 1.15"W x 0.19"Th	2-pin JST-PH connector (2mm pitch)	Rechargeable	Primary	\$6.95
2309567	Dantona Industries	HS-503759-CON	Flat Pack	3.7	1400	Lithium Polymer	2.40"L x 1.50"W x 0.20"Th	2-pin JST-PH connector (2mm pitch)	Rechargeable	Primary	\$9.95
2309575	Dantona Industries	HS-785060-CON	Flat Pack	3.7	2500	Lithium Polymer	2.55"L x 2.00"W x 0.30"Th	2-pin JST-PH connector (2mm pitch)	Rechargeable	Primary	\$14.95
2282647	Jameco Reliapro	357095	Flat Pack	3.7	2800	Lithium Polymer	3.62"L x 2.78"W x 0.15"Th	Wires	Rechargeable	Primary	\$5.00
2280743	SEIKO INSTRUMENTS	MS518SE-FL35E	MS518SE	3	3.4	Lithium (Manganese Silicon)	0.23"Dia. x 0.07"Th (5.8x1.8mm)	PC mount	Rechargeable	Secondary	\$1.89
2279191	Jameco Reliapro	P1013L	Pack	5	10000	Lithium-Ion	3.9"L x 2.6"W x 0.9"H	USB Type-C and USB micro-B	Rechargeable	Back-Up	\$17.95
2292135	Jameco Reliapro	YS-163452	Pack	7.4	1300	Lithium Polymer	2.16"L x 1.29"W x 0.67"Th	(2) female pin-header	Rechargeable	Primary	\$10.95
2292191	Jameco Reliapro	12V4500MAH	Pack	12	4500	Lithium Polymer	3.35"L x 2.40"W x 0.75"Th	2.1mm female barrel plug	Rechargeable	Primary	\$29.95
2129351	MG Electronics	LBP-124500	Pack	12	4500	Lithium-Ion	2.00"L x 0.75"W x 3.00"H	2.1mm x 5.5mm female barrel plug	Rechargeable	Primary	\$49.95
2315239	Samsung Electronics	INR18650-29E/7PK	Pack	25.2	2900	Lithium-Ion	2.8"L x 2.8"W x 1.3"H	(4) Wires	Rechargeable, protected type	Primary	\$29.95