



[Click Here to Request a Large Quantity Quote](#)

Motors-Vibrating

Jameco Part #	Manufacturer	Manufacturer Part #	Operating Voltage (VDC)	Operating Current (mA)	Operating Range (VDC)	Rated RPM@VDC	Termination	Motor Size (Diameter x Length) (inch)	Shaft Size (Diameter x Length) (inch)	Price 1
256306	Jameco Valuepro	6ZK003-R	1.3	80	0.85 - 1.60	8500 @ 1.3	1" wires	0.23 x 0.39	0.10 x 0.10	\$2.65
2209035	Jinlong Machinery	Z4SL2A0280131	1.3	85	1.1 - 1.6	10000 @ 3.0	1" wires	0.18 x 0.40	0.20 x 0.15	\$1.95
2236762	Jinlong Machinery	Z6SCAA0061141	1.3	90	.90 - 1.6	8500 @ 1.3	PC Terminal	0.27 x 0.40	0.11 x 0.16	\$1.75
2230838	Jinlong Machinery	C1226A001F	1.3	100	1.1 - 1.6	9000 @ 1.3	1" wires	0.47 x 0.11	No Shaft	\$1.95
256382	Jameco Valuepro	7ZK681-R	3	60	2.4 - 3.6	7500 @ 3.0	1.1" wires	0.28 x 0.66	0.12 x 0.16	\$3.49
256365	Jameco Valuepro	7ZK692-R	3	60	2.40 - 3.00	6500 @ 3.0	4.7" wires	0.28 x 0.66	0.18 x 0.22	\$3.49
2230184	Jinlong Machinery	Z6D12B0055211	3	70	2.40 - 3.60	11000 @ 3.0	0.87" wires	0.27 x 1.00	No Shaft	\$1.95
2237781	Jameco Valuepro	6ZK053-R-PINS	3	75	1.6 - 3.6	8500 @ 3.0	1" wires	0.15 x 0.10	0.15 x 0.10	\$3.75
256314	Jameco Valuepro	6ZK053-R	3	75	1.60 - 3.60	8500 @ 3.0	1" wires	0.23 x 0.39	0.10 x 0.10	\$2.75
2236771	Jinlong Machinery	Z6SC0B0170081	3	75	2.2 - 3.6	8000 @ 3.0	PC Terminal	0.27 x 0.40	0.06 x 0.16	\$1.95
256331	Jameco Valuepro	6ZK261-R	3	75	2.4 - 3.0	8500 @ 3.0	PC Terminal	0.27 x 0.48	0.11 x 0.11	\$2.95
2230846	Jinlong Machinery	C1026B200F	3	80	2.5 - 4.0	10000 @ 3.0	Coin Type	0.42 x 0.20	No Shaft	\$1.59
2189476	Jameco Valuepro	C1034B850F	3	80	2.50 x 4.00	9000 @ 3.0	1" wires	0.39 x 0.13	No Shaft	\$2.95
2271503	Jinlong Machinery	C1234B016F	3	80	2.7 - 3.3	9000 @ 3.0	2" wires	0.50 x 0.13	No Shaft	\$2.59
2218169	Jameco Valuepro	JL1027-001021-30-01	3	85	1.20- 3.00	12000 @ 3.0	1" wires	0.39 x 0.10	No Shaft	\$2.95

Jameco Part #	Manufacturer	Manufacturer Part #	Operating Voltage (VDC)	Operating Current (mA)	Operating Range (VDC)	Rated RPM@VDC	Termination	Motor Size (Diameter x Length) (inch)	Shaft Size (Diameter x Length) (inch)	Price 1
2234353	Jinlong Machinery	C1020B283F	3	90	2.3 - 4.0	9000 @ 3.0	1" wires	0.39 x 0.09	No Shaft	\$1.75
2278807	Jinlong Machinery	Z7AL2B1692082	3	250	2.2 - 3.6	12000 @ 3.0	1.8" wires	0.34 x 1.00	No Shaft	\$3.59