



[Click Here to Request a Large Quantity Quote](#)

[Alkaline Batteries](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Cell Size	Volts (VDC)	Nominal Capacity (mAh)	Chemistry	Size	Termination	Features	Battery Type	Price 1
2237976	Evergreen	L1028FT	23A	12	55	Alkaline (Manganese Dry)	0.41"Dia. x 1.12"(H)	Button Top	Non-Rechargeable	Primary	\$0.79
151095	Evergreen	VINNICS9V/GP6F22MS	9V	9	330	Alkaline (Zinc-chloride)	1.04"L x 0.62"W x 1.91"H	Snaps	Non-Rechargeable	Primary	\$1.19
2112461	Evergreen	L6F22/VINNIC	9V	9	550	Alkaline (Zinc-Manganese Dioxide)	1.04"L x 0.62"W x 1.91"H	Snaps	Non-Rechargeable	Primary	\$1.95
198731	Energizer Batteries	ALK 9V 522	9V	9	600	Alkaline (Zinc-Manganese Dioxide)	1.04"L x 0.62"W x 1.91"H	Snaps	Non-Rechargeable	Primary	\$2.25
2158493	Micropower Battery	R6S	AA	1.5	800	Zinc-chloride	0.57"(Dia) x 1.99"(H)	Button Top	Non-Rechargeable	Primary	\$0.29
2112444	Evergreen	LR6AM3	AA	1.5	2450	Alkaline (Manganese Dry)	0.57"Dia. x 1.99"L	Button Top	Non-Rechargeable	Primary	\$0.49
198707	Energizer Batteries	ALK AA (EN91)	AA	1.5	2800	Alkaline (Zinc-Manganese Dioxide)	0.57"Dia. x 1.99"L	Button Top	Non-Rechargeable	Primary	\$0.69
2112436	Evergreen	LR03AM4	AAA	1.5	1200	Alkaline (Manganese Dry)	0.41"Dia.x 1.75"HL	Button Top	Non-Rechargeable	Primary	\$0.45
198715	Energizer Batteries	ALK AAA (EN92)	AAA	1.5	1200	Alkaline (Zinc-Manganese Dioxide)	0.41"Dia. x 1.75"L	Button Top	Non-Rechargeable	Primary	\$0.69
2112428	Evergreen	LR14AM2	C	1.5	6700	Alkaline (Zinc, EMD, HKO, Graphite)	0.98"Dia. x 1.90"L	Button Top	Non-Rechargeable	Primary	\$1.19
215845	Energizer Batteries	ALK D EN-95	D	1.5	18000	Alkaline (Zinc-Manganese Dioxide)	1.35"Dia. x 2.42"L	Button Top	Non-Rechargeable	Primary	\$1.75
140783	Evergreen	S357ST	SR44	1.55	175	Silver-Oxide	0.45"Dia. x 0.21"Th	Pressure Fit	Non-Rechargeable	Primary	\$1.25