



[Click Here to Request a Large Quantity Quote](#)

[Audio Components-Speakers](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Impedance (Ohms)	Size (Diameter x Depth) (inch)	Nominal Input Power (W)	Input Power (max) (W)	Ouput SPL (dB)	Frequency Range (Hz)	Magnet Size (Diameter x H) (inches)	Price 1
<a href="#">673766</a>	Jameco Valuepro	AZ-50S	4	1.9 x 0.2	0.4	0.8	70	500 - 6000	1.9 x 0.1	\$1.09
<a href="#">2229618</a>	Jameco Valuepro	SP99023A	4	2.1 x 1.25	10	20	90	400 - 8000	2.1 x 1.25	\$1.75
<a href="#">2224041</a>	Jameco Valuepro	110153-01	4	2.4 x 1.4	10	10	85	1000 - 12000	2.2 x 0.5	\$1.95
<a href="#">99996</a>	Jameco Valuepro	TQ-066F-R	4	2.6 x 0.9	3	4	95	300 - 14000	1.8 x 0.5	\$3.59
<a href="#">2234759</a>	Jameco Valuepro	TQ-023CP-8	8	0.9 x 0.4	2	4	76	300 - 20000	0.5 x 0.12	\$3.59
<a href="#">2099606</a>	Jameco Valuepro	SP801W	8	1.05 x 0.35	0.1	0.2	78	320 - 7500	0.67 x 0.17	\$1.59
<a href="#">2227508</a>	Jameco Valuepro	AZ30R	8	1.2 x 0.2	0.4	0.8	70	1300 - 8000	0.5 x 0.2	\$1.49
<a href="#">2228851</a>	CUI	GC0361MA	8	1.42 x 0.18	0.2	0.5	84	380 - 680	0.64 x .65	\$1.49
<a href="#">2272639</a>	Jameco Valuepro	SPU3520	8	1.4L x 0.8W x 0.32D	1	1	80	500-2000	0.55 x 0.10	\$1.49
<a href="#">2234134</a>	Jameco Valuepro	40R	8	1.5 x 0.2	1	1.5	93	100 - 15000	0.63 x 0.05	\$2.49
<a href="#">76030</a>	Jameco Valuepro	AZ-40S	8	1.6 x 0.2	0.4	0.8	70	600 - 6000	1.6 x 0.1	\$1.49
<a href="#">2227516</a>	Jameco Valuepro	AZ40R	8	1.6 x 0.2	0.4	0.8	70	600 - 6000	1.6 x 0.1	\$1.25
<a href="#">2115442</a>	Jameco Valuepro	K7048022	8	1.6L x 2.8W x 0.9H	3	3	82	310 - 12000	0.87 x 0.29	\$2.09
<a href="#">135812</a>	Jameco Valuepro	TV-4171A-R	8	1.6L x 2.8W x 1.2H	2	3	88	450 - 20000	0.5 z 0.5	\$2.59
<a href="#">2205561</a>	Panasonic	45P30S	8	1.8 x 0.7	0.1	0.1	93	530 - 3000	0.69 x 0.45	\$0.75
<a href="#">2231161</a>	Shogyo International	GF0506X	8	2 x 0.68	0.25	0.5	82	430 - 7200	1.8 x 0.5	\$1.95
<a href="#">88411</a>	Jameco Valuepro	A0200-R	8	2 x 0.8	0.2	0.4	82	430 - 4500	0.5 x 0.4	\$2.25
<a href="#">135694</a>	Jameco Valuepro	TQ-050F-R	8	2.0 x 0.7	0.2	0.3	82	500 - 6000	1.3 x 0.5	\$2.29
<a href="#">2239146</a>	MG Electronics	MSC299SWC	8	2.0 x 0.7	0.7	2	83	500 - 8000	1.3 x 0.4	\$1.95
<a href="#">2208825</a>	Jameco Valuepro	EAS-6P60SD	8	2.2 x 1.3	0.4	0.8	85	100 - 5000	2.2 x 1.3	\$0.99
<a href="#">2146388</a>	Jameco Valuepro	TR-057A-R	8	2.25 x 0.77	0.25	0.5	84	300 - 14000	0.5 x 0.4	\$2.75
<a href="#">2258793</a>	Jameco Valuepro	S03O7F390	8	2.9L x 1.2W x 1.0H	0.5	1	80	100 - 1000	1.2 x 0.8	\$1.95
<a href="#">2167285</a>	Jameco Valuepro	1-529-483-11	8	3.0 x 2.25	4	5	85	180 - 10000	2.5 x 1.0	\$3.59
<a href="#">2265895</a>	Jameco Valuepro	BLS86-2-08H30.5-05LF	8	3.4 x 3.4 x 1.21	6	12	87	800 - 10000	2.3 x 0.4	\$2.95
<a href="#">1954818</a>	Jameco Valuepro	TQ-100F-R	8	4.0 x 1.4	5	8	97	800 - 10000	1.8 x 0.5	\$3.59
<a href="#">2224032</a>	Zenith Electronics	49-1334-02	8	6.3L x 3.1W x 2.2D	7	7	85	100 - 18000	2.1 x 1.0	\$2.75

