



[Click Here to Request a Large Quantity Quote](#)

[PW24 Series Wirewound Potentiometers](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Resistance (Ohm)	Power Rating	Tolerance	Shaft Style	Shaft Length	Termination Style	Taper	Body Diameter	Manufacturer Series	Voltage Rating	Price 1
<a href="#">2291143</a>	Jameco Valuepro	5W-PW-24H-22S-5?	5	5 W	20%	Round	0.866 in.	Solder, Panel Mount	Linear	24 mm	PW24	250 V	\$5.29
<a href="#">2291151</a>	Jameco Valuepro	5W-PW-24H-22S-10?	10	5 W	20%	Round	0.866 in.	Solder, Panel Mount	Linear	24 mm	PW24	250 V	\$5.29
<a href="#">2234855</a>	Jameco Valuepro	5W-VW24F-10D6-20K-B25	25	5 W	20%	Knurled Slotted	0.590 in.	Solder, Panel Mount	Linear	24 mm	VW24	250 V	\$4.95
<a href="#">2291159</a>	Jameco Valuepro	5W-PW-24H-22S-25?	25	5 W	20%	Round	0.866 in.	Solder, Panel Mount	Linear	24 mm	PW24	250 V	\$5.29
<a href="#">2272279</a>	Jameco Valuepro	5W-PW-24H-20S-B50	50	5 W	20%	Round Slotted	0.787 in.	Solderable Lug	Linear	24 mm	PW24	250 V	\$4.95
<a href="#">2291167</a>	Jameco Valuepro	5W-PW-24H-22S-100?	100	5 W	20%	Round	0.866 in.	Solder, Panel Mount	Linear	24 mm	PW24	250 V	\$5.29
<a href="#">140514</a>	Jameco Valuepro	5W-PW-24H-20S-B100	100	5 W	20%	Round Slotted	0.787 in.	Solderable Lug	Linear	24 mm	PW24	250 V	\$4.95
<a href="#">2291175</a>	Jameco Valuepro	5W-PW-24H-22S-250?	250	5 W	20%	Round	0.866 in.	Solder, Panel Mount	Linear	24 mm	PW24	250 V	\$5.29
<a href="#">2291183</a>	Jameco Valuepro	5W-PW-24H-22S-500?	500	5 W	20%	Round	0.866 in.	Solder, Panel Mount	Linear	24 mm	PW24	250 V	\$5.29
<a href="#">2291191</a>	Jameco Valuepro	5W-PW-24H-22S-1K?	1000	5 W	20%	Round	0.866 in.	Solder, Panel Mount	Linear	24 mm	PW24	250 V	\$5.95
<a href="#">2291199</a>	Jameco Valuepro	5W-PW-24H-22S-5K?	5000	5 W	20%	Round	0.866 in.	Solder, Panel Mount	Linear	24 mm	PW24	250 V	\$6.95