



[Click Here to Request a Large Quantity Quote](#)

[Networking Modular Plugs Jacks](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Gender	Contact Arrangement	Common Name	Entry	Panel Stops	Body Orientation	Mounting	Housing Color	Shielded	Price 1
204410	Jameco Valuepro	TMP-SR02-BLACK-R	Boot	N/A	RJ45	Side	No	Side	Round Strain Relief	Black	No	\$0.25
2328695	TE Connectivity	555165-5	Jack	6P2C	RJ11	Side	No	Right Angle	Through Hole	Black	No	\$0.69
151766	Jameco Valuepro	9602-6141-M	Jack	6P4C	RJ11	Side	Yes	Right Angle	Through Hole	Black	No	\$0.59
115837	Jameco Valuepro	3008F-6621-R	Jack	6P6C	RJ11	Side	Yes	Right Angle	Through Hole	Gray	No	\$0.89
956176	TE Connectivity	5520258-3	Jack	6P6C	RJ11, RJ12, RJ14, RJ25	Top	Yes	Straight	Through Hole	Black	No	\$1.39
124039	Jameco Valuepro	623K-6P6C-R	Jack	6P6C	RJ25	Side	No	Right Angle	6 Wire Leads	White	No	\$1.25
2298143	Arndt Electronics	87180-066	Jack	6P6C	RJ25	Side	No	Right Angle	Through Hole	Black	No	\$1.25
2281359	Amphenol	69254-001F	Jack	6P6C	RJ25	Top	Yes	Straight	Through Hole	Black	No	\$0.99
2328719	Max Con	MJ-H-88-NF	Jack	8P8C	RJ45	Side	No	Right Angle	Through Hole	Black	No	\$1.95
115844	Adam Technologies	MTJ-882BX1-FS	Jack	8P8C	RJ45	Side	No	Right Angle	Through Hole	Black	Yes	\$0.59
2328703	Steward	SS-700810SA-PG3-1-BA-A300	Jack	8P8C	RJ45	Side	No	Right Angle	Through Hole	Black	Yes	\$1.49
2322071	Bel Fuse	0826-1A1T-23-F	Jack	8P8C	RJ45	Side	No	Right Angle	Through Hole	Chrome	No	\$4.49
524461	TE Connectivity	5555164-1	Jack	8P8C	RJ45	Side	Yes	Right Angle	Through Hole	Black	No	\$0.99
2078258	Jameco Valuepro	MJV0808KX06	Jack	8P8C	RJ45	Side	Yes	Right Angle	Through Hole	Black	No	\$0.49
2150395	Adam Technologies	RJ45-8P8C	Jack	8P8C	RJ45	Side	Yes	Right Angle	Through Hole	Black	No	\$0.69
754929	TE Connectivity	5555167-1	Jack	8P8C	RJ45	Side	Yes	Right Angle	Through Hole	Black	No	\$0.99
852529	TE Connectivity	555141-1	Jack	8P8C	RJ45	Side	Yes	Right Angle	Through Hole	Black	Yes	\$0.00
2323095	RS Electronics	557165	Jack	8P8C	RJ45	Side	Yes	Straight	IDC	Black	Yes	\$2.49
2314207	FCI	90598-006LF	Jack	8P8C	RJ45	Top	Yes	Straight	Through Hole	Black	No	\$0.69
2322079	Bel Fuse	0845-2RIT-E4	Jack	8P8C (1x2)	RJ45	Side	No	Right Angle	Through Hole	Chrome	No	\$9.95
2328711	Max Con	MJHS-G-88-5B-T	Jack	8P8C (1x5)	RJ45	Side	No	Right Angle	Through Hole	Black	Yes	\$2.95
2328839	Max Con	MJDS-G-88-12-PG4T-6	Jack	8P8C (2x6)	RJ45	Side	No	Right Angle	Through Hole	Black	Yes	\$9.95
2322263	Pulse Electronics	JW0-0013NL	Jack	8P8C, 2x USB	RJ45	Side	No	Right Angle	Through Hole	Chrome	No	\$9.95

Jameco Part #	Manufacturer	Manufacturer Part #	Gender	Contact Arrangement	Common Name	Entry	Panel Stops	Body Orientation	Mounting	Housing Color	Shielded	Price 1
180646	Jameco Valuepro	TMP-1001	Plug	10P10C	RJ50	Side	No	Straight	Cable Mount	Clear	No	\$0.69
79290	Adam Technologies	MTP-64-U	Plug	6P4C	RJ11, RJ14	Side	No	Straight	Cable Mount	Clear	No	\$0.15
79273	Jameco Valuepro	PT-066	Plug	6P6C	RJ12	Side	No	Straight	Cable Mount	Clear	No	\$0.39
79281	Steren Electronics	300-068	Plug	8P8C	RJ45	Side	No	Straight	Cable Mount	Clear	No	\$0.59
119343	Steren Electronics	300-168	Plug	8P8C	RJ45	Side	No	Straight	Cable Mount	Clear	No	\$0.49
116611	Jameco Valuepro	GU4511-R	Plug	8P8C	RJ45	Side	No	Straight	Cable Mount	Clear	Yes	\$0.69