



[Click Here to Request a Large Quantity Quote](#)

[Circuit Protection-Fuses](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Manufacturer Series	Blow characteristic	Rated Breaking Capacity (A)	Voltage Rating (AC)	Fuse Material	Diameter (mm)	Body Length (mm)	Price 1
<a href="#">2287527</a>	Littelfuse	237002-010	237	Medium Blow	2	125	Glass	5	20	\$0.35
<a href="#">2280351</a>	Littelfuse	0229003.KXP	2AG	Slow Blow	3	250	Glass	5	15	\$0.29
<a href="#">2129836</a>	Bel Fuse	5ST(P)630	5ST	Slow Blow	0.63	250	Glass	5	20	\$0.39
<a href="#">2161668</a>	Optifuse	FSC-10A	FSC	Fast Acting	10	250	Glass	5	20	\$0.32
<a href="#">103827</a>	Jameco Valuepro	GFS5225	GFS	Medium Blow	1	250	Glass	5	20	\$0.19
<a href="#">103887</a>	Jameco Valuepro	GFS5202-R	GMA	Fast Acting	0.25	250	Glass	5	20	\$0.35
<a href="#">102041</a>	Jameco Valuepro	GFS5250-R	GMA	Fast Acting	0.5	250	Glass	5	20	\$0.35
<a href="#">103908</a>	Jameco Valuepro	GFS5205-R	GMA	Fast Acting	1	250	Glass	5	20	\$0.35
<a href="#">103916</a>	Jameco Valuepro	GFS5207-R	GMA	Fast Acting	2	250	Glass	5	20	\$0.35
<a href="#">103924</a>	Jameco Valuepro	GFS5209-R	GMA	Fast Acting	3	250	Glass	5	20	\$0.35
<a href="#">103932</a>	Jameco Valuepro	MFG52A5	GMA	Fast Acting	5	250	Glass	5	20	\$0.35
<a href="#">2159664</a>	Optifuse	GMA-16	GMA	Fast Acting	16	250	Glass	5	20	\$0.45
<a href="#">197502</a>	Optifuse	TSC-500MA	MMG52	Slow Blow	0.5	250	Glass	5	20	\$0.59
<a href="#">197465</a>	Jameco Valuepro	MMG52-1-R	MMG52	Slow Blow	1	250	Glass	5	20	\$0.59
<a href="#">197472</a>	Jameco Valuepro	LMG52-2	MMG52	Slow Blow	2	250	Glass	5	20	\$0.59
<a href="#">197500</a>	Jameco Valuepro	TSC-5A	MMG52	Slow Blow	5	250	Glass	5	20	\$0.59