



[Click Here to Request a Large Quantity Quote](#)

[Automotive Connectors and Crimp Terminals](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Gender	Number of Contacts	Number of Rows	Maximum Current Rating	Maximum Voltage Rating	Pitch (mm)	Housing Color	Body Orientation	Product Depth (mm)	Product Length (mm)	Price 1
2232534	Delphi	12129557	Cavity Plug	1	1	N/A	N/A	0	Blue	Straight	1.9	13.7	\$0.25
2287231	Omron	25-13936	Female	10	2	12 A	28 VDC	8.38	Black	Straight	31.5	33.27	\$1.95
2232500	Delphi	15326910	Female	12	2	25 A	N/A	6.5	Black	Straight	52.85	31.2	\$1.49
2232702	Yazaki	7282-5567-40	Female	12	2	N/A	N/A	4.9	Grey	Straight	2.195	39.25	\$2.49
2232729	Yazaki	7283-5643-40	Female	13	2	15 A	N/A	4.9	Grey	Straight	24.75	35.15	\$2.49
2232542	Delphi	04687929	Female	14	2	N/A	N/A	2.8	Black	Straight	36.06	49.75	\$1.25
2232753	Molex	33476-1711	Female	16	2	22 A	250 VDC	3.5	Yellow	Straight	32.79	49.65	\$1.95
2232446	Delphi	54550415	Female	4	1	N/A	N/A	4	Yellow	Straight	27.3	38	\$1.49
2232737	Yazaki	7283-5916-40	Female	6	2	N/A	N/A	4.9	Grey	Straight	24.78	36.87	\$2.49
2232518	Delphi	12052834-B	Lock	1	1	25 A	N/A	0	Green	Straight	12	22	\$0.25
2232497	Delphi	12129384	Lock	1	1	N/A	N/A	0	Black	Straight	11.5	24.9	\$0.35
2232526	Delphi	12110299	Lock	1	1	N/A	N/A	0	Red	Straight	7.7	25.6	\$0.25
2232745	Molex	33472-1201	Male	12	2	22 A	N/A	3.5	Natural	Straight	50.79	43.25	\$1.25
2232551	Delphi	04687935	Male	14	2	N/A	N/A	5.25	Black	Straight	26.5	45.8	\$1.19
2232454	Delphi	54550416	Male	4	1	N/A	N/A	4	Yellow	Straight	27.3	45.8	\$1.19
2232420	Delphi	54550403	Male	4	1	N/A	N/A	5.25	Yellow	Straight	26.1	45.3	\$1.49
2232489	Delphi	12129382	Plug Seal	1	1	N/A	N/A	0	Blue	Straight			\$0.39
2287263	TE Connectivity	828922-1	Plug Seal	1	1	N/A	N/A	0	Clear	Straight	7.8	6.2	\$0.25
2232471	Delphi	12129381	Plug Seal	1	1	N/A	N/A	0	Dark Red	Straight	8.5	13.05	\$0.49
2287255	TE Connectivity	828905-1	Plug Seal	1	1	N/A	N/A	0	White	Straight	7.8	5.6	\$0.25