



[Click Here to Request a Large Quantity Quote](#)

[27 to 54 Volt Open Frame Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Number of Outputs	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Size (L" x W" x H")	PFC Function	Agency Approvals	Price 1
2174143	MEAN WELL	EPS-15-48	1	48	0.344	43.2 to 52.8	85 to 264	47 to 63	JST B2P-VH	2.5 x 1.8 x 0.9	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$7.20
2164711	MEAN WELL	EPS-65-48	1	48	1.5	43.2 to 52.8	90 to 264	47 to 63	JST B4P-VH	4 x 2 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	\$13.10
2239744	MEAN WELL	EPS-120-48	1	48	2.5		80 to 264	47 to 63	JST B4P-VH	4 x 2 x 1.14	No	UL/CUL/TUV/CB/CE/EN/EAC	\$20.30
2172480	MEAN WELL	EPP-150-48	1	48	3.125		90 to 264	47 to 63	JST B4P-VH	4 x 2 x 1.1	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$39.00
2249301	MEAN WELL	EPP-200-48	1	48	4.2		80 to 264	47 to 63	JST B6P-VH	4 x 2 x 1.14	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$40.90
694508	MEAN WELL	USP-225-48	1	48	4.7	43.2 to 52.8	90 to 264	47 to 63	Molex 39-29-9206	8 x 4 x 1.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$59.69
2253917	MEAN WELL	EPP-400-48	1	48	5.3		80 to 264	47 to 63	Screw Terminals	5 x 3 x 1.38	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$68.80
2164295	MEAN WELL	EPP-300-48	1	48	6.25		90 to 264	47 to 63	Screw Terminals	5 x 3 x 1.4	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$57.00
2304559	MEAN WELL	EPP-500-48	1	48	6.7		80 to 264	47 to 63	Screw Terminals	5 x 3 x 1.57	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$82.70
668756	MEAN WELL	USP-350-48	1	48	7.3	43.2 to 52.8	90 to 264	47 to 63	JST B9P-VH (x2)	9.3 x 4 x 1.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$92.95