



[Click Here to Request a Large Quantity Quote](#)

Multiple Output Open Frame Power Supplies

Jameco Part #	Manufacturer	Manufacturer Part #	Number of Outputs	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Size (L" x W" x H")	PFC Function	Agency Approvals	Price 1
212338	MEAN WELL	PD-25A	2	5	2.1	12	85 to 264	47 to 63	Molex 41791-04	4.2 x 2.4 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$11.95
212312	MEAN WELL	PD-2505	2	5	2.5	-5	85 to 264	47 to 63	Molex 41791-04	4.2 x 2.4 x 1.1	No	UL/CUL/TUV/CE/EN	\$10.95
194862	MEAN WELL	PD-45A	2	5	3.2	12	90 to 264	47 to 440	Molex 5273-06	5 x 3 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	\$12.49
194871	MEAN WELL	PD-45B	2	5	3.2	24	90 to 264	47 to 440	Molex 5273-06	5 x 3 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	\$12.75
194897	MEAN WELL	PD-65B	2	5	3.5	24	90 to 264	47 to 440	Molex 5273-06	5 x 3 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	\$15.49
194889	MEAN WELL	PD-65A	2	5	5.5	12	90 to 264	47 to 440	Molex 5273-06	5 x 3 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	\$15.49
148690	MEAN WELL	PD-2512	2	12	1	-12	85 to 264	47 to 63	Molex 41791-04	4.2 x 2.4 x 1.1	No	UL/CUL/TUV/CE/EN	\$11.95
2100857	MEAN WELL	PD-2515	2	15	1	-15	85 to 264	47 to 63	Molex 41791-04	4.2 x 2.4 x 1.1	No	UL/CUL/TUV/CE/EN	\$11.95
88402	MEAN WELL	PT-45B	3	5	3	12 , -12	90 to 264	47 to 440	Molex 5273-06	5 x 3 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	\$13.49
215707	MEAN WELL	PT-65D	3	5	4	12 , 24	90 to 264	47 to 440	Molex 5273-06	5 x 3 x 1.7	No	UL/CUL/TUV/CB/CE/EN/EAC	\$15.95
375030	MEAN WELL	PT-45C	3	5	5	15 , -15	90 to 264	47 to 440	Molex 5273-06	5 x 3 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	\$13.49
216734	MEAN WELL	PT-65B	3	5	5.5	12 , -12	90 to 264	47 to 440	Molex 5273-06	5 x 3 x 1.7	No	UL/CUL/TUV/CB/CE/EN/EAC	\$13.95
216726	MEAN WELL	PT-65C	3	5	5.5	15 , -15	90 to 264	47 to 440	Molex 5273-06	5 x 3 x 1.7	No	UL/CUL/TUV/CB/CE/EN/EAC	\$15.95
2197741	Skynet	SNP-N563		3.3	6	5	85 to 264	47 to 63	Molex 5273-10A	5 x 3 x 1.38	No	UL/CUL/TUV/VDE	\$5.95