



[Click Here to Request a Large Quantity Quote](#)

LED Multi Color

Jameco Part #	Manufacturer	Manufacturer Part #	Package	Color	Luminous Intensity - Iv (mcd)	Lens Type	Viewing Angle (deg)	Forward Voltage - Vf (Typ.)	Forward Current - If (Typ.)	Wavelength	Height (mm)	Lead Pitch	Price 1	Price 10
<a href="#">2219567</a>	Jameco Valuepro	RGB LED CA-10	10mm, T-3 3/4	RGB		Diffused		2.0/3.2/3.2	20 mA	625 nm, 525 nm, 470 nm	10.9	0.05"	\$0.59	\$0.49
<a href="#">2219575</a>	Jameco Valuepro	RGB LED CC-10	10mm, T-3 3/4	RGB		Clear		2.0/3.4/3.4	20 mA	625 nm, 525 nm, 470 nm	10.9	0.05"	\$0.49	\$0.39
<a href="#">104889</a>	Jameco Valuepro	LEG5292	2mm x 5mm	Green/Orange	6	Non Diffused	116	1.7	30 mA	565 nm, 635 nm	7	0.1"	\$0.25	\$0.19
<a href="#">2186419</a>	Lite-On Electronics	LTL-2H3VYKNT	3mm, T-1	Amber/Yellow	3400	Clear	22	1.9	50 mA	595 nm	8.7	0.1"	\$0.25	\$0.15
<a href="#">2283151</a>	Jameco Valuepro	LHG2062B	3mm, T-1	Green/Red	2.0/5.0	Diffused	70	2.0/5.0	30 mA	565 nm, 697 nm	5.2	0.1"	\$0.25	\$0.19
<a href="#">94553</a>	Jameco Valuepro	LHG2062	3mm, T-1	Green/Red	2.0/5.0	Diffused White	70	2.6	30 mA	565 nm, 697 nm	5.2	0.1"	\$0.25	\$0.19
<a href="#">2278855</a>	Jameco Valuepro	LED-3mmRDGRN	3mm, T-1	Green/Red	2.0/5.0	White Diffused	36	1.7		565 nm, 697 nm	5.2	0.1"	\$0.25	\$0.19
<a href="#">156946</a>	Jameco Valuepro	UT0362-21-D61-R	3mm, T-1	Green/Red	2.7/13.3	White Diffused	50	2.1	30 mA	567 nm, 670 nm		0.1"	\$0.39	\$0.29
<a href="#">1995935</a>	Lite-On Electronics	LTL-14CHJ	3mm, T-1	Green/Red Orange	4.8	White Diffused	200	2.6	30 mA	565 nm, 630 nm	4.45	0.1"	\$0.25	\$0.15
<a href="#">2186371</a>	Lite-On Electronics	LTL-1BEWJ	3mm, T-1	Red/Green	12.6/5.6	White Diffused	140	1.8/2.1	40 mA, 30 mA	565 nm, 660 nm	5.15	0.1"	\$0.25	\$0.15
<a href="#">2224163</a>	Kingbright Corporation	WP115WEGW	3mm, T-1	Red/Green	40	White Diffused	60	2.0/2.2	30 mA, 25 mA	568 nm, 617 nm	5	0.1"	\$0.25	\$0.19
<a href="#">2186451</a>	Lite-On Electronics	LTL-1BEHKVMP1	3mm, T-1 RA	Red/Green	19/29	Water Clear	55	2.0/2.1	30 mA	565 nm, 650 nm	4.05	0.1"	\$0.25	\$0.05
<a href="#">2006772</a>	Lite-On Electronics	LTL-2H3VYKNT1	5mm, T-1 3/4	Amber/Yellow	3400	Water Clear	15	2	50 mA	595 nm	8.7	0.1"	\$0.25	\$0.06
<a href="#">334182</a>	Jameco Valuepro	GDG-5MMSURCSYGC	5mm, T-1 3/4	Green/Red	2.0/8.0	Diffused White	30	2.6	30 mA	565 nm, 697 nm	8.6	0.1"	\$0.25	\$0.19

Jameco Part #	Manufacturer	Manufacturer Part #	Package	Color	Luminous Intensity - Iv (mcd)	Lens Type	Viewing Angle (deg)	Forward Voltage - Vf (Typ.)	Forward Current - If (Typ.)	Wavelength	Height (mm)	Lead Pitch	Price 1	Price 10
<a href="#">1109260</a>	Vishay	TLUV5300	5mm, T-1 3/4	Green/Red	2.5	White Diffused	60	3	30 mA	545 nm, 630 nm	8.6	0.1"	\$0.25	\$0.10
<a href="#">2266591</a>	Jameco Valuepro	5ARG9HWB	5mm, T-1 3/4	Green/Red	2.6	White Diffused				565 nm, 697 nm	8.6	0.1"	\$0.29	\$0.19
<a href="#">34673</a>	Jameco Valuepro	LHG3392	5mm, T-1 3/4	Green/Red	3.0/12.0	Diffused White	70	2.8	30 mA	565 nm, 697 nm		0.1"	\$0.25	\$0.19
<a href="#">697557</a>	Lite-On Electronics	LTL-30EFJ	5mm, T-1 3/4	Green/Red	5.6/19	White Diffused	30	2.6	30 mA	565 nm, 697 nm	8.6	0.05"	\$0.25	\$0.10
<a href="#">1995960</a>	Lite-On Electronics	LTL-30EHJ-002	5mm, T-1 3/4	Green/Red Orange	29/40	White Diffused	30	2.1	30 mA	565 nm, 630 nm	8.6	0.05"	\$0.25	\$0.15
<a href="#">2219559</a>	Jameco Valuepro	RGB LED CC-5	5mm, T-1 3/4	RGB	1700/5000/4000	Diffused	25	1.9/3.0/3.0	20 mA	620 nm, 520 nm, 465 nm	8.7	0.05"	\$1.25	\$0.99
<a href="#">2299583</a>	MCD Electronics	MCDL-5013RBGC-C-9"	5mm, T-1 3/4	RGB	2000/1200/3000	Water Clear		1.9/3.0/3.0	20 mA	625 nm, 525 nm, 470 nm		9" Leads w/ conn.	\$1.75	\$1.65
<a href="#">2299591</a>	MCD Electronics	MCDL-5013RBGC-C-15"	5mm, T-1 3/4	RGB	2000/1200/3000	Water Clear		1.9/3.0/3.0	20 mA	625 nm, 525 nm, 470 nm		15" Leads w/ conn.	\$1.95	\$1.85
<a href="#">2211127</a>	Jameco Valuepro	MSL-504RGB-4P+	5mm, T-1 3/4	RGB	2000/3000/1200	Water Clear	25	2.0/3.4/3.4	25 mA	625 nm, 525 nm, 470 nm	7.9	0.05"	\$0.79	\$0.65
<a href="#">2211119</a>	Jameco Valuepro	MSL-504RGB-4P-	5mm, T-1 3/4	RGB	2000/3000/1200	Water Clear	25	2.0/3.4/3.4	30 mA	625 nm, 525 nm, 470 nm	7.9	0.1"	\$0.85	\$0.75
<a href="#">2128500</a>	Jameco Valuepro	MCDL-5013RGBC-TL-A	5mm, T-1 3/4	RGB	3000/5000/1000	Water Clear	25	2.0/3.5/3.5	30 mA	628 nm, 525 nm, 470 nm	8.7	0.05"	\$2.25	\$1.95
<a href="#">2210829</a>	MCD Electronics	MCDL-5T8R6G5B6C-CA	5mm, T-1 3/4	RGB	3500/4000/2000	Water Clear	20	2.25/3.5/3.5	30 mA	624 nm, 525 nm, 470 nm	8.7	0.05"	\$1.75	\$1.59
<a href="#">2125181</a>	Jameco Valuepro	MCDL-5T8R6G5B6C	5mm, T-1 3/4	RGB	3500/4000/2000	Water Clear	20	2.25/3.5/3.5	30 mA	624 nm, 525 nm, 470 nm	8.7	0.1"	\$2.25	\$1.95
<a href="#">2228957</a>	Jameco Valuepro	RGB-LED-CC-5-WC	5mm, T-1 3/4	RGB	5000/9000/6000	Water Clear	20	2.0/3.2/3.2	30 mA	625 nm, 525 nm, 470 nm	8.7	0.05"	\$0.39	\$0.35
<a href="#">2236439</a>	Sunled Corporation	XLMDKDG59MW3.15	5mm, T-1 3/4	Red Green	1195/1495	Diffused	60	3.3	20 mA	650 nm, 515 nm	8.6	3" Leads	\$0.99	\$0.89
<a href="#">2186460</a>	Lite-On Electronics	LTL-30WJNF	5mm, T-1 3/4	Red/Green	19/87	Diffused	60	2.1	40 mA, 30 mA	565 nm, 660 nm	8.7	0.1"	\$0.25	\$0.10