



[Click Here to Request a Large Quantity Quote](#)

7.5 to 13.8 Volt Open Frame Switching Power Supplies

Jameco Part #	Manufacturer	Manufacturer Part #	Number of Outputs	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Size (L" x W" x H")	PFC Function	Agency Approvals	Price 1
<a href="#">2164501</a>	MEAN WELL	EPS-45-7.5	1	7.5	6	7.13 to 8.25	90 to 264	47 to 63	JST B4P-VH	4 x 2 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	\$12.40
<a href="#">2099981</a>	Arndt	SBU60-105	1	11	4.84	12 , 13	90 to 264	47 to 63	Molex 09-50-3061	5 x 3 x 1.1	No	UL/CUL/CE	\$7.95
<a href="#">2105543</a>	MEAN WELL	PS-05-12	1	12	0.5		85 to 264	47 to 63	Molex 5273-02	3 x 1.6 x 0.8	No	CB/CE/EN/EAC	\$5.70
<a href="#">2174098</a>	MEAN WELL	EPS-15-12	1	12	1.38	10.8 to 13.5	85 to 264	47 to 63	JST B2P-VH	2.5 x 1.8 x 0.9	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$7.20
<a href="#">2227559</a>	Bel Power Solutions	BLP30-1012G	1	12	2.1		100 to 250	50 to 60		4.5 x 2.5 x 0.16	No	UL/CULTUV/CE	\$5.49
<a href="#">2164332</a>	MEAN WELL	EPS-25-12	1	12	2.34	10.8 to 13.5	85 to 264	47 to 63	JST B2P-VH	3 x 2 x 0.9	No	UL/CUL/TUV/CB/CE/EN/EAC	\$11.20
<a href="#">2164421</a>	MEAN WELL	EPS-35-12	1	12	3.3	10.8 to 13.5	85 to 264	47 to 63	JST B2P-VH	3 x 2 x 0.9	No	UL/CUL/TUV/CB/CE/EN/EAC	\$11.60
<a href="#">2248641</a>	MEAN WELL	EPS-45S-12	1	12	3.8		80 to 264	47 to 63	JST B2P-VH	3 x 2 x 0.95	No	UL/CUL/TUV/CB/CE/EN/EAC	\$12.70
<a href="#">2164519</a>	MEAN WELL	EPS-45-12	1	12	4.2	10.8 to 13.5	90 to 264	47 to 63	JST B4P-VH	4 x 2 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	\$12.40
<a href="#">2234732</a>	Arndt	ESO065-12	1	12	5.4		100 to 240	47 to 63	Wires with Fork Terminals	5 x 3 x 1.46	No	UL/CUL/CE	\$4.95
<a href="#">2248712</a>	MEAN WELL	EPS-65S-12	1	12	5.42		80 to 264	47 to 63	JST B2P-VH	3 x 2 x 0.95	No	UL/CUL/TUV/CB/CE/EN/EAC	\$13.30
<a href="#">2164674</a>	MEAN WELL	EPS-65-12	1	12	6	10.8 to 13.5	90 to 264	47 to 63	JST B4P-VH	4 x 2 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	\$13.10

Jameco Part #	Manufacturer	Manufacturer Part #	Number of Outputs	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Size (L" x W" x H")	PFC Function	Agency Approvals	Price 1
173472	MEAN WELL	LPS-100-12	1	12	8.4		88 to 132, 176 to 264	47 to 63	JST B8P-VH	8.7 x 2.4 x 1.3	No	UL/CUL/TUV/CB/CE/EN/EAC	\$27.60
2172391	MEAN WELL	EPP-100-12	1	12	8.5		90 to 264	47 to 63	JST B4P-VH	4 x 2 x 1.1	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$35.70
2239429	MEAN WELL	EPS-120-12	1	12	10		80 to 264	47 to 63	JST B4P-VH	4 x 2 x 1.14	No	UL/CUL/TUV/CB/CE/EN/EAC	\$20.30
213681	MEAN WELL	LPP-150-12	1	12	12.5		85 to 264	47 to 63	JST B6P-VH (x2)	8.7 x 3 x 1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$33.30
668713	MEAN WELL	PPS-200-12	1	12	16.6	10.8 to 13.2	90 to 264	47 to 63	JST B8P-VH	5 x 3 x 1.4	Yes	UL/CUL/TUV/CB/CE/EN	\$61.95
2240059	MEAN WELL	EPP-200-12	1	12	16.7		80 to 264	47 to 63	JST B6P-VH	4 x 2 x 1.14	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$40.90
2253853	MEAN WELL	EPP-400-12	1	12	20.8		80 to 264	47 to 63	Screw Terminals	5 x 3 x 1.38	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$68.80
2164252	MEAN WELL	EPP-300-12	1	12	25		90 to 264	47 to 63	Screw Terminals	5 x 3 x 1.4	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$57.00
2304511	MEAN WELL	EPP-500-12	1	12	26.7		80 to 264	47 to 63	Screw Terminals	5 x 3 x 1.57	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$82.70
2248667	MEAN WELL	EPS-45S-24	1	24	1.9		80 to 264	47 to 63	JST B2P-VH	3 x 2 x 0.95	No	UL/CUL/TUV/CB/CE/EN/EAC	\$12.70
2248739	MEAN WELL	EPS-65S-24	1	24	2.71		80 to 264	47 to 63	JST B2P-VH	3 x 2 x 0.95	No	UL/CUL/TUV/CB/CE/EN/EAC	\$13.30
2248675	MEAN WELL	EPS-45S-48	1	48	0.94		80 to 264	47 to 63	JST B2P-VH	3 x 2 x 0.95	No	UL/CUL/TUV/CB/CE/EN/EAC	\$12.70
2248747	MEAN WELL	EPS-65S-48	1	48	1.36		80 to 264	47 to 63	JST B2P-VH	3 x 2 x 0.95	No	UL/CUL/TUV/CB/CE/EN/EAC	\$13.30
668781	MEAN WELL	RPD-65C	2	12	4.5	5	90 to 264	47 to 440	Molex 5273-06	5 x 3 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	\$19.29
2188772	Umec USA	UP0401S-09		9	4.4		90 to 264	47 to 63	Molex 09-65-2068	3.58 x 2.48 x 1.13	No	UL/CSA/TUV/CB/CE	\$4.95
2234716	MEAN WELL	PS-65-12-MOD									No	UL/CUL/TUV/CB/CE/EN	\$13.95
2234724	MEAN WELL	PS-45-12-MOD									No	UL/CUL/TUV/CB/CE/EN	\$9.95