



[Click Here to Request a Large Quantity Quote](#)

[Circuit Protection-Fuses](#) [Resettable](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Current Rating	Voltage Rating	IHOLD (A)	ITRIP (A)	Initial Resistance Ohms @ 23°C MIN	Initial Resistance Ohms @ 23°C MAX	Mounting Feature	Terminal Placement	Number of Terminals	Price 1
2280487	TYCO Power Systems	LVR005S	1 A	240 VDC	0.05	0.12	18.5	31	Through Hole	Radial	2	\$0.39
2280367	TYCO Power Systems	LVR100S	10 A	240 VDC	1	2	0.218	0.334	Through Hole	Radial	2	\$1.49
2285887	TYCO Power Systems	RGE300K-2	100 A	16 VDC	3	5.1	0.035	0.105	Through Hole	Radial	2	\$0.49
866293	Advanced Micro Devices	RUEF300	100 A	30 VDC	3	6	0.02	0.08	Through Hole	Radial	2	\$0.49
2281231	Bourns	MF-R015/600-A-2	3 A	250 VDC	0.15	0.3	7	10	Through Hole	Radial	2	\$0.59
2281239	Bourns	MF-R015/600F-2	3 A	250 VDC	0.15	0.3	7	12	Through Hole	Radial	2	\$0.59
2281247	Bourns	MF-R016/600-1-2	3 A	250 VDC	0.16	0.32	4	8	Through Hole	Radial	2	\$0.59
2281255	Bourns	MF-R016/600-2	3 A	250 VDC	0.16	0.32	4	10	Through Hole	Radial	2	\$0.59
867288	Raychem/TYCO Electronics	TR600-160LF-0.130	3 A	250 VDC	0.16	0.32	18	22	Through Hole	Radial	2	\$0.59
1997615	Bourns	MF-R700	40 A	30 VDC	7	14	7	14	Through Hole	Radial	2	\$0.65
924166	Littelfuse	TR600-150-2	40 A	60 VDC	0.15	0.3	6	12	Through Hole	Radial	2	\$0.59
199874	Excel Cell Electronics	ERFRA050-60Z	40 A	60 VDC	0.5	1	0.5	1.17	Through Hole	Radial	2	\$0.55
199938	Excel Cell Electronics	ERFRA160-60Z	40 A	60 VDC	1.6	3.2	0.09	0.22	Through Hole	Radial	2	\$0.69
2285287	Littelfuse	RXE075	40 A	60 VDC	3	7.5	0.25	0.4	Through Hole	Radial	2	\$0.29
866736	Advanced Micro Devices	RXEF020	40 A	72 VDC	0.2	0.4	1.83	4.4	Through Hole	Radial	2	\$0.35