



[Click Here to Request a Large Quantity Quote](#)

[Rectangular Connectors-IDC](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Gender	No. of Contacts	No. of Rows	Maximum Voltage Rating	Maximum Current Rating	Maximum Contact Resistance	Contact Plating	Body Orientation	Housing Color	Price 1
2276959	TE Connectivity	3-641435-2	Plug	2	1	250VDC, 250VAC	1	20 mOhm	Tin	Right Angle	Orange	\$0.49
42658	Jameco Valuepro	8200-14-R	Plug	14	2	250VDC, 250VAC	1	30 mOhm	Phosphor Bronze	Right Angle	Black	\$0.89
42674	Jameco Valuepro	8200-16-R	Plug	16	2	250VDC, 250VAC	1	30 mOhm	Gold	Straight	Black	\$0.99
104097	Jameco Valuepro	8200-20-R	Plug	20	2	250VDC, 250VAC	1	30 mOhm	Phosphor Bronze	Straight	Black	\$1.09
2271415	Arndt	IDC-24-0.1	Plug	24	2	250VDC, 250VAC	1	20 mOhm	Gold	Right Angle	Black	\$1.19
42691	Jameco Valuepro	8200-24-R	Plug	24	2	250VDC, 250VAC	1	20 mOhm	Gold Over Nickel	Right Angle	Black	\$1.25
42712	Jameco Valuepro	8200-40-R	Plug	40	2	250VDC, 250VAC	1	30 mOhm	Phosphor Bronze	Straight	Black	\$1.39
2203910	Jameco Valuepro	8000-6-R	Receptacle	6	2	250VDC, 250VAC	1	20 mOhm	Gold	Right Angle	Black	\$0.25
32492	Jameco Valuepro	8000-10-R	Receptacle	10	2	250VDC, 250VAC	1	20 mOhm	Gold	Right Angle	Black	\$0.39
138376	Jameco Valuepro	8000-10NE	Receptacle	10	2	250VDC, 250VAC	1	20 mOhm	Gold	Right Angle	Black	\$0.39
742215	TE Connectivity	1658621-1	Receptacle	10	2	250VDC, 250VAC	1	20 mOhm	Gold Over Nickel	Right Angle	Black	\$0.79
153948	Jameco Valuepro	8000-14-R	Receptacle	14	2	250VDC, 250VAC	1	30 mOhm	Phosphor Bronze	Right Angle	Black	\$0.49
119467	Jameco Valuepro	8000-16-R	Receptacle	16	2	250VDC, 250VAC	1	20 mOhm	Gold	Right Angle	Black	\$0.55
525325	TE Connectivity	746285-3	Receptacle	16	2	250VDC, 250VAC	1	20 mOhm	Gold Over Nickel	Right Angle	Black	\$0.99
901722	TE Connectivity	1658622-3	Receptacle	16	2	250VDC, 250VAC	1	20 mOhm	Gold Over Nickel	Right Angle	Black	\$1.25

Jameco Part #	Manufacturer	Manufacturer Part #	Gender	No. of Contacts	No. of Rows	Maximum Voltage Rating	Maximum Current Rating	Maximum Contact Resistance	Contact Plating	Body Orientation	Housing Color	Price 1
32522	Jameco Valuepro	8000-20-R	Receptacle	20	2	250VDC, 250VAC	1	20 mOhm	Gold	Right Angle	Black	\$0.59
525333	TE Connectivity	746285-4	Receptacle	20	2	250VDC, 250VAC	1	20 mOhm	Gold Over Nickel	Right Angle	Black	\$1.39
901600	TE Connectivity	1658621-9	Receptacle	20	2	250VDC, 250VAC	1	20 mOhm	Gold Over Nickel	Right Angle	Black	\$2.09
32564	Jameco Valuepro	8000-26-R	Receptacle	26	2	250VDC, 250VAC	1	20 mOhm	Gold	Right Angle	Black	\$0.69
2218134	TE Connectivity	622-2630-B	Receptacle	26	2	250VDC, 250VAC	1	20 mOhm	Gold	Right Angle	Blue	\$0.89
901642	TE Connectivity	1658622-1	Receptacle	26	2	250VDC, 250VAC	1	20 mOhm	Gold Over Nickel	Right Angle	Black	\$0.75
32644	Jameco Valuepro	8000-34-R	Receptacle	34	2	250VDC, 250VAC	1	20 mOhm	Gold	Right Angle	Black	\$0.79
1963124	TE Connectivity	1-746610-5	Receptacle	40	2	250VDC, 250VAC	1	20 mOhm	Gold Over Nickel	Straight	White	\$1.49
32679	Jameco Valuepro	8000-40-R	Receptacle	40	2	250VDC, 250VAC	1	30 mOhm	Phosphor Bronze	Right Angle	Black	\$0.85
32708	Jameco Valuepro	8000-50-R	Receptacle	50	2	250VDC, 250VAC	1	20 mOhm	Gold	Right Angle	Black	\$0.89