

[Click Here to Request a Large Quantity Quote](#)

[Rectangular Connectors-Headers and PCB Receptacles \(BREAKAWAY\)](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Gender	Pitch (mm)	Body Orientation	Number of Rows	Number of Contacts	Contact Material	Contact Plating	Housing Color	Housing Material	Price 1
2302231	AVX	11-5016-2016-10-001	Male	1.27	Straight	2	16	Brass	Gold Flash	Black	Polybutylene Terephthalate	\$0.43
53576	Jameco Valuepro	7000-2X01RG-R	Male	2.54	Right Angle	2	20	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.65
53583	Jameco Valuepro	7000-2X13RG	Male	2.54	Right Angle	2	26	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.75
53605	Jameco Valuepro	7000-2X20RG-R	Male	2.54	Right Angle	2	40	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.99
53612	Jameco Valuepro	7000-2X25RG	Male	2.54	Right Angle	2	50	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.89
68339	Jameco Valuepro	1X36SG	Male	2.54	Straight	1	36	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.55
2120284	Adam Technologies	PH2-80-TA	Male	2.54	Straight	1	80	Brass	Gold	Black	Polybutylene Terephthalate	\$0.85
2302287	Molex	10-89-1103	Male	2.54	Straight	2	10	Brass	Gold Flash	Black	Polybutylene Terephthalate	\$0.89
67821	Jameco Valuepro	7000-2X5SG-R	Male	2.54	Straight	2	10	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.29
2280319	Samtec	TSW105-07-T-D	Male	2.54	Straight	2	10	Phosphor Bronze	Tin	Black	Polyester	\$0.39
203810	Jameco Valuepro	2012-254-2X6SG	Male	2.54	Straight	2	12	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.25
53495	Jameco Valuepro	7000-2X13SG	Male	2.54	Straight	2	13	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.35
118456	Jameco Valuepro	7000-2X7SG-R	Male	2.54	Straight	2	14	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.39
109568	Jameco Valuepro	7000-2X8SG-R	Male	2.54	Straight	2	16	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.43
2302223	Jameco Valuepro	7000-2X9SG-R	Male	2.54	Straight	2	18	Brass	Gold Flash	Black	Polybutylene Terephthalate	\$0.46

Jameco Part #	Manufacturer	Manufacturer Part #	Gender	Pitch (mm)	Body Orientation	Number of Rows	Number of Contacts	Contact Material	Contact Plating	Housing Color	Housing Material	Price 1
2076877	Jameco Valuepro	7000-2X9SG-R	Male	2.54	Straight	2	18	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.45
53480	Jameco Valuepro	7000-2X10SG-R	Male	2.54	Straight	2	20	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.49
2205528	Mill Max	460-10-220-00-001000	Male	2.54	Straight	2	20	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$2.25
203836	Jameco Valuepro	7000-2X11SG-R	Male	2.54	Straight	2	22	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.55
203844	Jameco Valuepro	2012-254-2X12SG	Male	2.54	Straight	2	24	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.59
203852	Jameco Valuepro	7000-2X14SG-R	Male	2.54	Straight	2	28	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.69
203879	Jameco Valuepro	7000-2X15SG-R	Male	2.54	Straight	2	30	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.75
203861	Jameco Valuepro	7000-2X16SG-R	Male	2.54	Straight	2	32	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.79
53517	Jameco Valuepro	7000-2X17SG-R	Male	2.54	Straight	2	34	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.39
203888	Jameco Valuepro	7000-2X18SG-R	Male	2.54	Straight	2	36	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.85
203895	Jameco Valuepro	7000-2X19SG-R	Male	2.54	Straight	2	38	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.85
109517	Jameco Valuepro	7000-2X4SG-R	Male	2.54	Straight	2	4	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.25
115027	Jameco Valuepro	C2X2SG	Male	2.54	Straight	2	4	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.14
53532	Jameco Valuepro	7000-2X20SG	Male	2.54	Straight	2	40	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.85
53560	Jameco Valuepro	7000-2X25SG-R	Male	2.54	Straight	2	50	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.89
115035	Jameco Valuepro	7000-2X3SG	Male	2.54	Straight	2	6	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.17
68574	Jameco Valuepro	7000-2X30SG	Male	2.54	Straight	2	60	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.95
103406	Jameco Valuepro	70002X36SG-R	Male	2.54	Straight	2	72	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.99

Jameco Part #	Manufacturer	Manufacturer Part #	Gender	Pitch (mm)	Body Orientation	Number of Rows	Number of Contacts	Contact Material	Contact Plating	Housing Color	Housing Material	Price 1
2200701	Berg Electronics	67997-472	Male	2.54	Straight	2	72	Phosphor Bronze	Tin	Black	High Temperature Plastic	\$0.59
2135312	Fujitsu	724P008AU	Male	2.54	Straight	2	8	Phosphor Bronze	Gold	Black	Thermoplastic	\$0.25
2280303	Samtec	ZW-04-10-T-D-590-120	Male	2.54	Straight	2	8	Phosphor Bronze	Tin Over Nickel	Black	Polyester	\$0.99
117197	Jameco Valuepro	7000-2X40SG-R	Male	2.54	Straight	2	80	Brass	Gold Over Nickel	Black	Polybutylene Terephthalate	\$1.29
164815	On Shore Technology	OSTOP240000	Male	5.00	Straight	1	24	Brass	Tin	Black	Thermoplastic	\$1.29