



[Click Here to Request a Large Quantity Quote](#)

Memory-SRAM

| Jameco Part #           | Manufacturer           | Manufacturer Part # | Description   | Supplier Package | Price 1 |
|-------------------------|------------------------|---------------------|---|------------------|---------|
| <a href="#">38957</a>   | Major Brands           | 2114N               | IC 2114N SRAM 4096-Bit (1024x4) 450ns 5V                              | DIP-18           | \$2.49  |
| <a href="#">38973</a>   | Major Brands           | 2114N-2             | IC 2114N-2 CMOS SRAM 4096-Bit (1024x4) 200ns                          | DIP-18           | \$2.95  |
| <a href="#">42198</a>   | Major Brands           | 5101                | IC 5101 CMOS SRAM 1024-Bit (256x4) 650ns                              | DIP-22           | \$5.95  |
| <a href="#">42809</a>   | Major Brands           | 6116P-3             | IC 6116P-3 CMOS SRAM 16,384-Bit (2Kx8) 150ns                          | DIP-24           | \$2.95  |
| <a href="#">242675</a>  | Major Brands           | 6116P-70            | IC 6116P-70 CMOS SRAM 16,384 Bit (2Kx8) 70 ns                         | DIP-24           | \$3.95  |
| <a href="#">42833</a>   | Major Brands           | 62256LP-10          | Static RAM 32K x 8-Bit High Speed CMOS 100ns DIP-28                   | DIP-28           | \$4.95  |
| <a href="#">42850</a>   | Major Brands           | 62256LP-15          | Static RAM 32K x 8-Bit High Speed CMOS 150ns DIP-28                   | DIP-28           | \$3.95  |
| <a href="#">82472</a>   | Major Brands           | 62256LP-70          | IC 62256LP-CMOS SRAM 256K-Bit (32Kx8) 70ns Low Power                  | DIP-28           | \$3.95  |
| <a href="#">42884</a>   | Major Brands           | 6264LP-10           | IC 6264LP-10 CMOS SRAM 64K-Bit (8Kx8) 100ns Low Power                 | DIP-28           | \$3.49  |
| <a href="#">85121</a>   | Major Brands           | 6264LP-70           | IC 6264LP-70 CMOS SRAM 64K-Bit (8Kx8) 70ns Low Power                  | DIP-28           | \$3.95  |
| <a href="#">42921</a>   | Major Brands           | 6264P-15            | Static RAM 8K x 8-Bit High Speed CMOS 150ns DIP-28                    | DIP-28           | \$3.95  |
| <a href="#">131810</a>  | Major Brands           | 628128LP-70         | IC 628128LP-70 CMOS SRAM 1M-Bit (128Kx8) 70ns Low Power               | DIP-32           | \$5.95  |
| <a href="#">157358</a>  | Major Brands           | 628512LP-70         | IC 628512LP-70 CMOS SRAM 4096-Bit (512Kx8) 70ns Low Power             | DIP-32           | \$12.95 |
| <a href="#">43238</a>   | Major Brands           | 6514                | IC 6514 1024 x 4 CMOS SRAM 4096-Bit (1024x4) 200ns Low Power          | DIP-18           | \$3.95  |
| <a href="#">43561</a>   | Major Brands           | 6810                | IC 6810 SRAM 1024-Bit (128x8) 450ns 1MHz 5V                           | DIP-24           | \$4.95  |
| <a href="#">2287943</a> | Cypress Semiconductor  | 7C168A-15PC         | IC 7C168A-15PC CMOS SRAM 16K-Bit (4Kx4) 15ns Low Power High Speed     | DIP-20           | \$2.95  |
| <a href="#">2303039</a> | Advanced Micro Devices | AM21L41-20PC        | 4K (4096x1) Static RAM TTL 200ns DIP-18                               | DIP-18           | \$3.95  |
| <a href="#">2288183</a> | Major Brands           | AS7C259-15PC        | IC AS7C259-15PC CMOS SRAM 294,912-Bit (32,768x9) 15ns High Speed      | DIP-32           | \$7.95  |
| <a href="#">391793</a>  | Cypress Semiconductor  | CY62256L-70PC       | IC CY62256L-70PC CMOS SRAM 256K-Bit (32kx8) 55/70ns Low Power         | DIP-28           | \$4.95  |
| <a href="#">391822</a>  | Cypress Semiconductor  | CY62256LL-70PC      | IC CY62256LL-70PC CMOS SRAM 256k-Bit 32kx8 Asynch 70ns Low Power      | DIP-28           | \$3.95  |
| <a href="#">2301855</a> | Cypress Semiconductor  | CY7C164-35PC        | Static RAM Memory 16Kx4 DIP-22  | DIP-22           | \$3.95  |
| <a href="#">242376</a>  | Major Brands           | CY7C199-35PC        | IC CY7C199-35PC CMOS SRAM 256K-Bit (32Kx8) 35ns 5V Chip Asynch Single | DIP-28           | \$3.95  |
| <a href="#">2302863</a> | Cypress Semiconductor  | CY7C199-55PC        | SRAM Asynchronous Memory 256KB (32Kx8) Parallel 15ns DIP-28           | DIP-28           | \$3.49  |
| <a href="#">2301863</a> | Cypress Semiconductor  | CY7C330-40WMB       | CMOS Programmable Synchronous State Machine DIP-28                    | DIP-28           | \$69.95 |
| <a href="#">2301871</a> | Cypress Semiconductor  | CY7C403-15PC        | 64x4 Cascadable FIFO DIP-16   | DIP-16           | \$9.95  |
| <a href="#">2297055</a> | NEC Corporation        | DG446C-2            | 2048 Word x 8-Bit Static CMOS RAM 200ns DIP-24                        | DIP-24           | \$7.95  |
| <a href="#">2297063</a> | NEC Corporation        | DG449C-2            | 2048 Word x 8-Bit Static CMOS RAM 200ns DIP-24                        | DIP-24           | \$4.95  |

| Jameco Part #           | Manufacturer                            | Manufacturer Part # | Description   | Supplier Package | Price 1 |
|-------------------------|---|---------------------|---|------------------|---------|
| <a href="#">2291391</a> | Dallas Semiconductor                    | DS1220AB-150        | IC NVSRAM (Non-Volatile SRAM) Memory 16Kb (2Kx8) Parallel 150ns 24-EDIP | EDIP-24          | \$12.95 |
| <a href="#">177113</a>  | Dallas Semiconductor                    | DS1230Y-100+        | IC DS1230Y-100 SRAM 256K-Bit (32Kx8) 100ns Non-Volatile                 |                  | \$16.95 |
| <a href="#">114323</a>  | Dallas Semiconductor                    | DS1230Y-150         | IC DS1230Y-150 SRAM 256K-Bit (32Kx8) 150ns Non-Volatile                 |                  | \$14.95 |
| <a href="#">2291431</a> | Dallas Semiconductor                    | DS1992L-F5          | iButton Memory NVRAM F5 MicroCan 125B                                   | MicroCan         | \$7.95  |
| <a href="#">2302527</a> | California Micro Devices                | G65SC32P-2          | Programmable CMOS RAM I/O Timer Device DIP-40                           | DIP-40           | \$14.95 |
| <a href="#">2291455</a> | Major Brands                            | GS1881CKA           | IC Video Sync Separator DIP-8   | SOIC-8           | \$2.95  |
| <a href="#">2288143</a> | HITACHI                                 | HM3-65728K-5        | IC HM3-65728K-5 CMOS SRAM 16K-Bit (2Kx8) 35ns Low Power High Speed      | DIP-24           | \$12.95 |
| <a href="#">242448</a>  | HITACHI                                 | HM628512LP-5        | IC 628512LP-55 CMOS SRAM 4096K-Bit (512Kx8) 55ns Low Power              | DIP-32           | \$15.95 |
| <a href="#">2302615</a> | Samsung Electronics                     | KM681000CLP-7L      | CMOS SRAM 125K x 8-Bit Low Voltage DIP-32                               | DIP-32           | \$5.95  |
| <a href="#">2287983</a> | Mitsubishi Electric and Electronics USA | M5M5118P            | IC M5M5118P CMOS SRAM 16,384-Bit (2048x8) 200ns                         | DIP-24           | \$2.95  |
| <a href="#">2287991</a> | National Semiconductor                  | MM2102AN-4L         | IC MM2102AN-4L NMOS SRAM 1024-Bit (1024x1) 250ns Low Power              | DIP-16           | \$1.95  |
| <a href="#">2302575</a> | Major Brands                            | MS6516L-10PC        | Static RAM 2K x 8-bit CMOS DIP-24                                       | DIP-24           | \$4.95  |
| <a href="#">2303135</a> | Intel Corporation                       | P2114AL-3           | Static RAM (SRAM) 4K (1Kx4) 150 ns DIP-18                               | DIP-18           | \$4.95  |
| <a href="#">2297071</a> | Major Brands                            | P4C164-25CC         | Ultra High Speed 8Kx8 Static CMOS RAM (SRAM) 25ns DIP-28                | DIP-28           | \$12.95 |
| <a href="#">2306935</a> | TI                                      | TMS2114L-20NL       | Static RAM (SRAM) 4-Bit (1024x4) 200ns Low Power DIP-18                 | DIP-18           | \$1.49  |
| <a href="#">2297047</a> | NEC Corporation                         | UPD431000ACZ-70L    | 1 Mbit CMOS Static RAM 128K-Word x 8-Bit DIP-32                         | DIP-32           | \$4.95  |