



[Click Here to Request a Large Quantity Quote](#)

Knobs - Plastic

Jameco Part #	Manufacturer	Manufacturer Part #	Shaft Dia.	Product Type	Indicator Style	Body Color	Material	Size (Dia." x H")	Mounting	Price 1
2288655	Jameco Valuepro	KS23	0.125" (1/8")	Fluted	N/A	Black	Plastic	0.92 x 0.58	Set Screw	\$0.79
2239138	Jameco Valuepro	JK-906D-3.2(1/8")	0.125" (1/8")	Fluted	Top Line White	Black	Phenolic	0.61 x 0.58	Set Screw	\$0.89
2288631	Jameco Valuepro	PKX-60B1/8	0.125" (1/8")	Fluted	Top Line White Dot	Black	Plastic	0.78 x 0.59	Set Screw	\$1.25
2239111	Jameco Valuepro	JK-901D-3.2(1/8")	0.125" (1/8")	Fluted	White Top Line	Black	Phenolic	0.78 x 0.47	Set Screw	\$0.69
2239120	Jameco Valuepro	JK-905C-3.2(1/8")	0.125" (1/8")	Ribbed	White Side Raised	Black/Blue	Phenolic	0.57 x 0.60	Set Screw	\$1.49
2288623	Jameco Valuepro	407-D-1-K1	0.125" (1/8")	Skirted Ribbed	White Skirt Arrow	Black	Plastic	1.03 x 0.81	Set Screw	\$0.99
2288647	Jameco Valuepro	TDK-1032	0.188" (10-32 Thread)	Tear Drop Axis Control	N/A	Black	Phenolic	0.75 x 1.25	10-32 Screw On	\$0.79
2288615	Jameco Valuepro	RP-316	0.188" (3/16")	Ribbed	Raised White Side Line	Red	Plastic	0.54 x 0.75	Slip On	\$0.65
2235778	Arndt	KN1564	0.234" (15/64")	Black Phenolic	Plastic Pointer	Black	Plastic	1.00 x 0.50	Set Screw	\$0.59
2236041	Eagle Plastics	450-3102GR	0.240" (6 mm)	Flutes (3)	White Side Line	Black/Alum	Plastic	0.78 x 0.63	Slip On D	\$0.55
2288639	Jameco Valuepro	KN6BG	0.240" (6 mm)	Ribbed	Grey Side Line	Black	Plastic	0.70 x 0.51	Slip On D	\$0.59
2236113	Kobiconn	450-2401	0.240" (6 mm)	Ribbed Skirted	White Side Line	Black	Phenolic/Alum	0.78 x 0.69	Slip On D	\$0.59
102788	Jameco Valuepro	JK903C-R	0.250" (1/4")	Black Phenolic	Top White Line	Black	Plastic	0.74 x 0.50	Set Screw	\$1.39
265261	Jameco Valuepro	CR-MS-5-T18	0.250" (1/4")	Fluted	Grey Side Line	Grey/Lt Grey	Phenolic	0.51 x 0.68	Knurled Shaft	\$0.49
2228543	Jameco Valuepro	JK-902D	0.250" (1/4")	Fluted	Top Line White	Black	Phenolic	0.75 x 0.42	Set Screw	\$0.69
265122	Jameco Valuepro	JK-906D-R	0.250" (1/4")	Fluted	Top Line White Dot	Black	Phenolic	0.61 x 0.58	Set Screw	\$1.39
104176	Jameco Valuepro	JK-902C	0.250" (1/4")	Fluted	White Line/Dot	Black	Phenolic	0.75 x 0.49	Set Screw	\$1.39
265009	Jameco Valuepro	JK-902B	0.250" (1/4")	Fluted	White Line/Dot	Black	Phenolic	0.95 x 0.60	Set Screw	\$1.39
264955	Jameco Valuepro	JK-901C-R	0.250" (1/4")	Fluted	White Line/Dot	Black	Phenolic	1.06 x 0.61	Set Screw	\$1.39
264998	Jameco Valuepro	JK-902A-R	0.250" (1/4")	Fluted	White Line/Dot	Black	Phenolic	1.31 x 0.69	Set Screw	\$1.39
264990	Jameco Valuepro	JK-901D-R	0.250" (1/4")	Fluted	White Side Line	Black	Phenolic	0.78 x 0.47	Set Screw	\$1.39
265018	Jameco Valuepro	JK-904A-R	0.250" (1/4")	Fluted	White Side Line	Black/Red	Phenolic	0.78 x 0.47	Set Screw	\$1.39
265077	Jameco Valuepro	JK-905C-R	0.250" (1/4")	Ribbed	White Side Raised	Black/Blue	Phenolic	0.57 x 0.58	Set Screw	\$1.39
265084	Jameco Valuepro	JK-905D	0.250" (1/4")	Ribbed	White Side Raised	Black/Green	Phenolic	0.57 x 0.58	Set Screw	\$1.39
265051	Jameco Valuepro	JK-905A-R	0.250" (1/4")	Ribbed	White Side Raised	Black/Red	Phenolic	0.57 x 0.58	Set Screw	\$1.39
265069	Jameco Valuepro	JK-905B-R	0.250" (1/4")	Ribbed	White Side Raised	Black/Yellow	Phenolic	0.57 x 0.58	Set Screw	\$1.39
2229634	Arndt	EWKNOB21	0.250" (1/4")	Ribbed	White To Dot	Black	Phenolic	0.64 x 0.35	Set Screw	\$0.59

Jameco Part #	Manufacturer	Manufacturer Part #	Shaft Dia.	Product Type	Indicator Style	Body Color	Material	Size (Dia." x H")	Mounting	Price 1
264883	Jameco Valuepro	RN-112A-R	0.250" (1/4")	Skirted Ribbed	Numbered 1-10	Black/Alum	Phenolic/Alum	1.46 x 0.92	Set Screw	\$1.39
202287	Jameco Valuepro	G/S(CP-Z1-M-S)-R	0.250" (1/4")	Skirted Ribbed	White Skirt Line	Black	Plastic	0.80 x 0.60	Set Screw	\$1.39
2288663	Jameco Valuepro	RB-67-5-DC	0.375" (3/8")	Ribbed	N/A	Black	Plastic	2.25 x 1.00	Set Screw	\$1.25