



[Click Here to Request a Large Quantity Quote](#)

[5 Volt DC Brushless Fan](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Voltage (VDC)	Height - mm	Width - mm	Depth - mm	Air Flow (CFM)	Bearing	Current (mA)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1
2302815	Sunon	MC20080V2-000U-A99	5	20	20	8	1.3	Vapo	90	UL/CSA/VDE/CE	21	5.5"	\$9.95
2095277	ADDA Corporation	AD2005LX-G70	5	20	20	10	0.6	Hypro	80	UL/CUL/TUV/CE/CSA	20	5.5"	\$9.95
2289247	SEPA	MFB25A-05	5	25	25	10	1.9	Ball	85	-	17	2" w/ 2P connector	\$3.95
2132197	ADDA Corporation	AD0205MB-G50GL	5	25	25	10	2.2	Ball	120	UL/CUL/TUV/CE/CSA	23	5.5"	\$4.95
2276575	Toshiba	D25MO5P-1	5	25	25	10	2.3	Ball	70	-	9.5	2.5"	\$6.95
695050	Sunon	MC25100V2-0000-99	5	25	25	10	3	Vapo	80	UL/CUL	16	5.5"	\$8.95
2302823	Sunon	KDE0503PEB-2-8(MS.N)	5	30	30	6	4.3	Ball	150	UL/CSA/VDE/CE	24.5	5.5"	\$9.95
2234695	Sunon	MC30060V1-0000-A99	5	30	30	6	4.9	Vapo	112	UL/CUL/TUV	28	6"	\$9.95
2188924	ADDA Corporation	AD0305HX-K70(TX)	5	30	30	6.8	3.5	Ball	120	UL/CUL/TUV	32	12"	\$7.95
2304895	Gulf Electrics	GD053010MB-N (2F5)	5	30	30	10	3	Ball	80	UL/CUL/CE	18	(3) 12", speed sensor	\$7.95
2304887	Gulf Electrics	GD053010EB-N (2I9)	5	30	30	10	4	Dual Ball	120	UL/CUL/CE	28	12"	\$7.95
2304255	ADDA Corporation	AD0405LX-G70(XT1)	5	40	40	10	4.1	Hypro	80	UL/CUL/TUV/CE	14	12"	\$9.95
2231742	ADDA Corporation	AD0405LB-G70	5	40	40	10	4.7	Ball	80	UL/CUL/TUV/CE	21	11"	\$5.95
2258814	ADDA Corporation	AD0405MB-G76-LF	5	40	40	10	5	Ball	110	UL/CE	22	(3) 4" w/ conn., speed sensor	\$3.95
2302831	Sunon	KDE0504PFS2-8	5	40	40	10	5.6	Sleeve	110	UL/CSA/VDE/CE	24	11"	\$6.95
2131928	ADDA Corporation	AD0405MX-G76-LF	5	40	40	10	5.7	Hypro	110	UL/CUL/TUV/CE	20	(3) 11", speed sensor	\$4.95
1928353	ADDA Corporation	AD0405HX-G70	5	40	40	10	6.7	Hypro	190	UL/CUL/TUV/CE	30	11"	\$8.95
2132189	ADDA Corporation	AD0405HB-G70(TS)	5	40	40	10	8.7	Ball	100	UL/CUL/TUV/CE/CSA	25	12 w/ conn.	\$9.95

Jameco Part #	Manufacturer	Manufacturer Part #	Voltage (VDC)	Height - mm	Width - mm	Depth - mm	Air Flow (CFM)	Bearing	Current (mA)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1
2230993	Delta Electronics	FBK04F05L	5	40	40	20	3.9	Ball	120	UL	24	11"	\$4.95
1928361	ADDA Corporation	AD0405DS-C50(T1)	5	40	40	20	4.7	Sleeve	120	UL/TUV/CE	10	12"	\$4.95
2121295	ADDA Corporation	AD0405HB-C50	5	40	40	20	5.7	Ball	110	UL/TUV/CSA	20	3.5" w/ conn.	\$3.95
2120057	Sunon	KD0504PKB2(2).GN	5	40	40	20	7.7	Ball	142	UL/CUL/TUV	29	12"	\$7.95
2304903	Gulf Electrics	GD054020ML-N (1F5)	5	40	40	20	8.06	Sintetico	100	UL/CUL/CE	22	12"	\$8.95
2304911	Gulf Electrics	GD054020HL-N (1F7)	5	40	40	20	10.05	Sintetico	170	UL/CUL/CE	26.5	(3) 12", speed sensor	\$8.95
2150774	ADDA Corporation	AD0505MB-G70	5	50	50	10	10.5	Ball	180	UL/CUL/TUV/CE	24	12"	\$8.95
1776257	Delta Electronics	AFB0605MB	5	60	60	15	13.5	Ball	200	UL/CSA/VDE/CE	29	12.9"	\$9.95
2132120	ADDA Corporation	AD0605LB-A72GL-LF	5	60	60	25	13.82	Ball	250	UL/CSA/TUV	16.1	(3) 12", alarm	\$4.95
2306471	Delta Electronics	AFB0605M	5	60	60	25	16.2	Dual Ball	330	UL/CUL/TUV/CE	31	8" w/ conn.	\$5.95
2271127	ADDA Corporation	AG06005MB257103	5	60	60	25	23.3	Ball	300	UL/CUL/TUV/CE	37.1	12"	\$6.95
2131952	ADDA Corporation	AD0605HB-A72GL	5	60	60	25	24.3	Ball	250	UL/CSA/TUV/CE	28.8	(3) 12", alarm	\$6.95
2233211	ADDA Corporation	AD0805HS-D71	5	80	80	15	29.9	Sleeve	430	UL/CUL/TUV/CE	31.4	12"	\$6.95