



[Click Here to Request a Large Quantity Quote](#)

Memory-EPROM

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Supplier Package	Organization	Density	Maximum Random Access Time	Output Enable Access Time	Price 1
39950	Major Brands	27128A-15	IC 27128A-15 EPROM 128K-Bit 150ns NMOS UV Erasable Electrically Programmable Memory	DIP-28	16Kx8	128KBit	150ns	50ns	\$3.95
39968	Major Brands	27128A-20	UV EPROM NMOS 128Kb (16Kx8) DIP-28	DIP-28	16Kx8	128KBit	200ns	75ns	\$4.95
40002	Major Brands	2716	IC 2716 EPROM 16K-Bit 450ns NMOS UV Erasable and Electrically Programmable EPROM	DIP-24	2Kx8	16KBit	450ns	120ns	\$3.95
40011	Major Brands	2716-1	IC 2716-1 EPROM 16K-Bit 350ns NMOS UV Erasable and Electrically Programmable EPROM	DIP-24	2Kx8	16KBit	350ns	120ns	\$4.49
308662	Major Brands	2716A-2	IC 2716A-2 EPROM 16K-Bit 200ns NMOS UV Erasable PROM	DIP-24	2Kx8	16KBit	200ns	75ns	\$4.95
40045	Major Brands	27256-20	256K (32Kx8) UV Erasable PROMS (EPROM) 5V DIP-28 200ns	DIP-28	32Kx8	256KBit	200ns	55ns	\$8.95
40096	Major Brands	2732	IC 2732 EPROM 32K-Bit 450ns NMOS UV Erasable and Electrically Programmable EPROM	DIP-24	4Kx8	32KBit	450ns	100ns	\$5.95
40125	Major Brands	2732A-25	IC 2732A-25 EPROM 32K-Bit 250ns NMOS UV Erasable and Electrically Programmable EPROM	DIP-24	4Kx8	32KBit	250ns	100ns	\$4.95
40192	Major Brands	2764-20	IC 2764-20 EPROM 64K-Bit 200ns NMOS UV Erasable and Electrically Programmed EPROM	DIP-28	8Kx8	64KBit	200ns	75ns	\$4.95
40248	Major Brands	2764A-25	IC 2764A-25 EPROM 64K-Bit 250ns CMOS Express ROM Device	DIP-28	8Kx8	64KBit	250ns	50ns	\$4.25
74624	Major Brands	27C010-12	IC 27C010-12 EPROM 1MEG-Bit 120ns CMOS UV Erasable Programmable ROM	DIP-32	128Kx8	1MBit	120ns	55ns	\$3.95
146149	Major Brands	27C010-70	IC 27C010-70 EPROM 1MEG-Bit 70ns CMOS Ultraviolet Erasable Programmable Rom	DIP-32	128Kx8	1MBit	70ns	40ns	\$4.95
65699	Major Brands	27C020-15	IC 27C020-15 EPROM 2M-Bit 150ns CMOS UV Erasable EPROM and OTP EPROM	DIP-32	256Kx8	2MBit	150ns	65ns	\$3.95
102293	Major Brands	27C040-12	IC 27C040-12 EPROM 4M-Bit 120ns CMOS Ultraviolet Erasable Programmable Rom	DIP-32	512Kx8	4MBit	120ns	50ns	\$6.45
85462	Major Brands	27C040-15	IC 27C040-15 EPROM 4096K-Bit 150ns CMOS UV Erasable Programmed ROM	DIP-32	512Kx8	4MBit	150ns	65ns	\$5.95

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Supplier Package	Organization	Density	Maximum Random Access Time	Output Enable Access Time	Price 1
266124	Major Brands	27C040-70	IC 27C040-70 EPROM 4M-Bit 70ns CMOS UV Erasable Programmable ROM	DIP-32	512Kx8	4MBit	70ns	35ns	\$6.95
2303695	SGS Thomson	27C1001-12C1	EPROM OTP Memory IC 1MB (128Kx8) Parallel 120ns PLCC-32	PLCC-32	128Kx8	1MBit	120ns	50ns	\$5.95
203641	Advanced Micro Devices	27C1024-120DC	IC 27C1024-120 EPROM 1M-Bit 120ns CMOS Ultraviolet Erasable PROM (Ceramic Pkg)	DIP-40	64Kx16	1MBit	120ns	45ns	\$3.95
87935	Major Brands	27C128-12	IC 27C128-12 EPROM 128K-Bit 120ns CMOS UV Erasable Programmable ROM	DIP-28	16Kx8	128KBit	120ns	50ns	\$4.95
39677	Major Brands	27C128-15	CMOS UV EPROM 128K (16K x 8-Bit) 150ns DIP-28	DIP-28	16Kx8	128KBit	150ns	70ns	\$4.75
39685	Major Brands	27C128-25	IC 27C128-25 EPROM 128K-Bit 250ns CMOS Ultraviolet Erasable Programmable Rom	DIP-28	16Kx8	128KBit	250ns	50ns	\$3.95
112740	Major Brands	27C256-10	IC 27C256-10 EPROM 256K-Bit 100ns CMOS UV Erasable Programmable ROM	DIP-28	32Kx8	256KBit	100ns	50ns	\$4.95
39714	Major Brands	27C256-15	IC 27C256-15 EPROM 256K-Bit 150ns CMOS UV Erasable Prommable ROM	DIP-28	32Kx8	256KB	150ns	65ns	\$4.49
39722	Major Brands	27C256-20	IC 27C256-20 EPROM 256K-Bit 200ns CMOS UV EPROM AND OTP EPROM	DIP-28	32Kx8	256KBit	200ns	75ns	\$3.95
39731	Major Brands	27C256-25	IC 27C256-25 EPROM 256K-Bit 250ns CMOS Electrically Programmable ROM	DIP-28	32Kx8	256KBit	250ns	75ns	\$3.49
140476	Major Brands	27C256-70	IC 27C256-70 EPROM 256K-Bit 70ns CMOS Ultraviolet Erasable Programmable ROM	DIP-28	32Kx8	256KBit	70ns	40ns	\$5.95
131959	Major Brands	27C512-10	IC 27C512-10 EPROM 512K-Bit 100ns CMOS Ultraviolet Erasable ROM	DIP-28	64Kx8	512KBit	100ns	50ns	\$4.49
39781	Major Brands	27C512-15	IC 27C512-15 EPROM 512K-Bit 150ns UV EPROM and OTP EPROM	DIP-28	64Kx8	512KBit	150ns	40ns	\$3.25
39790	Major Brands	27C512-20	5 VOLT 64KX8 DIP-28 200 NANOSECONDS EPROM	DIP-28	64Kx8	512KBit	200ns	75ns	\$2.95
203625	Major Brands	27C512-70	IC 27C512-70 EPROM 512K-Bit 70ns UV EPROM and OTP EPROM	DIP-28	64Kx8	512KBit	70ns	40ns	\$4.95
266036	Major Brands	27C64-10	IC 27C64-10 EPROM 64K-Bit 100ns UV Erasable and Electrically Reprogrammed CMOS PROM	DIP-28	8Kx8	64KBit	100ns	60ns	\$5.95
105304	Major Brands	27C64-12	IC 27C64-12 EPROM 64K-Bit 120ns CMOS UV Erasable Programmable ROM	DIP-28	8Kx8	64KBit	120ns	50ns	\$5.49
39829	Major Brands	27C64-15	IC 27C64-15 EPROM 64k-Bit 150ns CMOS UV Erasable Programmable ROM	DIP-28	8Kx8	64KBit	150ns	50ns	\$4.95
74608	Major Brands	27C64-20	IC 27C64-20 EPROM 65,536-Bit 200ns CMOS UV Erasable	DIP-28	8Kx8	64KBit	200ns	60ns	\$3.75

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Supplier Package	Organization	Density	Maximum Random Access Time	Output Enable Access Time	Price 1
			Electrically Programmable OTP						
2303047	Advanced Micro Devices	AM27128-200PC	EPROM OTP 128K (16Kx8) 200ns 5V DIP-28	DIP-28	16Kx8	128KBit	200ns	75ns	\$3.95
2303055	Advanced Micro Devices	AM27256-1D	EPROM OTP 256K (32Kx8) 8-Bit 200ns 5V DIP-28	DIP-28	32Kx8	256KBit	170ns	75ns	\$4.95
2303063	Advanced Micro Devices	AM27C010-255DC	CMOS EPROM 1MB (128Kx8) 8-Bit 250ns 5V DIP-32	DIP-32	128Kx8	1MBit	250ns	75ns	\$4.95
266044	Advanced Micro Devices	AM27C64-90DC	CMOS UV EPROM 64K (8Kx8-bit) 90ns DIP-28	DIP-28	8Kx8	64KBit	90ns	40ns	\$5.95
2287935	Advanced Micro Devices	AM27S281APC	IC AM27S281 PROM 8,192-Bit 80ns Bipolar Schottky TTL Prom (one time programmable)	PDIP-28	1Kx8	8KBit	80ns	40ns	\$4.95
2303967	Atmel (Microchip)	AT27C010-12PC	EPROM - OTP Memory 1MB (128Kx8) Parallel 120ns DIP-32	DIP-32 (0.6"W)	128Kx8	1MBit	120ns	35ns	\$2.95
40061	Intel Corporation	D27256	IC 27256-25 EPROM 256K-Bit 250ns Production UV Erasable PROM	DIP-28	32Kx8	256KBit	250ns	60ns	\$4.95
2303127	Intel Corporation	D27C210-200V10	CHMOS EPROM 1M (64Kx16) 120ns DIP-40	DIP-40	64Kx16	1MBit	200ns	70ns	\$5.95
40230	Major Brands	M2764A-2F1	IC 2764A-20 EPROM 64K-Bit 200ns CMOS Express ROM Device Programmed & Tested OTP	DIP-28	8Kx8	64KBit	200ns	50ns	\$4.49
697944	STMicroelectronics	M27C1001-10F1	IC 27C1001-10 EPROM 1M-Bit 100ns UV EPROM and OTP EPROM	DIP-32	128Kx8	1MBit	100ns	50ns	\$7.95
697961	STMicroelectronics	M27C1001-12F1	IC 27C101-12 EPROM 1M-Bit 128Kx8 32-pin DIP 120ns	FDIP-32	128Kx8	1Mbit	120ns	60ns	\$7.95
697987	STMicroelectronics	M27C1001-15F1	IC 27C1001 EPROM 1M-Bit 150ns Ultraviolet Erase and OTP (one time programmable)	DIP-32	128Kx8	1MBit	120ns	60ns	\$6.95
2303295	SGS Thomson	M27C1001-20	UV EPROM 1MB (128Kx8) 200ns 5V DIP-32	DIP-32	128Kx8	1MBit	200ns	60ns	\$6.95
698023	STMicroelectronics	M27C2001-10F1	EPROM U Volt 2M-Bit 256K x 8 100ns 32-Pin CFDIPW Tube	DIP-32	256Kx8	2MBit	100ns	50ns	\$6.95
698031	STMicroelectronics	M27C2001-12F1	IC 27C2001-12 EPROM 2M-Bit 120ns UV EPROM and OTP EPROM	DIP-32	256Kx8	2MBit	120ns	50ns	\$5.95
698082	STMicroelectronics	M27C256B-10F1	IC 27C256B-10 EPROM 256K-Bit 100ns UV EPROM and OTP EPROM	DIP-28	32Kx8	256KBit	100ns	50ns	\$5.49
698091	STMicroelectronics	M27C256B-12F1	IC 27C256B-12 EPROM 256K-Bit 120ns UV EPROM and OTP EPROM	DIP-28	32Kx8	256KBit	120ns	60ns	\$4.95
698111	STMicroelectronics	M27C256B-15F1	IC 27C256B-15 EPROM 256K-Bit 150ns UV EPROM and OTP EPROM	DIP-28	32Kx8	256KBit	150ns	65ns	\$4.49
698226	STMicroelectronics	M27C512-12F1	IC 27C512-12 EPROM 512K-Bit 120ns UV EPROM and OTP EPROM	DIP-28	64Kx8	512KBit	120ns	50ns	\$4.95

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Supplier Package	Organization	Density	Maximum Random Access Time	Output Enable Access Time	Price 1
698234	STMicroelectronics	M27C512-15F1	IC 27C512-15 EPROM 512K-Bit 150ns UV EPROM and OTP EPROM	DIP-28	64Kx8	512KBit	150ns	60ns	\$4.49
698322	STMicroelectronics	M27C64A-15F1	IC 27C64A-15 EPROM 64K-Bit 150ns UV EPROM	DIP-28	8Kx8	64KBit	150ns	75ns	\$5.95
2303119	Fujitsu	MBM2764-30	NMOS UV EEPROM 64K (8Kx8) 300ns DIP-28	DIP-28	8Kx8	64KBit	300ns	105ns	\$3.95
2303143	Major Brands	MD2202-D48	DiskOnChip 2000 DIP Flash Memory 48MB DIP-32	DIP-32 (0.6"W)	n/a	48MBit	130ns	91ns	\$49.95
33611	TI	TMS2716JL	IC 2716 EPROM 16,384-Bit 450ns Eraseable Programmable Rom	DIP-24	2Kx8	16KBit	450ns	n/a	\$9.95
2303207	TI	TMS27C010A-15JL	EPROM 1M (128Kx8) CMOS 150ns DIP-32	DIP-32	128Kx8	1MBit	150ns	75ns	\$6.95
2288047	Major Brands	WS57C45-35MB	IC 57C45-35 PROM 16K-Bit 35ns Registered CMOS High Speed Military (one time programmable)	PDIP-24	2Kx8	16KBit	35ns	15ns	\$9.95
2303215	Major Brands	X2816AP-45	EEPROM 2Kx8 NMOS 450ns PDIP-24	DIP-24	2Kx8	16KBit	450ns	150ns	\$6.95
2303231	Major Brands	X28C256D-25	Byte Alterable EEPROM 32K x 8-Bit 5V 250ns CDIP-28	DIP-28	32Kx8	256KBit	250ns	100ns	\$19.95