



[Click Here to Request a Large Quantity Quote](#)

[Bourns 3362 Series Potentiometer and Equivalents](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Manufacturer Series	Family	Resistance (Ohms)	Power Rating	Tolerance (%)	Number of Turns	Actuator Type	Actuator Orientation	Price 1
<a href="#">2194751</a>	BI Technologies	25WR201 (3362H-1-201)	3362	H	200	0.5 W	10	1	Top Cross	Top	\$0.99
<a href="#">2291719</a>	Bourns	3362H-1-102LF/VP	3362	H	1000	0.5 W	10	1	Top Slot	Top	\$0.99
<a href="#">2194742</a>	BI Technologies	25WR202 (3362H-1-202)	3362	H	2000	0.5 W	10	1	Top Cross	Top	\$0.99
<a href="#">2291727</a>	Bourns	3362H-1-502LF/VP	3362	H	5000	0.5 W	10	1	Top Slot	Top	\$0.99
<a href="#">770371</a>	Jameco Valuepro	3362H-1-103VP	3362	H	10000	0.5 W	10	1	Top Cross	Top	\$0.99
<a href="#">2194777</a>	BI Technologies	25WR500K (3362H-1-504)	3362	H	500000	0.5 W	10	1	Top Cross	Top	\$0.79
<a href="#">2194734</a>	BI Technologies	25WR105 (3362H-1-105)	3362	H	1 Meg	0.5 W	10	1	Top Cross	Top	\$0.99
<a href="#">2194697</a>	BI Technologies	25VR101 (3362M-1-101)	3362	M	100	0.5 W	10	1	Side Cross	Side	\$0.99
<a href="#">2280895</a>	Bourns	3362M-1-102LF	3362	M	1000	0.5 W	10	1	Side Cross	Side	\$0.99
<a href="#">2194700</a>	BI Technologies	25VR205 (3362M-1-205)	3362	M	2 Meg	0.5 W	10	1	Side Cross	Side	\$0.99
<a href="#">770419</a>	Bourns	3362P-1-101LF	3362	P	100	0.5 W	10	1	Top Cross	Top	\$0.99
<a href="#">182810</a>	Bourns	3362P-1-501LF	3362	P	500	0.5 W	10	1	Top Cross	Top	\$0.99
<a href="#">253982</a>	Bourns	3362P-1-102VP	3362	P	1000	0.5 W	10	1	Top Cross	Top	\$0.99
<a href="#">2201586</a>	BI Technologies	25PR202 (3362P-1-202LP)	3362	P	2000	0.5 W	10	1	Top Cross	Top	\$0.99
<a href="#">182829</a>	Bourns	3362P-1-502VP	3362	P	5000	0.5 W	10	1	Top Cross	Top	\$0.99
<a href="#">182837</a>	Jameco Valuepro	3362P-1-103VP(25PR10)	3362	P	10000	0.5 W	10	1	Top Cross	Top	\$0.99
<a href="#">254002</a>	Jameco Valuepro	25PR203/3362P-1-203VP	3362	P	20000	0.5 W	10	1	Top Cross	Top	\$0.99
<a href="#">254028</a>	Jameco Valuepro	3362P-1-503VP	3362	P	50000	0.5 W	10	1	Top Cross	Top	\$0.99
<a href="#">254036</a>	Jameco Valuepro	3362P-1-104VP/LF	3362	P	100000	0.5 W	10	1	Top Cross	Top	\$0.99
<a href="#">254044</a>	Jameco Valuepro	3362P-1-504VP/LF	3362	P	500000	0.5 W	10	1	Top Cross	Top	\$0.99
<a href="#">254115</a>	Jameco Valuepro	3362P-1-105VP	3362	P	1 Meg	0.5 W	10	1	Top Cross	Top	\$0.99
<a href="#">2285599</a>	Bourns	3362S-1-101LF	3362	S	100	0.5 W	10	1	Side Cross	Side	\$0.99
<a href="#">2194646</a>	BI Technologies	25SR20K (3362S-1-203VP)	3362	S	20000	0.5 W	10	1	Side Cross	Side	\$0.99
<a href="#">770540</a>	Jameco Valuepro	25UR200/3362U-1-200VP	3362	U	20	0.5 W	10	1	Top Cross	Top	\$0.99

Jameco Part #	Manufacturer	Manufacturer Part #	Manufacturer Series	Family	Resistance (Ohms)	Power Rating	Tolerance (%)	Number of Turns	Actuator Type	Actuator Orientation	Price 1
<a href="#">2133771</a>	Philips Semiconductor	CT-6U102/3362U-1-102VP	3362	U	1000	0.5 W	10	1	Top Cross	Top	\$0.99
<a href="#">770523</a>	Bourns	3362U-1-102LF	3362	U	1000	0.5 W	10	1	Top Cross	Top	\$0.99
<a href="#">2194689</a>	BI Technologies	25UR200K (3362U-1-204)	3362	U	200000	0.5 W	10	1	Top Cross	Top	\$0.99
<a href="#">2133780</a>	Jameco Valuepro	3362U-1-105LF	3362	U	1 Meg	0.5 W	10	1	Top Cross	Top	\$0.79
<a href="#">2285583</a>	Bourns	3362W-1-101LF	3362	W	100	0.5 W	10	1	Side Cross	Side	\$0.99
<a href="#">254166</a>	BI Technologies	25RXR501/62-2-1 (3362W-1)	3362	W	500	0.5 W	10	1	Side Cross	Side	\$0.79
<a href="#">254204</a>	Jameco Valuepro	3362W-1-103VP	3362	W	10000	0.5 W	10	1	Side Cross	Side	\$0.99
<a href="#">254211</a>	BI Technologies	25RXR20K (3362W-1-203)	3362	W	20000	0.5 W	10	1	Side Cross	Side	\$0.99
<a href="#">254262</a>	BI Technologies	25RXR500K (3362W-1-504)	3362	W	500000	0.5 W	10	1	Side Cross	Side	\$0.99
<a href="#">2194785</a>	BI Technologies	25XR500K (3362X-1-504)	3362	X	500000	0.5 W	10	1	Side Cross	Side	\$0.99
<a href="#">2194620</a>	BI Technologies	25RSR1K (3362Z-1-102VP)	3362	Z	1000	0.5 W	10	1	Side Cross	Side	\$0.79
<a href="#">2194638</a>	BI Technologies	25RS2K (3362Z-1-202)	3362	Z	2000	0.5 W	10	1	Side Cross	Side	\$0.99