



[Click Here to Request a Large Quantity Quote](#)

[Bourns 3329 Series Potentiometer and Equivalents](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Manufacturer Series	Family	Resistance (Ohms)	Power Rating	Tolerance (%)	Number of Turns	Actuator Type	Actuator Orientation	Price 1
2195850	BI Technologies	82PFR10 (3329H-1-100)	3329	H	10	0.5 W	20	1	Top Slot	Top	\$1.95
2195286	BI Technologies	82PFR20 (3329H-1-200)	3329	H	20	0.5 W	20	1	Top Slot	Top	\$1.49
1947626	BI Technologies	62PR50 (3329H-1-500)	3329	H	50	0.5 W	10	1	Top Slot	Top	\$1.95
770021	BI Technologies	82PR100/82MR100 (3329H-1)	3329	H	100	0.5 W	10	1	Top Slot	Top	\$1.95
854436	BI Technologies	62PR200/62-3-1/201(3329H)	3329	H	200	0.5 W	10	1	Top Slot	Top	\$1.95
2179235	Spectrol/Vishay Corporation	62-3-1/2-251 (3329H-1-251	3329	H	250	0.5 W	10	1	Top Slot	Top	\$1.95
2180383	BI Technologies	62PR500 (3329H-1-501)	3329	H	500	0.5 W	10	1	Top Slot	Top	\$1.95
2179278	Spectrol/Vishay Corporation	75H102/3329H-1-102	3329	H	1000	0.5 W	10	1	Top Slot	Top	\$1.49
1157907	BI Technologies	82PR1K (3329H-1-102)	3329	H	1000	0.5 W	10	1	Top Slot	Top	\$1.25
854356	Spectrol/Vishay Corporation	62-3-1/2-102 (3329H-1-102	3329	H	1000	0.5 W	10	1	Top Slot	Top	\$1.95
854452	Spectrol/Vishay Corporation	62-3-1/2-202 (3329H-1-202	3329	H	2000	0.5 W	10	1	Top Slot	Top	\$1.25
1157931	BI Technologies	62PR2K (3329H-1-202)	3329	H	2000	0.5 W	10	1	Top Slot	Top	\$1.49
2180391	Bourns	3329H-1-202LF	3329	H	2000	0.5 W	10	1	Top Slot	Top	\$1.49
854532	Vishay	3329H-1-502(62-3-1/2-502)	3329	H	5000	0.5 W	10	1	Top Slot	Top	\$1.95
1157940	BI Technologies	82PFR5K/82PR5K (3329H-1-5	3329	H	5000	0.5 W	10	1	Top Slot	Top	\$1.25
2179286	Spectrol/Vishay Corporation	75H103 (3329H-1-103)	3329	H	10000	0.5 W	10	1	Top Slot	Top	\$1.25
1157915	BI Technologies	62PR10K /3329H-1-103	3329	H	10000	0.5 W	10	1	Top Slot	Top	\$1.95
854487	BI Technologies	82PR20K/3329H-1-203LF	3329	H	20000	0.5 W	10	1	Top Slot	Top	\$1.25
854399	BI Technologies	82PR50K (3329H-1-503-VP)	3329	H	50000	0.5 W	10	1	Top Slot	Top	\$1.25
854567	Spectrol/Vishay Corporation	62-3-1/2-503 (3329H-1-503	3329	H	50000	0.5 W	10	1	Top Slot	Top	\$1.95
770030	BI Technologies	62PR100K (3329H-1-104)	3329	H	100000	0.5 W	10	1	Top Slot	Top	\$1.49

Jameco Part #	Manufacturer	Manufacturer Part #	Manufacturer Series	Family	Resistance (Ohms)	Power Rating	Tolerance (%)	Number of Turns	Actuator Type	Actuator Orientation	Price 1
2180404	Spectrol/Vishay Corporation	75H100K (3329H-1-104)	3329	H	100000	0.5 W	10	1	Top Slot	Top	\$1.25
770056	BI Technologies	62PR200K (3329H-1-204)	3329	H	200000	0.5 W	10	1	Top Slot	Top	\$1.95
2133667	Bourns	3329H-1-504LF	3329	H	500000	0.5 W	10	1	Top Slot	Top	\$1.95
254561	BI Technologies	82MR20 (3329P-1-200-VP)	3329	P	20	0.5 W	10	1	Top Slot	Top	\$1.95
854508	Spectrol/Vishay Corporation	62-1-1/2-501 (3329P-1-501)	3329	P	500	0.5 W	10	1	Top Slot	Top	\$1.49
95441	Bourns	3329P-1-102LF (T7YA1K)	3329	P	1000	0.5 W	10	1	Top Slot	Top	\$1.95
254502	BI Technologies	82MR2K (3329P-1-202-VP)	3329	P	2000	0.5 W	10	1	Top Slot	Top	\$1.95
254511	BI Technologies	62MR5K (3329P-1-502-VP)	3329	P	5000	0.5 W	10	1	Top Slot	Top	\$1.95
96719	Jameco Valuepro	3221P10K/3329P-1-103VP/LF	3329	P	10000	0.5 W	10	1	Top Slot	Top	\$1.95
254537	BI Technologies	62MR20K (3329P-1-203-VP)	3329	P	20000	0.5 W	10	1	Top Slot	Top	\$1.49
2179294	Spectrol/Vishay Corporation	75P203 (3329P-1-203)	3329	P	20000	0.5 W	10	1	Top Slot	Top	\$1.25
770101	Bourns	3329P-1-503	3329	P	50000	0.5 W	10	1	Top Slot	Top	\$1.95
95484	BI Technologies	82MR100K/3321P100K(3329P)	3329	P	100000	0.5 W	10	1	Top Slot	Top	\$1.49
254570	BI Technologies	62MR200K (3329P-1-204-VP)	3329	P	200000	0.5 W	10	1	Top Slot	Top	\$1.49
254538	BI Technologies	62MR250K (3329P-1-254-VP)	3329	P	250000	0.5 W	10	1	Top Slot	Top	\$1.95
254588	BI Technologies	62MR500K (3329P-1-504-VP)	3329	P	500000	0.5 W	10	1	Top Slot	Top	\$1.95
254596	BI Technologies	62MR1MEG (3329P-1-105-VP)	3329	P	1 Meg	0.5 W	10	1	Top Slot	Top	\$1.95
2195278	BI Technologies	82WR500 (3329U-1-501)	3329	U	500	0.5 W	10	1	Top Slot	Top	\$1.49
2195251	BI Technologies	82WFR10K (3329U-1-103)	3329	U	10000	0.5 W	10	1	Top Slot	Top	\$1.25
2201851	BI Technologies	82WFR100K (3329U-1-104)	3329	U	100000	0.5 W	10	1	Top Slot	Top	\$1.25
2195260	BI Technologies	82WFR250K (3329U-1-254)	3329	U	250000	0.5 W	10	1	Top Slot	Top	\$1.25
770144	BI Technologies	82PAR2K (3329W-1-202)	3329	W	2000	0.5 W	10	1	Side Slot	Top	\$1.95
2235196	Jameco Valuepro	3329W-1-502VP	3329	W	5000	0.5 W	10	1	Side Slot	Side	\$1.95
2235209	Jameco Valuepro	3329W-1-103VP	3329	W	10000	0.5 W	10	1	Side Slot	Side	\$1.95
770136	BI Technologies	82PAR10K (3329W-1-103)	3329	W	10000	0.5 W	10	1	Side Slot	Top	\$1.25
770161	BI Technologies	82PAR25K	3329	W	25000	0.5 W	10	1	Side Slot	Top	\$1.95
2180412	Spectrol/Vishay Corporation	75T102/3329X-1-102VP	3329	X	1000	0.5 W	10	1	Side Slot	Side	\$1.95
2276431	Bourns	3339H-1-102	3339	H	1000	0.5 W	10	4	Top Cross	Top	\$3.95