



[Click Here to Request a Large Quantity Quote](#)

[IR LED Emitters](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Type	Color	Lens Type	Package	Wavelength	Viewing Angle (deg)	Forward Voltage - Vf (Typ.)	Forward Current - If (Typ.)	Height (mm)	Mounting	Price 1
1110914	Vishay	TSAL6100	IR Emitter	InfraRed	Blue Grey	5mm, T-1 3/4	940 nm	20	1.35	100 mA	8.7	0.1"	\$0.49
2275839	Jameco Valuepro	LED-5mmIR	IR Emitter	InfraRed	Clear	5mm, T-1 3/4	940 nm	30	1.4	20 mA	8.6	0.1"	\$0.25
2285031	Major Brands	1N6265	IR Emitter	InfraRed	Clear	TO-46	940 nm	40	1.7	100 mA	3.94	0.1"	\$0.39
2279287	Jameco Valuepro	LED-5mmIR	IR Emitter	InfraRed	Clear Blue	5mm, T-1 3/4	940 nm		1.2	20 mA	8.7	0.1"	\$0.25
2125261	Vishay	TSHA4400	IR Emitter	InfraRed	Water Clear	3mm, T-1	875 nm	20	1.5	100 mA	4.5	0.1"	\$0.25
2276407	Everlight Electronics	SIR204	IR Emitter	InfraRed	Water Clear	3mm, T-1	875 nm	30	1.3	20 mA	5.2	0.1"	\$0.25
2291223	Fairchild Semiconductor	QEC113	IR Emitter	InfraRed	Water Clear	3mm, T-1	940 nm	8	1.5	50 mA	4.93	0.1"	\$0.25
1950825	Jameco Valuepro	L-34F3CS	IR Emitter	InfraRed	Water Clear	3mm, T-1	940 nm	50	1.2	20 mA	5.25	0.1"	\$0.39
372737	Jameco Valuepro	UT1883-81-880-R	IR Emitter	InfraRed	Water Clear	5mm, T-1 3/4	880 nm	10	1.5	20 mA	8.7	0.1"	\$0.39
106526	Ligitek	LVIR3333	IR Emitter	InfraRed	White Non Diffused	5mm, T-1 3/4	940 nm	20	1.2	20 mA	8.6	0.1"	\$0.35
2276663	Optek Technology	OP296B	IR Emitter	Infrared	IR Transmissive	5mm, T-1 3/4	890 nm	20	2.0	150 mA	7.6	0.1"	\$0.29
112150	Ligitek	LIR2043	IR Emitter	Infrared	Water Clear	3mm, T-1	940 nm	30	1.2	20 mA	5.2	0.1"	\$0.35