



[Click Here to Request a Large Quantity Quote](#)

[RV112BF Series Dual Audio Linear Taper Potentiometers](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Resistance (Ohms)	Power Rating	Tolerance (%)	Shaft Type	Shaft Length	Termination Style	Taper	Body Diameter	Manufacturer Series	Voltage Rating	Price 1
2272039	Taiwan Alpha	RV112BF-40-25A-B1K	1000	0.05 W	20	D	0.980"	PCB, Snap-In	Linear	11 mm	RV112BF	50 V	\$1.49
2271639	Taiwan Alpha	RV112BF-40E1-25A-B5K	5000	0.05 W	20	D	0.980"	PCB, Panel Mount	Linear	11 mm	RV112BF	50 V	\$1.49
2269495	Taiwan Alpha	RV112BF-40-25A-A10K	10000	0.05 W	20	D	0.980"	PCB, Snap-In	Audio	11 mm	RV112BF	50 V	\$1.49
2272047	Taiwan Alpha	RV112BF-40-25A-B10K	10000	0.05 W	20	D	0.980"	PCB, Snap-In	Linear	11 mm	RV112BF	50 V	\$1.49
2269503	Taiwan Alpha	RV112BF-40E1-25A-A50K	50000	0.05 W	20	D	0.980"	PCB, Panel Mount	Audio	11 mm	RV112BF	50 V	\$1.49
2271647	Taiwan Alpha	RV112BF-40-25A-A50K	50000	0.05 W	20	D	0.980"	PCB, Snap-In	Audio	11 mm	RV112BF	50 V	\$1.49
2269935	Taiwan Alpha	RV112BCF-40-25F-A50K	50000	0.05 W	20	D	0.980"	PCB, Snap-In	Audio	11 mm	RV112BF	50 V	\$1.49
2272071	Taiwan Alpha	RV112BF-40-25A-B50K	50000	0.05 W	20	D	0.980"	PCB, Snap-In	Linear	11 mm	RV112BF	50 V	\$1.49
2272015	Taiwan Alpha	RV112BF-40-25A-A100K	100000	0.05 W	20	D	0.980"	PCB, Snap-In	Audio	11 mm	RV112BF	50 V	\$1.49
2272055	Taiwan Alpha	RV112BF-40-25A-B100K	100000	0.05 W	20	D	0.980"	PCB, Snap-In	Linear	11 mm	RV112BF	50 V	\$1.49
2272023	Taiwan Alpha	RV112BF-40-25A-A500K	500000	0.05 W	20	D	0.980"	PCB, Snap-In	Audio	11 mm	RV112BF	50 V	\$1.49
2272063	Taiwan Alpha	RV112BF-40E1-25A-B1M	1 Meg	0.05 W	20	D	0.980"	PCB, Panel Mount	Linear	11 mm	RV112BF	50 V	\$1.49
2272031	Taiwan Alpha	RV112BF-40-25A-A1M	1 Meg	0.05 W	20	D	0.980"	PCB, Snap-In	Audio	11 mm	RV112BF	50 V	\$1.49